Date Printed: 6/7/2021 Page 1 / 6

# Safety Data Sheet



Trusted Quality Since 1921 \* www.rustoleum.com

## 1. Identification

**Product Name:** IC LSPR 6PK YELLOW STRIPING **Revision Date:** 

**Product Identifier:** 1648838V

Recommended Use: Marking Paint

**Rust-Oleum Corporation** Supplier:

11 Hawthorn Parkway Vernon Hills, IL 60061

**USA** 

Rust-Oleum Canada (ROCA) 200 Confederation Parkway Concord, ON L4K 4T8

Canada

Emergency Phone: 800-387-3625

Regulatory Department Preparer:

24 Hour Hotline: 847-367-7700 **Emergency Telephone:** 

Supercedes Date: **New SDS** 

**Rust-Oleum Corporation** Manufacturer:

11 Hawthorn Parkway Vernon Hills, IL 60061

USA

6/7/2021

#### 2. Hazards Identification

## Classification

Symbol(s) of Product







Signal Word

Danger

## Possible Hazards

21% of the mixture consists of ingredient(s) of unknown acute toxicity.

#### **GHS HAZARD STATEMENTS**

Flammable Aerosol, category 1 H222 Extremely flammable aerosol. H319 Eye Irritation, category 2A Causes serious eye irritation. STOT, Single Exposure, category 3, NE H336 May cause drowsiness or dizziness.

Gases under Pressure; Compressed Gas H280 Contains gas under pressure; may explode if heated.

## **GHS LABEL PRECAUTIONARY STATEMENTS**

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. NO

SMOKING.

P211 Do not spray on an open flame or other ignition source.

P251 Do not pierce or burn, even after use.

P261 Avoid breathing dust/fume/gas/mist/vapors/spray.

P264 Wash hands thoroughly after handling. P271 Use only outdoors or in a well-ventilated area.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

No Information

Date Printed: 6/7/2021 Page 2 / 6

P312 Call a POISON CENTER or doctor/physician if you feel unwell.

P405 Store locked up.

P501 Dispose of contents/container in accordance with local, regional and national regulations.

P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present

and easy to do. Continue rinsing.

P337+P313 If eye irritation persists: Get medical advice/attention.

P403+P233 Store in a well-ventilated place. Keep container tightly closed.

P410+P403 Protect from sunlight. Store in a well-ventilated place.

P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C / 122°F.

# 3. Composition / Information on Ingredients

#### **HAZARDOUS SUBSTANCES**

<u>Chemical Name</u>	CAS-No.	<u>Wt.%</u>	GHS Symbols	GHS Statements
Acetone	67-64-1	17	GHS02-GHS07	H225-319-332-336
Propane	74-98-6	14	GHS04	H280
n-Butyl Acetate	123-86-4	12	GHS02-GHS07	H226-336
n-Butane	106-97-8	6.7	GHS04	H280
Xylenes (o-, m-, p- Isomers)	1330-20-7	3.2	GHS02-GHS07	H226-315-319-332
Titanium Dioxide	13463-67-7	3.0	Not Available	Not Available
Ethyl 3-Ethoxypropionate	763-69-9	1.4	GHS06	H331
Ethylbenzene	100-41-4	0.8	GHS02-GHS07- GHS08	H225-304-332-373

## 4. First-Aid Measures

**FIRST AID - EYE CONTACT:** Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

**FIRST AID - SKIN CONTACT:** Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

**FIRST AID - INHALATION:** Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

**FIRST AID - INGESTION:** Aspiration hazard: Do not induce vomiting or give anything by mouth because this material can enter the lungs and cause severe lung damage. Get immediate medical attention. If swallowed, get medical attention.

## 5. Fire-Fighting Measures

**EXTINGUISHING MEDIA:** Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

**UNUSUAL FIRE AND EXPLOSION HAZARDS:** Water spray may be ineffective. Closed containers may explode when exposed to extreme heat due to buildup of steam. Closed containers may explode when exposed to extreme heat. Vapors may form explosive mixtures with air. Vapors can travel to a source of ignition and flash back. Isolate from heat, electrical equipment, sparks and open flame. Perforation of the pressurized container may cause bursting of the can. FLASH POINT IS LESS THAN 20°F. EXTREMELY FLAMMABLE LIQUID AND VAPOR!

**SPECIAL FIREFIGHTING PROCEDURES:** Water may be used to cool closed containers to prevent pressure buildup and possible autoignition or explosion. Full protective equipment including self-contained breathing apparatus should be used. Evacuate area and fight fire from a safe distance. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

Special Fire and Explosion Hazard (Combustible Dust): No Information

Date Printed: 6/7/2021 Page 3 / 6

#### 6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Isolate the hazard area and deny entry to unnecessary and unprotected personnel. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Ventilate area, isolate spilled material, and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations.

## 7. Handling and Storage

**HANDLING:** Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

**STORAGE:** Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Contents under pressure. Do not store above 120°F. Store large quantities in buildings designed and protected for storage of flammable aerosols. Keep away from heat, sparks, flame and sources of ignition. Avoid excess heat. Product should be stored in tightly sealed containers and protected from heat, moisture, and foreign materials.

Advice on Safe Handling of Combustible Dust: No Information

## 8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Acetone	67-64-1	20.0	250 ppm	500 ppm	1000 ppm	N.E.
Propane	74-98-6	15.0	N.E.	N.E.	1000 ppm	N.E.
n-Butyl Acetate	123-86-4	15.0	50 ppm	150 ppm	150 ppm	N.E.
n-Butane	106-97-8	10.0	N.E.	1000 ppm	N.E.	N.E.
Xylenes (o-, m-, p- Isomers)	1330-20-7	5.0	100 ppm	150 ppm	100 ppm	N.E.
Titanium Dioxide	13463-67-7	5.0	10 mg/m3	N.E.	15 mg/m3	N.E.
Ethyl 3-Ethoxypropionate	763-69-9	5.0	N.E.	N.E.	N.E.	N.E.
Ethylbenzene	100-41-4	1.0	20 ppm	N.E.	100 ppm	N.E.

#### PERSONAL PROTECTION

**ENGINEERING CONTROLS:** Provide general dilution of local exhaust ventilation in volume and pattern to keep TLV of hazardous ingredients below acceptable limits. Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Use explosion-proof ventilation equipment. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

**RESPIRATORY PROTECTION:** A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

SKIN PROTECTION: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

**OTHER PROTECTIVE EQUIPMENT:** Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

**HYGIENIC PRACTICES:** Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

Date Printed: 6/7/2021 Page 4 / 6

# 9. Physical and Chemical Properties

Appearance: **Physical State:** Aerosolized Mist Liquid Odor: Solvent Like **Odor Threshold:** N.E. Specific Gravity: 0.964 :Ha N.A. Freeze Point, °C: Viscosity: N.D. N.D. Solubility in Water: Partition Coefficient, n-octanol/ Slight N.D. water: Decomposition Temp., °C: N.D. Boiling Range, °C: Explosive Limits, vol%: -37 - 537 1.0 - 13.0Flammability: Flash Point, °C: Supports Combustion -96 **Evaporation Rate:** Auto-Ignition Temp., °C: Faster than Ether N.D. Vapor Density: Vapor Pressure: Heavier than Air N.D.

(See "Other information" Section for abbreviation legend)

## 10. Stability and Reactivity

Conditions to Avoid: Avoid temperatures above 120°F (49°C). Avoid all possible sources of ignition.

Incompatibility: Incompatible with strong oxidizing agents, strong acids and strong alkalies.

**Hazardous Decomposition:** By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

**Hazardous Polymerization:** Will not occur under normal conditions. **Stability:** This product is stable under normal storage conditions.

## 11. Toxicological Information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Causes Serious Eye Irritation

**EFFECTS OF OVEREXPOSURE - SKIN CONTACT:** No Information

**EFFECTS OF OVEREXPOSURE - INHALATION:** Harmful if inhaled. High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs. Prolonged or excessive inhalation may cause respiratory tract irritation.

**EFFECTS OF OVEREXPOSURE - INGESTION:** Harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: May cause central nervous system disorder (e.g., narcosis involving a loss of coordination, weakness, fatigue, mental confusion, and blurred vision) and/or damage. High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage. Overexposure to xylene in laboratory animals has been associated with liver abnormalities, kidney, lung, spleen, eye and blood damage as well as reproductive disorders. Effects in humans, due to chronic overexposure, have included liver, cardiac abnormalities and nervous system damage. IARC lists Ethylbenzene as a possible human carcinogen (group 2B). Contains Titanium Dioxide. Titanium Dioxide is listed as a Group 2B-"Possibly carcinogenic to humans" by IARC. No significant exposure to Titanium Dioxide is thought to occur during the use of products in which Titanium Dioxide is bound to other materials, such as in paints during brush application or drying. Risk of overexposure depends on duration and level of exposure to dust from repeated sanding of surfaces or spray mist and the actual concentration of Titanium Dioxide in the formula. (Ref: IARC Monograph, Vol. 93, 2010)

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

#### **ACUTE TOXICITY VALUES**

The acute effects of this product have not been tested. Data on individual components are tabulated below:

CAS-No.	Chemical Name	Oral LD50	Dermal LD50	Vapor LC50
67-64-1	Acetone	5800 mg/kg Rat	>15700 mg/kg Rabbit	50.1 mg/L Rat
123-86-4	n-Butyl Acetate	10768 mg/kg Rat	>17600 mg/kg Rabbit	> 21 mg/L Rat
106-97-8	n-Butane	N.E.	N.E.	658 mg/L Rat
1330-20-7	Xylenes (o-, m-, p- Isomers)	3500 mg/kg Rat	>4350 mg/kg Rabbit	29.08 mg/L Rat
13463-67-7	Titanium Dioxide	>10000 mg/kg Rat	2500 mg/kg	N.E.
763-69-9	Ethyl 3-Ethoxypropionate	5000 mg/kg Rat	>9500 mg/kg Rabbit	>5.96 mg/L Rat
100-41-4	Ethylbenzene	3500 mg/kg Rat	15400 mg/kg Rabbit	17.4 mg/L Rat

N.E. - Not Established

# 12. Ecological Information

Date Printed: 6/7/2021 Page 5 / 6

**ECOLOGICAL INFORMATION:** Product is a mixture of listed components.

## 13. Disposal Information

**DISPOSAL INFORMATION:** Do not incinerate closed containers. This product as supplied is a USEPA defined ignitable hazardous waste. Dispose of unusable product as a hazardous waste (D001) in accordance with local, state, and federal regulation.

# 14. Transport Information

UN Number:	Domestic (USDOT)	International (IMDG)	<u>Air (IATA)</u>	TDG (Canada)
	N.A.	1950	1950	N.A.
Proper Shipping Name:	Paint and Related Spray Products in Ltd Qty	Aerosols	Aerosols, flammable	Aerosols
Hazard Class: Packing Group: Limited Quantity:	N.A.	2	2.1	N.A.
	N.A.	N.A.	N.A.	N.A.
	Yes	Yes	Yes	Yes

# 15. Regulatory Information

# U.S. Federal Regulations:

#### **CERCLA - SARA Hazard Category**

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Gas under pressure, Serious eye damage or eye irritation, Specific target organ toxicity (single or repeated exposure)

#### **SARA Section 313**

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

Chemical NameCAS-No.Xylenes (o-, m-, p- Isomers)1330-20-7Ethylbenzene100-41-4Aluminum Oxide1344-28-1

#### **Toxic Substances Control Act**

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

# U.S. State Regulations:

## California Proposition 65

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov.

Date Printed: 6/7/2021 Page 6 / 6

## 16. Other Information

**HMIS RATINGS** 

Health: 2\* Flammability: 4 Physical Hazard: 0 Personal Protection: X

**NFPA RATINGS** 

Health: 2 Flammability: 4 Instability: 0

Maximum Incremental Reactivity: 0.66

SDS REVISION DATE: 6/7/2021

**REASON FOR REVISION:** 

Legend: N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.