

METAL MAN[®]

Arc 80T DC Inverter Stick Welder



DESCRIPTION

The Metal Man Arc 80T is a DC-only inverter stick welder with an exceptionally smooth stick welding performance in an extremely small package. It is intended for use for welding steel, stainless steel, cast iron, and hard surfacing, using electrodes from 1/16 inch to 3/32 inch.

The Arc 80T is super portable allowing the operator the flexibility to use this welder for mobile and outdoor applications. This unit is equipped with a cooling fan and thermal overload protection. Quick connect weld cable connections make set-up and tear down quick and easy.

Order Part Number: ARC 80T

SPECIFICATIONS

Item	Description
Power Supply	120V, 20A, 60 Hz, Single-Phase
No-Load Voltage	70 Volts DC
Duty Cycle	40% @ 75A
Suggested Electrodes	E6013, E7014, E7018, Stainless Steel
Electrode Diameters	1/16" to 3/32"
Dimensions	12-3/8" x 4.25" x 7"
Weight	6.6 lbs.
Shipping	13" x 8" x 9" 9.6 lbs.
UPC	857448005629

METAL MAN[®]