

COMMANDER™ TRAFFIC DRUM

Engineered for
durability and performance

Enhanced Material Formulation for Superior Reboundability & Durability

- Available in high and low density polyethylene
- Five tier design
- MASH Accepted, Meets MUTCD Standards

Extended Usable Life

NEW Power Dome

- Handle and Dome interfuse creating strength
- thicker wall
- resists denting


Power Dome

Gentle slope of dome
merges with handle




- Customize Your Drums →
- Name or logo molded in at our factory

Comfort Grip Handle



20% More Per Truckload


- ### NEW Tighter Stacking & Packing
- Maximizes transport and storage space



Improved Tire Interlock

NEW Tire Locking Ring Design


- Inhibits movement of drum on road surface
- wedge fit created from skirt ramp and elliptical shaped bottom
- Textured skirt increases friction and grabs tire
- Anti-roll design, flat sections on two sides



Revolutionary Light Folding

NEW Light Mounting Design


- Light easily turns for stacking



PLASTICADE®

Plasticade.com

COMMANDER™ TRAFFIC DRUM



Specs	
Composition	High Density or Low Density Polyethylene
Weight	8 lbs.
Color	Orange
Retroreflective Sheeting	Available in Engineer, High Intensity Prismatic, or Diamond Grades
Stripes	4" W or 6" W
Tire Ring	22.5" inside diameter 24 lbs. Bundled in stacks of 35 ea.



PLASTICADE®

100 Howard Avenue
Des Plaines, IL 60018
phone (800) 772-0355
fax (847) 966-8074

Plasticade.com

Patent Pending
MADE IN THE USA