



SALAMANDER ELECTRIC HEATER

- HEAVY DUTY FINTUBE ELEMENT FOR UNIFORM HEAT OUTPUT
- BUILT-IN THERMOSTAT AND SAFETY THERMAL CUTOFF
- TIP-OVER SWITCH FOR EXTRA SAFETY
- EXCELLENT CHOICE TO HEAT AREAS THAT ARE INDOORS AND ENCLOSED CEILING HEIGHTS OF 15 FEET OR LESS



Model #	VOLTS	KW	PHASE	AMPS	BTU	TEMP. Rise, F
653558	240	10	1	41.7	34,120	46
653673 653566	208	15	3	41.7	51,180	61
653670 653567	240	15	1	62.5	51,180	46
653671 653568	240	15	3	36.1	51,180	46
653672 653569	480	15	3	18.1	51,180	46
653674 246068	480	30	3	36	102,389	65

AVERAGE MINUTES TO ACHIEVE TEMPERATURE RISE

AREA SIZE:	1000 SQ.FT		1500 SQ.FT		2000 SQ.FT	
	TEMP RISE		TEMP RISE		TEMP RISE	
HEATER	20°F	40°F	20°F	40°F	20°F	40°F
10 KW	70 MIN	140 MIN	105 MIN	210 MIN	-	-
15 KW	47 MIN	94 MIN	71 MIN	142 MIN	94 MIN	188 MIN
30 KW	23 MIN	46 MIN	35 MIN	70 MIN	47 MIN	94 MIN

NOTE: Based on a 15' ceiling height. Lower ceiling height will reduce the time