

Drain Cleaning Collection

Hygienic | Sanitary | Safe

Remco
a Vikan company



ACO Modular 200



Remco provides high-quality, color-coded FDA-compliant tools that are ideally suited for food processing and food retail environments. Remco features Vikan's advanced line of brushes, brooms, and squeegees specifically designed to meet the cleaning requirements of drainage systems. These tools are durable, efficient, and cost-effective, making them an excellent solution for challenges commonly encountered during drain cleaning. The total-color and hygienic design of these tools are designed to prevent cross-contamination as part of a color-coding system.


Hygienic Cleaning Tools for Drainage Systems

Available from Remco Products

About 30% of highly contaminated surfaces in a food facility stem from biofilms and bacteria found in drainage systems. Hygienic color-coded cleaning tools, specifically those designed for drain cleaning, can help prevent cross-contamination within a facility.

Drains and gullies present specific challenges to sanitation efforts. Our variety of sanitation tools assist in the detailed cleaning of nooks and crannies commonly found in these areas.

Regardless of the operation's size and complexity, Vikan and Remco offer tools that come in up to 12 distinguishable colors, making them ideal for integration with color-coded plans.



Vikan® 51" Ultra Hygiene Handle
29609



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
59.25"	1.26"	1.26"
Weight:	0.85 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene	

Vikan® 59" Ultra Hygiene Handle
29629



Colors Available: 1 2 3 4 5 6 7 8 9 10 11 12

Length:	Width:	Height:
59.1"	1.26"	1.26"
Weight:	0.99 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene	

Vikan® 40" Ultra Hygiene Handle
29689



Colors Available: 2 3 4 5 6 9

Length:	Width:	Height:
39.4"	1.26"	1.26"
Weight:	0.68 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene	

Vikan® 3" Tube Brush
5380-77-9



Colors Available: 2 3 4 5 6 9

Length:	Width:	Height:
6.1"	3.15"	3.15"
Weight:	0.26 lbs.	
Maximum Temperature:	250°F	
Material:	Polyester/Polypropylene/SS	

Vikan® 4" Tube Brush
5380-103-9



Colors Available: 2 3 4 5 6 9

Length:	Width:	Height:
6.5"	3.9"	3.9"
Weight:	0.33 lbs.	
Maximum Temperature:	250°F	
Material:	Polyester/Polypropylene/SS	

Vikan® 2" Stainless Steel Handle Mounted Scraper
40109



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
8.07"	1.97"	1.26"
Weight:	0.18 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/Stainless Steel	



Vikan® Drain Cleaning Brush
53619



Colors Available:

Length:	Width:	Height:
10.83"	3.78"	2.36"
Weight:	0.35 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/SS/Polyester	

Vikan® Ø3.5" One-Piece Pipe Brush
5381-90-9



Colors Available:

Length:	Width:	Height:
16.93"	3.54"	3.54"
Weight:	0.37 lbs.	
Maximum Temperature:	250°F	
Material:	Polyester/Polypropylene/SS	

Vikan® Long Handle Scrubbing Brush
41869



Colors Available:

Length:	Width:	Height:
15.75"	2.75"	2.8"
Weight:	0.53 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/Polyester/SS	

Vikan® Stiff Tank Brush
70379



Colors Available:

Length:	Width:	Height:
8.07"	5.12"	3.94"
Weight:	1.04 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/Polyester/SS	

Vikan® High-Low Brush
70479



Colors Available:

Length:	Width:	Height:
10.43"	5.91"	3.94"
Weight:	1.1 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/Polyester/SS	

Vikan® 3 Gallon Bucket
56869



Colors Available:

Length:	Width:	Height:
12.8"	13"	13"
Weight:	2.2 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/Stainless Steel	

Denotes product is made of FDA-compliant materials.

Denotes product is autoclavable to 250°F.

Denotes product is dishwasher safe to 176°F.

Denotes bristle type.



12" Deck/Wall Scrub
70609



Colors Available: 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20

Length:	Width:	Height:
12.01"	3.35"	4.33"
Weight:	1.3 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/Polyester/SS	



16" Ultra Hygiene Squeegee
71409



Colors Available: 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20

Length:	Width:	Height:
15.75"	3.15"	3.54"
Weight:	0.57 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/Rubber	



24" Ultra Hygiene Squeegee
71609



Colors Available: 1 2 3 4 5 6 7 8 9

Length:	Width:	Height:
23.6"	3.7"	4.3"
Weight:	0.84 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/Rubber	



Wall Bracket, Grip Band Module
10119



Colors Available: 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20

Length:	Width:	Height:
3.27"	3.43"	1.89"
Weight:	0.18 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/TPE Rubber/Polyamide	



Wall Bracket, Grip Band Module
10139



Colors Available: 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20

Length:	Width:	Height:
3.27"	3.43"	1.89"
Weight:	0.18 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/TPE Rubber/Polyamide	



Wall Bracket, Double Hook Module
10149



Colors Available: 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20

Length:	Width:	Height:
3.23"	3.07"	1.89"
Weight:	0.12 lbs.	
Maximum Temperature:	250°F	
Material:	Polypropylene/Polyamide	

Denotes product is made of FDA-compliant materials.

Denotes product is autoclavable to 250°F.

Denotes product is dishwasher safe to 176°F.

Denotes bristle type.

For more information, visit GlobalIndustrial.com.



Web: www.globalindustrial.com

Phone: 1-800-645-1232

© 2022 Remco Products 3/22 RMC-A120-GLO
Vikan® is a registered trademark of Vikan A/S.
Remco is Vikan's dedicated North American company.

Action images courtesy ACO
Phone: (800) 543-4764
info@acousa.com | www.acobuildingdrainage.com

ACO Modular 200

