

## Mister/Extractor/Detailer

Item# PFMS

## **Disinfectant Mister and Extractor/Detail Cleaner**

- This mister is designed for use with all water-based disinfectants from the EPA "List N".
- Dual brass nozzles atomizer nozzle and a wide area jet fan nozzle
- Whisper quiet when in mist only mode
- 3.5-gallon solution
- On-board storage for hoses, wands, and nozzles
- 35' Misting Hose
- 18" Misting Wand with atomizer nozzle pre-installed
- 25' power cord
- Built-in dolly with wheels features collapsible handle for easy use and storage



## **DISINFECT AND CLEAN**

Quickly and easily disinfect all of your high touch areas with this Mister/Extractor dual purpose machine. The mister features over a 120' reach providing plenty of room to work and the 3.5 gallon capacity allows you to mist between 7,500 - 10,000\* square feet of space. Easily extract/clean smaller spaces with the detail tool and optional floor tool that is perfect for touchups and cleaning in tight locations where bigger machines just can't fit. It's compact design includes a telescoping handle and 5" transport wheels that makes it simple to transport and store. \*Variance dependent on user application method.



**Easy Transport**ThePowr-Flite Nebula comes standard with a telescoping handle for easy transport



**10' Rigid Hose with Outsider Solution Line** 10' hose length provides the flexibility needed to reach almost anywhere you need to clean



Superior reach
35 foot misting hose and 25 foot power
cord allows for 120 foot of complete
disinfecting coverage.



Misting Wand
Durable 18" metal misting wand provides
easy application of disinfectant. Two included
nozzle tips meet application needs.



Hand Tool
Great for both spot/upholstery and detail cleaning of fabrics, upholstery and carpeting.

PUMP PRESSURE	55 PSI / 3.8 BAR
PUMP FLOW RATE	Atomizer nozzle .06 GPM, Fan nozzle & extraction .25 GPM
WATERLIFT	extraction mode only = 89 in/ 226 cm
AIRFLOW	104 cfm/ 177 M³/hr (extraction mode only)
VOLTAGE	Voltage = 115V
AMPS	Mist mode 1 A, Extractor mode 8.9
WHEELS	5"
WEIGHT	Machine only weight = 36 lbs
	Shipping weight = 41 lbs
VACUUM MOTOR	2 stage (Extraction Mode Only)
SOLUTION TANK	3.5 Gal / 13.2 L
RECOVERY TANK	2.5 Gal/9.5 L
POWER CORD LENGTH	25 feet/ 7.6 m
SOLUTION HOSE LENGTH	35 feet/ 10.7 m
VACUUM HOSE LENGTH	10 feet/ 3.05 m
MISTING WAND	18" / 45.72 cm