

## Product information

# 78 61 125

## Electronic Super Knips®


DIN ISO 9654



- Also suitable for cutting glass fibre cables (fibre optics)
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Special tool steel, oil hardened in multiple stages
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Ground, very sharp cutting edges without bevel
- Precisely shaped tips cut wires close to a surface from Ø 0.2 mm
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter



General	
Article No.	78 61 125
EAN	4003773035404
Pliers	burnished
Head	burnished
Handles	with multi-component grips
Weight	56 g
Dimensions	125 x 62 x 13 mm
Standard	DIN ISO 9654
REACH compliant	no
RohS compliant	no
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 1.2 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 1.6 mm
Jaw length (B)	9 mm
Jaw thickness (joint) (D)	7.5 mm
Head width (A)	13.5 mm



<b>Classification</b>	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112149

*technical change and errors excepted*

