

# Product Data Sheet

No. 51214 - 08/15

## MAX BUTANE FUEL

AEROSOL VOC <100%

PRODUCT NUMBER: 1214 8 OZ. NET WT.



### I. GENERAL DESCRIPTION

**Features:** Max Butane Fuel contains a highly refined and filtered liquefied petroleum gas (LPG) that is designed to be used in the Max Table Top Burner. It features a notched collar valve to ensure proper alignment with gas appliance and a countersink release vent and triple seam structure that allows gas to release safely in the event of overpressure. The can is disposable (cannot be refilled) and UL approved.

**Benefits:** Max Butane Fuel is purified for excellent flame quality. The can is specifically designed to fit all Max Table Top Burner.

**Uses:** Use while camping, picnicking, table side cooking, or catering. Great addition to any emergency preparedness kit.

**Warnings:** Refer to product operating instruction guides for use in the appropriate appliance. Not for indoor or household use. Extremely Flammable. DO NOT use or store near heat or open flame. DO NOT puncture or incinerate. Use in well ventilated area. DO NOT attempt to light appliance when gas odor is detected. Keep out of the reach of children. Once all of the fuel is used, discard empty can in accordance with local aerosol disposal regulations. Refer to the Safety Data Sheet for specific information on material hazards.

This product contains and when burned produces chemicals known to the State of California to cause cancer and birth defects or other reproductive harm.

Designed for use in Max Table Top Burner. Failure to use in the above appliances may result in unsafe operation and danger to the operator.

**Compatible with:**  
Max Table Top Burner #8253

#### Packaging:

Each can:	8 oz. net wt. (227 g)	13.1 fl. oz. (388 ml)	
Case (12/case):	11 lbs. (4.9 kg)	0.47 CF (0.013 CM)	11.3" x 8.5" x 8.4"

---

## II. CHARACTERISTICS AND PROPERTIES

---

**Specifications:**

None

**Appearance:**

Clear gas, non-staining

**Color:**

Colorless

**Odor:**

Odorized gas

**Performance and Chemical Properties:****Aerosol**

Weight per gallon.....	4.83 lbs
Specific gravity (H <sub>2</sub> O = 1) .....	0.58 @ -50°C
Flammability:	
Label marking .....	Extremely flammable
Flash point .....	<0°C
Volatile Organic Compound level .....	100%
Operating temperature range .....	40° to 110°F (5° to 43° C)
Auto ignition temperature range .....	761° to 842°F (405° to 450°C)
Boiling point.....	30° to 40°F (-1° to 4°C)
Vapor pressure .....	30 psi @ 70°F

**Base Materials** ..... LPG Hydrocarbon Propellant

---

## III. SHIPPING, STORAGE AND HEALTH

---

IMDG number .....	UN2037
D.O.T. container spec.....	2P
D.O.T. shipping description.....	Receptacles, small, containing gas or gas cartridges
Warehouse storage level number.....	NFPA 30B Level 3
Hazardous class (CFR-49) .....	2.1
Storage temperature .....	32° to 120°F (0° to 49°C)
HMIS ratings	
Health .....	1
Fire .....	4
Reactivity .....	0

---

## IV. MISCELLANEOUS

---

Does not contain ozone depleting substances.

---

## V. WARRANTY

---

1-year warranty to the original registered owner on all products from date of purchase. User returns, exchanges and defective refunds must be made with the original place of purchase. Because Aervoe cannot control Buyer's handling or use of product, Aervoe makes no warranty expressed or implied when not used or stored in accordance with directions. Aervoe shall not be liable for cost of labor, incidental or consequential damages, and this warranty is limited to replacement or repair of product or credit of purchase.