

## 

AWG 10-20

13 72

KNIPEX FORGED WIRE STRIPPER


Strips 10 to 20 AWG solid and stranded

## CUTTING SCREWS JUST GOT FASTER

Simply push and cut — no threading required




Non-threading screw cutting can be used from either the front or the back



- » Induction hardened blades and screw shear
- » Knurled tip for better grip
- Internal spring for easy opening
- » High-grade special tool steel, forged, multi stage oil-hardened



Shear type blades easily cut BX/MC cable



- Shear cutting blades offer 50% higher cutting capacity than competition
- Cutting blades designed to cut individual wires, NM-B, BX/MC and battery cable





13 71 8 Non-slip plastic coated handles



