SAFETY DATA SHEET

Issue Date 21-Jul-2022 **Revision Date** 12-Oct-2021 **Version** 2

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier
Product Name Pot, Pan and Dish Detergent

Other means of identification
Product Code 641623
Synonyms None

Details of the supplier of the safety data sheet
Company Name Global Industrial
2505 Mill Center Parkway
Buford GA 30518
(888) 978-7759

Emergency telephone number
Emergency Telephone Chemtrec (US &Canada) 800-424-9300
Chemtrec (outside US & Canada) 703-527-3887

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status
This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Serious eye damage/eye irritation	Category 2

Label elements

Emergency Overview

Warning

Hazard statements
Causes serious eye irritation



Appearance Clear Blue **Physical state** Liquid **Odor** Pleasant

Precautionary Statements - Prevention
Avoid direct contact with eyes.

Precautionary Statements - Response
Specific Treatment (See Section 4 on the SDS)
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
If eye irritation persists: Get medical advice/attention
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell
IF SWALLOWED: Rinse mouth. DO NOT induce vomiting
Drink plenty of water
Immediately call a POISON CENTER or doctor/physician

Precautionary Statements - Disposal
Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)
Other Information
• Toxic to aquatic life with long lasting effects

Unknown Acute Toxicity 0 % of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Cocamidopropyl Hydroxysultaine	68139-30-0	3-7	*
Sodium Laureth Sulfate	68585-34-2	1-5	*
Sodium Alpha Olefin Sulfonate	68439-57-6	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

Skin Contact Wash off immediately with plenty of water. If skin irritation persists, call a physician.

Eye contact Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If symptoms persist, call a physician.

Inhalation Remove to fresh air. If symptoms persist, call a physician.

Ingestion Rinse mouth. Drink plenty of water. Do NOT induce vomiting. If symptoms persist, call a physician.

Self-protection of the first aider Use personal protective equipment as required.

Most important symptoms and effects, both acute and delayed

Symptoms Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians May cause sensitization of susceptible persons.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media
Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical
In the event of fire and/or explosion do not breathe fumes. May cause sensitization by inhalation and skin contact. Thermal decomposition can lead to release of irritating and toxic gases and vapors.

Explosion data
Sensitivity to Mechanical Impact None.
Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters
As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with eyes and skin. Use personal protective equipment as required.

Environmental precautions

Environmental precautions Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Prevent product from entering drains. Soak up with inert absorbent material. Pick up and transfer to properly labeled containers. After cleaning, flush away traces with water.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Ensure adequate ventilation, especially in confined areas. Use personal protective equipment as required.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep out of the reach of children. Keep containers tightly closed in a cool, well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection No special technical protective measures are necessary.

Skin and body protection No special technical protective measures are necessary.

Respiratory protection No protective equipment is needed under normal use conditions.

General Hygiene When using do not eat, drink or smoke. Wash contaminated clothing before reuse.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Liquid
Appearance Clear Blue
Color Blue

Odor	Pleasant
Odor threshold	No Information available

Property	Values	Remarks • Method
pH	7.0 - 8.0	
Specific Gravity	1.025	
Viscosity	> 1000 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	None	
Boiling point / boiling range		
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

Other Information

Density Lbs/Gal	8.54
VOC Content (%)	Not Applicable

10. STABILITY AND REACTIVITY

Reactivity
No data available

Chemical stability
Stable under recommended storage conditions.

Possibility of Hazardous Reactions
None under normal processing.

Conditions to avoid
Extremes of temperature and direct sunlight.

Incompatible materials
None known based on information supplied.

Hazardous Decomposition Products
None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	Not an expected route of exposure.
Eye contact	Avoid contact with eyes. Direct contact may cause serious eye irritation.
Skin Contact	Prolonged or repeated contact may dry skin and cause irritation. May cause sensitization by skin contact.
Ingestion	Do not taste or swallow. May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Cocamidopropyl Hydroxysultaine 68139-30-0	= 5600 mg/kg (Rat)	-	-
Sodium Alpha Olefin Sulfonate 68439-57-6	= 2220 mg/kg (Rat)	> 740 mg/kg (Rabbit)	-

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation MAY CAUSE SKIN IRRITATION.
Sensitization May cause sensitization by skin contact.
Germ cell mutagenicity No Information available.
Carcinogenicity No Information available.
Reproductive toxicity No Information available.
STOT - single exposure No Information available.
STOT - repeated exposure No Information available.
Chronic toxicity Repeated contact may cause allergic reactions in very susceptible persons. Avoid repeated exposure.
Aspiration hazard No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 0 % of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .
ATEmix (oral) 36,564.30
ATEmix (dermal) 46,296.20

12. ECOLOGICAL INFORMATION

Ecotoxicity

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Sodium Chloride 7647-14-5	-	5560 - 6080: 96 h Lepomis macrochirus mg/L LC50 flow-through 12946: 96 h Lepomis macrochirus mg/L LC50 static 6020 - 7070: 96 h Pimephales promelas mg/L LC50 static 7050: 96 h Pimephales promelas mg/L LC50 semi-static 4747 - 7824: 96 h Oncorhynchus mykiss mg/L LC50 flow-through 6420 - 6700: 96 h Pimephales promelas mg/L LC50 static	340.7 - 469.2: 48 h Daphnia magna mg/L EC50 Static 1000: 48 h Daphnia magna mg/L EC50
Sodium Alpha Olefin Sulfonate 68439-57-6	-	1.0 - 10.0: 96 h Brachydanio rerio mg/L LC50 static 12.2: 96 h Brachydanio rerio mg/L LC50 semi-static	-
Lauramine Oxide 1643-20-5	-	134: 96 h Danio rerio mg/L LC50 semi-static	-
Sodium Sulfate 7757-82-6	-	3040 - 4380: 96 h Lepomis macrochirus mg/L LC50 static 13500: 96 h Lepomis macrochirus mg/L LC50 13500 - 14500: 96 h Pimephales promelas mg/L LC50 6800: 96 h Pimephales promelas mg/L LC50 static	2564: 48 h Daphnia magna mg/L EC50 630: 96 h Daphnia magna mg/L EC50

Persistence and degradability

No Information available.

Bioaccumulation
No Information available.

Other adverse effects No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Do not reuse container.

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT Not regulated

TDG Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL/NDSL	Complies

Legend:
TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313
Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)
This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA
This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product has been evaluated and does not require warning labeling under California Proposition 65.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Sodium Sulfate 7757-82-6	-	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	**Health hazards** 2	**Flammability** 0	**Instability** 0	**Physical and Chemical Properties** -
HMIS	**Health hazards** 2	**Flammability** 0	**Physical hazards** 0	**Personal protection** X

Issue Date 21-Jul-2022
Revision Date 12-Oct-2021
Revision Note
No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet