

## Specifications



*Rated for indoor  
use only*

**Model 761217  
Wall Mount Water Cooler,  
Filtered, Graphite/Stainless Steel**

### FEATURES:

- Easy-touch front and side push-bar control
- 3000-gallon capacity filtration system with NSF/ANSI 42 & 53 (lead, class 1 particulate, chlorine, taste and odor)
- Keyed door for easy filter access
- Laminar water flow ensures minimal splash
- Drainage system eliminates standing water
- LED filter level indicator display
- Flexible safety bubbler

### COOLING SYSTEM:

- Hermetically-sealed, single-phase reciprocating compressor; lifetime lubrication
- Fan cooled condenser with copper tube and aluminum fins; permanently lubricated motor
- Cooling system includes self-cleansing tube tank, continuous copper tubing, stainless steel tank and EPS foam insulation; meets UL requirements for self-extinguishing material
- R134a refrigerant
- Easily accessible and adjustable thermostat

### CONSTRUCTION:

- Stainless steel pan with integral drain
- Galvanized structural steel frame
- Rust-proof and dent resistant lower cover

Meets ADA Guidelines

Lead-Free Certified to NSF/ANSI 372

Certified to UL399 and CAN/CSA 22.2 No. 120




### WARRANTY:

5 year limited warranty on refrigeration system. Electrical components and water system are warranted for 12 months from the date of installation, or 18 months from the shipment date (whichever date comes first).

**Replacement Filters:  
Model 670336**

*For more information visit: [globalindustrial.com](http://globalindustrial.com)  
or call 1-800-645-1232*

## Specifications Chart

Specifications Chart							
Model	Voltage/Hertz	*Chilling Cap.	F.L. Amps	Rated Watts	UL399 and CAN/CSA 22.2 No. 120 Certified	ADA Compliant	ANSI/NSF 372 Certified
761217	115V/60Hz	8 GPH	1.9	219	✓	✓	✓

\*At 46° - 54° (F) against ambient air temperature of 77° (F)

PATENTS PENDING