

Specifications



**Model 761218
Wall Mount Water Bottle
Refilling Station, Filtered,
Graphite/Stainless Steel**

**Rated for indoor
use only**

**Replacement Filters:
Model 670336**

For more information visit:
globalindustrial.com
or call 1-800-645-1232

FEATURES:

- Touchless, sensor activation with auto 20-second shut-off
- Easy-touch front and side push-bar control
- 3000-gallon capacity filtration system with NSF/ANSI 42 & 53 (lead, class 1 particulate, chlorine, taste and odor)
- Keyed door for easy filter access
- Quick-fill rate of 1.0 GPM
- Laminar water flow ensures minimal splash
- Drainage system eliminates standing water
- LED filter level indicator display
- LED display counter tracks bottle quantity saved from waste
- Flexible safety bubbler

COOLING SYSTEM:

- Hermetically-sealed, single-phase reciprocating compressor; lifetime lubrication
- Fan cooled condenser with copper tube and aluminum fins; permanently lubricated motor
- Cooling system includes self-cleansing tube tank, continuous copper tubing, stainless steel tank and EPS foam insulation; meets UL requirements for self-extinguishing material
- R134a refrigerant
- Easily accessible and adjustable thermostat

CONSTRUCTION:

- Stainless steel pan with integral drain
- Galvanized structural steel frame
- Stainless steel bottle filler trim
- Rust-proof and dent resistant lower cover

Meets ADA Guidelines




Lead-Free Certified to NSF/ANSI 372

Certified to UL399 and CAN/CSA 22.2 No. 120

WARRANTY:

5 year limited warranty on refrigeration system. Electrical components and water system are warranted for 12 months from the date of installation, or 18 months from the shipment date (whichever date comes first).

Specifications Chart

Specifications Chart							
Model	Voltage/Hertz	*Chilling Cap.	F.L. Amps	Rated Watts	UL399 and CAN/CSA 22.2 No. 120 Certified	ADA Compliant	ANSI/NSF 372 Certified
761218	115V/60Hz	8 GPH	1.9	219	✓	✓	✓

*At 46° - 54° (F) against ambient air temperature of 77° (F)

PATENTED AND OTHER PATENTS PENDING