

1. PRODUCT AND COMPANY IDENTIFICATION**Product identifier****Product Name** Air Conditioning Coil & Fin Cleaner**Other means of identification****Product Code** 670282**Synonyms** None**Details of the supplier of the safety data sheet****Company Name** Global Industrial
2505 Mill Center Parkway
Buford GA 30518
(516) 608-3000**Emergency telephone number****Emergency Telephone** Chemtrec (US & Canada) 800-424-9300
Chemtrec (outside US & Canada) 703-527-3887**2. HAZARDS IDENTIFICATION****Classification****OSHA Regulatory Status**

This product has been classified in accordance with the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Skin corrosion/irritation	Category 3

Label elements**Emergency Overview****Warning****Hazard statements**

Causes mild skin irritation

Appearance Clear Blue**Physical state** Liquid**Odor** Cherry**Precautionary Statements - Response**

Immediately call a POISON CENTER or doctor/physician

Specific Treatment (See Section 4 on the SDS)

IF ON SKIN: Wash with plenty of soap and water

If skin irritation occurs: Get medical advice/attention

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Drink plenty of water

Immediately call a POISON CENTER or doctor/physician

Precautionary Statements - Disposal

Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)**Other Information**

Unknown Acute Toxicity

1% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
2-Hydroxypropanoic acid	79-33-4	1-5	*
Surfactant Blend	Proprietary	1-5	*
PROPRIETARY	Proprietary	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES**First aid measures****Skin Contact**

Wash off immediately with soap and plenty of water. If skin irritation persists, call a physician.

Eye contact

Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

Inhalation

Remove to fresh air.

Ingestion

Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed**Symptoms**

Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed**Note to physicians**

Treat symptomatically.

5. FIRE-FIGHTING MEASURES**Suitable extinguishing media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.**Specific hazards arising from the chemical**

No Information available.

Explosion data**Sensitivity to Mechanical Impact** None.**Sensitivity to Static Discharge** None.**Protective equipment and precautions for firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES**Personal precautions, protective equipment and emergency procedures****Personal precautions**

Ensure adequate ventilation, especially in confined areas.

Environmental precautions

Environmental precautions Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE**Precautions for safe handling**

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control parameters****Appropriate engineering controls**

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Safety glasses or chemical splash goggles.

Skin and body protection Wear chemical resistant gloves. Wear suitable protective clothing.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES**Information on basic physical and chemical properties**

Physical state Liquid
Appearance Clear Blue
Color Blue
Odor Cherry
Odor threshold No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	2.5 - 4.0	
Specific Gravity	1.011	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	> 205 °F	
Boiling point / boiling range		
Evaporation rate	No Information available	

Flammability (solid, gas)	No data available
Flammability Limits in Air	
Upper flammability limit:	No Information available
Lower flammability limit:	No Information available
Vapor pressure	No Information available
Vapor density	No Information available
Water solubility	Complete
Partition coefficient	No Information available
Autoignition temperature	No Information available
Decomposition temperature	No Information available

Other Information

Density Lbs/Gal	8.42
VOC Content (%)	Not Applicable

10. STABILITY AND REACTIVITY**Reactivity**

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Extremes of temperature and direct sunlight.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure****Product Information**

Inhalation	Avoid breathing vapors or mists. Inhalation of vapors in high concentration may cause irritation of respiratory system.
Eye contact	Avoid contact with eyes. Contact with eyes may cause irritation.
Skin Contact	Avoid contact with skin. Causes mild skin irritation.
Ingestion	Do not taste or swallow. May cause stomach distress, nausea, or vomiting.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
2-Hydroxypropanoic acid 79-33-4	= 3730 mg/kg (Rat) = 3543 mg/kg (Rat)	> 2000 mg/kg (Rabbit) > 2 g/kg (Rabbit)	> 7.94 mg/L (Rat) 4 h
Surfactant Blend	> 2000 mg/kg (Rat)	> 2000 mg/kg (Rat)	-

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation MAY CAUSE SKIN IRRITATION.

Sensitization	No Information available.
Germ cell mutagenicity	No Information available.
Carcinogenicity	No Information available.
Reproductive toxicity	No Information available.
STOT - single exposure	No Information available.
STOT - repeated exposure	No Information available.
Aspiration hazard	No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 1% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (dermal)	36,255.00
ATEmix (inhalation-dust/mist)	225.79

12. ECOLOGICAL INFORMATION**Ecotoxicity**

1% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-Hydroxypropanoic acid 79-33-4	3.5: 70 h Pseudokirchneriella subcapitata mg/L EC50	320: 96 h Brachydanio rerio mg/L LC50 semi-static 100 - 180: 96 h Lepomis macrochirus mg/L LC50 static 100 - 180: 96 h Oncorhynchus mykiss mg/L LC50 static	180 - 320: 48 h Daphnia magna mg/L EC50 Static 240: 48 h Daphnia magna mg/L EC50
Surfactant Blend	-	1.2: 96 h Oncorhynchus mykiss mg/L LC50	5.3: 48 h Daphnia mg/L LC50
Trisodium Citrate Dihydrate 6132-04-3	18000 - 32000: 96 h Chlorella vulgaris mg/L EC50	18000 - 32000: 96 h Poecilia reticulata mg/L LC50	5600 - 10000: 48 h Daphnia magna mg/L EC50

Persistence and degradability

No Information available.

Bioaccumulation

Bioaccumulative potential.

Chemical Name	Partition coefficient
2-Hydroxypropanoic acid 79-33-4	-0.62

Other adverse effects No Information available

13. DISPOSAL CONSIDERATIONS**Waste treatment methods**

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Do not reuse container.

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT Not regulated

TDG Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
DSL/NDSL Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product has been evaluated and does not require warning labeling under California Proposition 65.

U.S. State Right-to-Know Regulations

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 2	Flammability 0	Instability 0	Physical and Chemical Properties - Personal protection B
HMIS	Health hazards 2	Flammability 0	Physical hazards 0	

Issue Date 05-Nov-2018

Revision Date 16-May-2018

Revision Note
No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the

date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet