

1. PRODUCT AND COMPANY IDENTIFICATION**Product identifier****Product Name** Ink & Graffiti Remover**Other means of identification****Product Code** 670285
Synonyms None**Details of the supplier of the safety data sheet****Company Name** Global Industrial
2505 Mill Center Parkway
Buford GA 30518
(516) 608-3000**Emergency telephone number****Emergency Telephone** Chemtrec (US & Canada) 800-424-9300
Chemtrec (outside US & Canada) 703-527-3887**2. HAZARDS IDENTIFICATION****Classification****OSHA Regulatory Status**

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Category 5
Acute toxicity - Dermal	Category 5
Acute toxicity - Inhalation (Dusts/Mists)	Category 4
Serious eye damage/eye irritation	Category 2
Flammable liquids	Category 4

Label elements**Emergency Overview****Warning****Hazard statements**May be harmful if swallowed
May be harmful in contact with skin
Harmful if inhaled
Causes serious eye irritation
Combustible liquid**Appearance** Clear**Physical state** Liquid**Odor** Solvent

Precautionary Statements - Prevention

Use in a well-ventilated area

Avoid breathing dust/fume/gas/mist/vapors/spray

Wash face, hands and any exposed skin thoroughly after handling

Wear protective gloves/protective clothing/eye protection/face protection

Keep away from heat/sparks/open flames/hot surfaces. — No smoking

Precautionary Statements - Response

Call a POISON CENTER or doctor/physician if you feel unwell

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

If eye irritation persists: Get medical advice/attention

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Drink plenty of water

Immediately call a POISON CENTER or doctor/physician

Precautionary Statements - Disposal

Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)**Other Information**

- Harmful to aquatic life with long lasting effects
- Harmful to aquatic life

Unknown Acute Toxicity

0% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Benzyl Alcohol	100-51-6	15-40	*
2-Propanol	67-63-0	10-30	*
Orange Terpenes	5989-27-5	.1-1	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures**General advice**

If symptoms persist, call a physician. Do not breathe dust/fume/gas/mist/vapors/spray. Do not get in eyes, on skin, or on clothing.

Skin Contact

Consult a physician if necessary. Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Immediate medical attention is not required. If skin irritation persists, call a physician.

Eye contact

Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Keep eye wide open while rinsing. If symptoms persist, call a physician.

Inhalation

Remove to fresh air. Call a physician. If breathing is irregular or stopped, administer artificial respiration. Avoid direct contact with skin. Use barrier to give mouth-to-mouth resuscitation. Immediate medical attention is not required. If symptoms persist, call a physician. Move to fresh air in case of accidental inhalation of vapors or decomposition products.

Ingestion

Rinse mouth. Drink plenty of water. If symptoms persist, call a physician. Do NOT induce vomiting. Never give anything by mouth to an unconscious person.

Self-protection of the first aider

Use personal protective equipment as required.

Most important symptoms and effects, both acute and delayed

Symptoms Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES**Suitable extinguishing media**

Use. Dry chemical. Carbon dioxide (CO₂). Water spray (fog). Alcohol resistant foam.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

Keep product and empty container away from heat and sources of ignition. Risk of ignition.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES**Personal precautions, protective equipment and emergency procedures**

Personal precautions Use personal protective equipment as required. Remove all sources of ignition. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Pay attention to flashback. Take precautionary measures against static discharges.

Environmental precautions

Environmental precautions Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Cover liquid spill with sand, earth or other non-combustible absorbent material. Cover powder spill with plastic sheet or tarp to minimize spreading. Pick up and transfer to properly labeled containers. Soak up with inert absorbent material. Dam up. Take precautionary measures against static discharges.

7. HANDLING AND STORAGE**Precautions for safe handling**

Advice on safe handling Avoid contact with skin, eyes or clothing. Use personal protective equipment as required. Wash contaminated clothing before reuse. Do not breathe dust/fume/gas/mist/vapors/spray. Do not eat, drink or smoke when using this product. Use with local exhaust ventilation. All equipment used when handling the product must be grounded. Keep away from heat/sparks/open flames/hot surfaces. — No smoking. Take necessary action to avoid static electricity discharge (which might cause ignition of organic vapors).

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep container tightly closed in a dry and well-ventilated place. Keep out of the reach of children. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). Keep containers tightly closed in a cool, well-ventilated place. Keep away from heat. Keep in properly labeled containers.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
2-Propanol 67-63-0	STEL: 400 ppm TWA: 200 ppm	TWA: 400 ppm TWA: 980 mg/m ³ (vacated) TWA: 400 ppm (vacated) TWA: 980 mg/m ³ (vacated) STEL: 500 ppm (vacated) STEL: 1225 mg/m ³	IDLH: 2000 ppm TWA: 400 ppm TWA: 980 mg/m ³ STEL: 500 ppm STEL: 1225 mg/m ³
2-Ethyl Hexanol 104-76-7	TWA: 50 ppm S*	(vacated) TWA: 50 ppm (vacated) TWA: 270 mg/m ³ (vacated) S*	TWA: 50 ppm TWA: 270 mg/m ³
Ethanol 64-17-5	STEL: 1000 ppm	TWA: 1000 ppm TWA: 1900 mg/m ³ (vacated) TWA: 1000 ppm (vacated) TWA: 1900 mg/m ³	IDLH: 3300 ppm TWA: 1000 ppm TWA: 1900 mg/m ³

NIOSH IDLH Immediately Dangerous to Life or Health

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Tight sealing safety goggles.

Skin and body protection Wear protective gloves and protective clothing. Rubber gloves if prolonged contact and/or handling large volumes.

Respiratory protection Ensure adequate ventilation, especially in confined areas. If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators or air purifying respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Handle in accordance with good industrial hygiene and safety practice. When using do not eat, drink or smoke. Regular cleaning of equipment, work area and clothing is recommended. Wear suitable gloves and eye/face protection.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Liquid
Appearance Clear
Color Colorless
Odor Solvent
Odor threshold No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	9.5 - 10.5	
Specific Gravity	1.0	

Viscosity	Water Thin
Melting point/freezing point	No Information available
Flash point	84 °C 184 °F
Boiling point / boiling range	100 °C / 212 ° F Degrees /
Evaporation rate	No Information available
Flammability (solid, gas)	No data available
Flammability Limits in Air	
Upper flammability limit:	No Information available
Lower flammability limit:	No Information available
Vapor pressure	No Information available
Vapor density	No Information available
Water solubility	Complete
Partition coefficient	No Information available
Autoignition temperature	No Information available
Decomposition temperature	No Information available

Other Information

Density Lbs/Gal	8.34
VOC Content (%)	55.88

10. STABILITY AND REACTIVITY**Reactivity**

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Heat, flames and sparks.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure****Product Information**

Inhalation	Harmful by inhalation. Inhalation of vapors in high concentration may cause irritation of respiratory system.
Eye contact	Avoid contact with eyes. Direct contact may cause serious eye irritation.
Skin Contact	May be harmful in contact with skin. May cause irritation or burns to the skin. Prolonged or repeated contact may cause absorption to the skin.
Ingestion	May be harmful if swallowed. Ingestion may cause irritation to mucous membranes. Ingestion may result in the absorption of potentially harmful amounts leading to possible liver and kidney damage.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Benzyl Alcohol 100-51-6	= 1230 mg/kg (Rat)	= 2 g/kg (Rabbit)	= 8.8 mg/L (Rat) 4 h
2-Propanol 67-63-0	= 1870 mg/kg (Rat)	= 4059 mg/kg (Rabbit)	= 72600 mg/m ³ (Rat) 4 h

Orange Terpenes 5989-27-5	= 4400 mg/kg (Rat) = 5200 mg/kg (Rat) = 5300 mg/kg (Rat)	> 5 g/kg (Rabbit)	-
------------------------------	---	---------------------	---

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No Information available.
Germ cell mutagenicity No Information available.
Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen. Ethanol has been shown to be carcinogenic in long-term studies only when consumed as alcoholic beverage.

Chemical Name	ACGIH	IARC	NTP	OSHA
2-Propanol 67-63-0	-	Group 3	-	X
Orange Terpenes 5989-27-5	-	Group 3	-	X

IARC (International Agency for Research on Cancer)

Group 3 -Not classifiable as a human carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity No Information available.
STOT - single exposure No Information available.
STOT - repeated exposure No Information available.
Chronic toxicity Ethanol has been shown to be a reproductive toxin only when consumed as an alcoholic beverage. Ethanol has been shown to be carcinogenic in long-term studies only when consumed as alcoholic beverage.
Target organ effects EYES, Respiratory system, Skin.
Aspiration hazard No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral) 2,879.00
ATEmix (dermal) 4,984.00
ATEmix (inhalation-dust/mist) 4.40

12. ECOLOGICAL INFORMATION**Ecotoxicity**

2.35% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Benzyl Alcohol 100-51-6	35: 3 h Anabaena variabilis mg/L EC50	460: 96 h Pimephales promelas mg/L LC50 static 10: 96 h Lepomis macrochirus mg/L LC50 static	23: 48 h water flea mg/L EC50
2-Propanol 67-63-0	1000: 96 h Desmodemus subspicatus mg/L EC50 1000: 72 h Desmodemus subspicatus mg/L EC50	9640: 96 h Pimephales promelas mg/L LC50 flow-through 1400000: 96 h Lepomis macrochirus µg/L LC50 11130: 96 h Pimephales promelas mg/L LC50 static	13299: 48 h Daphnia magna mg/L EC50
2-(2-ethoxyethoxy)ethanol 111-90-0	-	10000: 96 h Lepomis macrochirus mg/L LC50 static 19100 - 23900: 96 h Lepomis macrochirus mg/L LC50 flow-through 11400 - 15700: 96 h Oncorhynchus mykiss mg/L LC50 flow-through 11600 - 16700: 96 h Pimephales promelas mg/L LC50 flow-through 13400: 96 h Salmo gairdneri mg/L LC50 flow-through	3940 - 4670: 48 h Daphnia magna mg/L EC50
Propylene Glycol 57-55-6	19000: 96 h Pseudokirchneriella subcapitata mg/L EC50	41 - 47: 96 h Oncorhynchus mykiss mL/L LC50 static 51600: 96 h	1000: 48 h Daphnia magna mg/L EC50 Static 10000: 24 h Daphnia

		Oncorhynchus mykiss mg/L LC50 static 51400: 96 h Pimephales promelas mg/L LC50 static 710: 96 h Pimephales promelas mg/L LC50	magna mg/L EC50
Diethylhexyl Sodium Sulfosuccinate 577-11-7	-	20 - 40: 96 h Oncorhynchus mykiss mg/L LC50 semi-static 24: 96 h Oncorhynchus mykiss mg/L LC50 static 37: 96 h Lepomis macrochirus mg/L LC50 static	36: 48 h Daphnia magna mg/L EC50
Sodium Dodecylbenzene Sulfonate 25155-30-0	-	10.8: 96 h Oncorhynchus mykiss mg/L LC50 static	-
Orange Terpenes 5989-27-5	-	0.619 - 0.796: 96 h Pimephales promelas mg/L LC50 flow-through 35: 96 h Oncorhynchus mykiss mg/L LC50	-
2-Ethyl Hexanol 104-76-7	8.5: 168 h Scenedesmus quadricauda mg/L EC50 2.7: 96 h Pseudokirchneriella subcapitata mg/L EC50 11.5: 72 h Desmodemus subspicatus mg/L EC50	5000: 48 h Leuciscus idus mg/L LC50 0.056 - 7.5: 96 h Oncorhynchus mykiss mg/L LC50 static 28.7: 96 h Lepomis macrochirus mg/L LC50 static 4.78 - 8.85: 96 h Oncorhynchus mykiss mg/L LC50 static 3.6 - 5.1: 96 h Lepomis macrochirus mg/L LC50 static 32 - 37: 96 h Oncorhynchus mykiss mg/L LC50 static 7.5: 96 h Oncorhynchus mykiss mg/L LC50 29.7: 96 h Pimephales promelas mg/L LC50 static 10.0 - 33.0: 96 h Lepomis macrochirus mg/L LC50 static 27 - 29.5: 96 h Pimephales promelas mg/L LC50 flow-through	4.78 - 8.87: 48 h Daphnia magna mg/L EC50 Static 31.8: 48 h Daphnia magna mg/L EC50 320: 48 h Daphnia magna mg/L EC50 39: 48 h Daphnia magna mg/L EC50 8.5: 48 h Daphnia magna mg/L EC50
Benzaldehyde 100-52-7	-	10.6 - 11.8: 96 h Oncorhynchus mykiss mg/L LC50 flow-through 12.69: 96 h Oncorhynchus mykiss mg/L LC50 static 6.8 - 8.53: 96 h Pimephales promelas mg/L LC50 flow-through 0.8 - 1.44: 96 h Lepomis macrochirus mg/L LC50 flow-through 7.5: 96 h Lepomis macrochirus mg/L LC50 static	50: 24 h Daphnia magna mg/L EC50
Sodium Sulfate 7757-82-6	-	3040 - 4380: 96 h Lepomis macrochirus mg/L LC50 static 13500: 96 h Lepomis macrochirus mg/L LC50 13500 - 14500: 96 h Pimephales promelas mg/L LC50 6800: 96 h Pimephales promelas mg/L LC50 static	2564: 48 h Daphnia magna mg/L EC50 630: 96 h Daphnia magna mg/L EC50
Ethanol 64-17-5	-	12.0 - 16.0: 96 h Oncorhynchus mykiss mL/L LC50 static 100: 96 h Pimephales promelas mg/L LC50 static 13400 - 15100: 96 h Pimephales promelas mg/L LC50 flow-through	9268 - 14221: 48 h Daphnia magna mg/L LC50 10800: 24 h Daphnia magna mg/L EC50 2: 48 h Daphnia magna mg/L EC50 Static
Sodium Chloride 7647-14-5	-	5560 - 6080: 96 h Lepomis macrochirus mg/L LC50 flow-through 12946: 96 h Lepomis macrochirus mg/L LC50 static 6020 - 7070: 96 h Pimephales promelas mg/L LC50 static 7050: 96 h Pimephales promelas mg/L LC50 semi-static 4747 - 7824: 96 h Oncorhynchus mykiss mg/L LC50 flow-through 6420 - 6700: 96 h Pimephales promelas mg/L LC50 static	340.7 - 469.2: 48 h Daphnia magna mg/L EC50 Static 1000: 48 h Daphnia magna mg/L EC50

Persistence and degradability

No Information available.

Bioaccumulation

Bioaccumulative potential.

Chemical Name	Partition coefficient
Benzyl Alcohol 100-51-6	1.1
2-Propanol 67-63-0	0.05

Other adverse effects No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste Status
2-Propanol 67-63-0	Toxic Ignitable
Orange Terpenes 5989-27-5	Toxic

14. TRANSPORT INFORMATION

The shipping classification information in this section (Section 14) is meant as a guide to the overall classification of the product. However, transportation classifications may be subject to change with changes in package size. Consult shipper requirements under 49 CFR, IATA and IMDG to assure regulatory compliance.

DOT Not regulated

TDG Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
DSL/NDSL Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
2-Propanol - 67-63-0	1.0
2-(2-ethoxyethoxy)ethanol - 111-90-0	1.0

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	Yes
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

US State Regulations**California Proposition 65**

This product has been evaluated and does not require warning labeling under California Proposition 65.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Benzyl Alcohol 100-51-6	-	X	X
2-Propanol 67-63-0	X	X	X
2-(2-ethoxyethoxy)ethanol 111-90-0	X	-	X
Propylene Glycol 57-55-6	X	-	X
Sodium Dodecylbenzene Sulfonate 25155-30-0	X	X	X
Orange Terpenes 5989-27-5	X	-	-
2-Ethyl Hexanol 104-76-7	X	X	X
Benzaldehyde 100-52-7	X	X	X
Sodium Sulfate 7757-82-6	-	X	X
Ethanol 64-17-5	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 1	Flammability 2	Instability 0	Physical and Chemical Properties - Personal protection B
HMIS	Health hazards 1	Flammability 2	Physical hazards 0	

Issue Date 30-Oct-2018

Revision Date 07-Feb-2018

Revision Note

No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet