



GLOBALTM INDUSTRIAL

Forklift Blue Arrow Light - Standard

Models
800503 & 800505

Technical Specifications:

- [LED] 2PCS Cree high power LEDs, 3W/LED
- Power: 6W
- Lux strength: 400LUX
- Voltage: 10~80V DC
- Color: Blue
- Life Time: >50000 Hours
- Working Temperature: -49 ~185°F
- Double insulated silicon rubberized wire, can bear very low&high temperature
- Reverse polarity protected
- Certificate: IP68, CE, ROHS

CAUTION: Follow safety precautions below prior to installation and use. Failure to observe instructions could result in item damage, severe personal injury, and/or property damage. For additional questions or concerns, contact Global Industrial Customer Service at 1-800-645-2986 or visit www.globalindustrial.com.

- To properly install this work light, you must have good understanding of automotive electrical procedures and systems, along with proficiency in the installation and use of safety warning equipment.

- When drilling into a vehicle structure, be sure that both sides of the surface are clear of anything that could be damaged.

- DO NOT install equipment or route wiring or cord in the deployment path of an air bag.

- You should frequently inspect the light to ensure that it is operating properly.

- This product contains high intensity LED devices. To prevent eyes damage, DO NOT stare into the light beam at close range.

- Connect light wire to vehicle battery, black wire connect to negative pole, Red wire connect to positive pole.

- Must fit a switch on the wire. Otherwise, the light will remain on.