

## 1. PRODUCT AND COMPANY IDENTIFICATION

**Product identifier**

**Product Name** Floor Cleaner & Deodorizer

**Other means of identification**

**Product Code** 640404-641608  
**Synonyms** None

**Details of the supplier of the safety data sheet**

**Company Name** Global Industrial  
2505 Mill Center Parkway  
Buford GA 30518  
(888) 978-7759

**Emergency telephone number**

**Emergency Telephone** Chemtrec (US & Canada) 800-424-9300  
Chemtrec (outside US & Canada) 703-527-3887

## 2. HAZARDS IDENTIFICATION

**Classification**

**OSHA Regulatory Status**

This product has been classified in accordance with the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

|                         |                |
|-------------------------|----------------|
| Acute toxicity - Oral   | Not classified |
| Acute toxicity - Dermal | Not classified |

**Label elements**

### Emergency Overview

**Appearance** Clear Purple

**Physical state** Liquid

**Odor** Lavender

**Precautionary Statements - Prevention**

Wash hands thoroughly after handling

**Precautionary Statements - Response**

Specific Treatment (See Section 4 on the SDS)  
IF ON SKIN: Wash with plenty of soap and water  
If skin irritation or rash occurs: Get medical advice/attention  
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing  
Call a POISON CENTER or doctor/physician if you feel unwell  
IF SWALLOWED: Rinse mouth. DO NOT induce vomiting  
Drink plenty of water  
Immediately call a POISON CENTER or doctor/physician

**Precautionary Statements - Disposal**

Disposal should be in accordance with applicable regional, national and local laws and regulations

**Hazards not otherwise classified (HNOC)**

**Other Information**

- Harmful to aquatic life with long lasting effects

• Harmful to aquatic life

Unknown Acute Toxicity

0% of the mixture consists of ingredient(s) of unknown toxicity

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

| Chemical Name    | CAS No.     | Weight-% | Trade Secret |
|------------------|-------------|----------|--------------|
| Surfactant Blend | Proprietary | 1-5      | *            |

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

### 4. FIRST AID MEASURES

#### First aid measures

|   |   |
|---|---|
| <b>Skin Contact</b>                       | Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.               |
| <b>Eye contact</b>                        | Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If symptoms persist, call a physician. |
| <b>Inhalation</b>                         | Remove to fresh air. If symptoms persist, call a physician.   |
| <b>Ingestion</b>                          | Do NOT induce vomiting. Drink plenty of water. Immediate medical attention is not required. Rinse mouth.                        |
| <b>Self-protection of the first aider</b> | Use personal protective equipment as required.  |

#### Most important symptoms and effects, both acute and delayed

**Symptoms** Any additional important symptoms and effects are described in Section 11: Toxicology Information.

#### Indication of any immediate medical attention and special treatment needed

**Note to physicians** May cause sensitization of susceptible persons.

### 5. FIRE-FIGHTING MEASURES

#### Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

#### Specific hazards arising from the chemical

In the event of fire and/or explosion do not breathe fumes. May cause sensitization by inhalation and skin contact. Thermal decomposition can lead to release of irritating and toxic gases and vapors.

#### Explosion data

**Sensitivity to Mechanical Impact** None.

**Sensitivity to Static Discharge** None.

#### Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

### 6. ACCIDENTAL RELEASE MEASURES

#### Personal precautions, protective equipment and emergency procedures

**Personal precautions** Use personal protective equipment as required. Avoid contact with eyes and skin.

**Environmental precautions**

**Environmental precautions** Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

**Methods and material for containment and cleaning up**

**Methods for containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Soak up with inert absorbent material. Pick up and transfer to properly labeled containers. After cleaning, flush away traces with water. Prevent product from entering drains.

**7. HANDLING AND STORAGE****Precautions for safe handling**

**Advice on safe handling** Ensure adequate ventilation, especially in confined areas. Use personal protective equipment as required.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep out of the reach of children. Keep container tightly closed. Keep containers tightly closed in a cool, well-ventilated place.

**Incompatible materials** None known based on information supplied.

**8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control parameters****Appropriate engineering controls**

**Engineering Controls** Showers, Eyewash stations & Ventilation systems.

**Individual protection measures, such as personal protective equipment**

**Eye/face protection** Safety glasses or chemical splash goggles.

**Skin and body protection** Rubber gloves.

**Respiratory protection** Ensure adequate ventilation, especially in confined areas. In case of inadequate ventilation wear respiratory protection.

**General Hygiene** When using do not eat, drink or smoke. Wash contaminated clothing before reuse.

**9. PHYSICAL AND CHEMICAL PROPERTIES****Information on basic physical and chemical properties**

**Physical state** Liquid  
**Appearance** Clear Purple  
**Color** Purple  
**Odor** Lavender  
**Odor threshold** No Information available

| <b><u>Property</u></b>        | <b><u>Values</u></b>     | <b><u>Remarks • Method</u></b> |
|-------------------------------|--------------------------|--------------------------------|
| pH                            | 6.0 - 8.0                |                                |
| Specific Gravity              | 1.0                      |                                |
| Viscosity                     | < 25 cP @ 25°C           |                                |
| Melting point/freezing point  | No Information available |                                |
| Flash point                   | None                     |                                |
| Boiling point / boiling range | 100 °C / 212 ° F Degrees |                                |

|                            |                          |
|----------------------------|--------------------------|
| Evaporation rate           | No Information available |
| Flammability (solid, gas)  | No data available        |
| Flammability Limits in Air |                          |
| Upper flammability limit:  | No Information available |
| Lower flammability limit:  | No Information available |
| Vapor pressure             | No Information available |
| Vapor density              | No Information available |
| Water solubility           | Complete                 |
| Partition coefficient      | No Information available |
| Autoignition temperature   | No Information available |
| Decomposition temperature  | No Information available |

**Other Information**

|                 |      |
|-----------------|------|
| Density Lbs/Gal | 8.33 |
| VOC Content (%) | 0%   |

**10. STABILITY AND REACTIVITY****Reactivity**

No data available

**Chemical stability**

Stable under recommended storage conditions.

**Possibility of Hazardous Reactions**

None under normal processing.

**Conditions to avoid**

Extremes of temperature and direct sunlight.

**Incompatible materials**

None known based on information supplied.

**Hazardous Decomposition Products**

None known based on information supplied.

**11. TOXICOLOGICAL INFORMATION****Information on likely routes of exposure****Product Information**

|                     |   |
|---------------------|---|
| <b>Inhalation</b>   | Avoid breathing vapors or mists. May cause irritation of respiratory tract.               |
| <b>Eye contact</b>  | Avoid contact with eyes. May cause irritation.  |
| <b>Skin Contact</b> | Avoid contact with skin. Prolonged or repeated contact may dry skin and cause irritation. |
| <b>Ingestion</b>    | Do not taste or swallow. May cause gastro intestinal irritation.                          |

| Chemical Name    | Oral LD50            | Dermal LD50          | Inhalation LC50 |
|------------------|----------------------|----------------------|-----------------|
| Surfactant Blend | > 2000 mg/kg ( Rat ) | > 2000 mg/kg ( Rat ) | -               |

**Information on toxicological effects**

**Symptoms** No Information available.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

**Sensitization** No Information available.  
**Germ cell mutagenicity** No Information available.  
**Carcinogenicity** No Information available.

|                                 |   |
|---------------------------------|---|
| <b>Reproductive toxicity</b>    | No Information available.   |
| <b>STOT - single exposure</b>   | No Information available.   |
| <b>STOT - repeated exposure</b> | No Information available.   |
| <b>Chronic toxicity</b>         | Repeated contact may cause allergic reactions in very susceptible persons. Avoid repeated exposure. |
| <b>Aspiration hazard</b>        | No Information available.   |

**Numerical measures of toxicity - Product Information**

**Unknown Acute Toxicity** 0% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

|                        |           |
|------------------------|-----------|
| <b>ATEmix (oral)</b>   | 66,667.00 |
| <b>ATEmix (dermal)</b> | 66,667.00 |

**12. ECOLOGICAL INFORMATION****Ecotoxicity**

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment

| <b>Chemical Name</b> | <b>Algae/aquatic plants</b> | <b>Fish</b>                                | <b>Crustacea</b>            |
|----------------------|-----------------------------|--|-----------------------------|
| Surfactant Blend     | -                           | 1.2: 96 h Oncorhynchus mykiss<br>mg/L LC50 | 5.3: 48 h Daphnia mg/L LC50 |

**Persistence and degradability**

No Information available.

**Bioaccumulation**

No Information available.

**Other adverse effects**

No Information available

**13. DISPOSAL CONSIDERATIONS****Waste treatment methods**

|                               |   |
|-------------------------------|---|
| <b>Disposal of wastes</b>     | Disposal should be in accordance with applicable regional, national and local laws and regulations. |
| <b>Contaminated packaging</b> | Do not reuse container.   |

This product contains one or more substances that are listed with the State of California as a hazardous waste.

**14. TRANSPORT INFORMATION**

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

**DOT** Not regulated

**TDG** Not regulated

**15. REGULATORY INFORMATION****International Inventories**

|                 |          |
|-----------------|----------|
| <b>TSCA</b>     | Complies |
| <b>DSL/NDSL</b> | Complies |

**Legend:**

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory  
**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**US Federal Regulations****SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

**SARA 311/312 Hazard Categories**

|  |     |
|--|-----|
| <b>Acute health hazard</b>               | Yes |
| <b>Chronic Health Hazard</b>             | No  |
| <b>Fire hazard</b>                       | No  |
| <b>Sudden release of pressure hazard</b> | No  |
| <b>Reactive Hazard</b>                   | No  |

**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

**US State Regulations****California Proposition 65**

This product has been evaluated and does not require warning labeling under California Proposition 65.

**U.S. State Right-to-Know Regulations****U.S. EPA Label Information**

**EPA Pesticide Registration Number** Not Applicable

|                              |
|------------------------------|
| <b>16. OTHER INFORMATION</b> |
|------------------------------|

|                    |                         |                       |                           |   |
|--------------------|-------------------------|-----------------------|---------------------------|---|
| <b><u>NFPA</u></b> | <b>Health hazards</b> 2 | <b>Flammability</b> 0 | <b>Instability</b> 0      | <b>Physical and Chemical Properties</b> - |
| <b><u>HMIS</u></b> | <b>Health hazards</b> 2 | <b>Flammability</b> 0 | <b>Physical hazards</b> 0 | <b>Personal protection</b> B              |

**Issue Date** 08-Mar-2018

**Revision Date** 06-Mar-2018

**Revision Note**

No Information available

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**