

**1. PRODUCT AND COMPANY IDENTIFICATION****Product identifier****Product Name** Calcium & Lime Remover**Other means of identification****Product Code** 670292**Synonyms** None**Details of the supplier of the safety data sheet****Company Name** Global Industrial  
2505 Mill Center Parkway  
Buford GA 30518  
(516) 608-3000**Emergency telephone number****Emergency Telephone** Chemtrec (US & Canada) 800-424-9300  
Chemtrec (outside US & Canada) 703-527-3887**2. HAZARDS IDENTIFICATION****Classification****OSHA Regulatory Status**

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Skin corrosion/irritation	Category 3

**Label elements****Emergency Overview****Warning****Hazard statements**

Causes mild skin irritation

**Appearance** Clear**Physical state** Liquid**Odor** Fresh & Clean**Precautionary Statements - Response**

Specific Treatment (See Section 4 on the SDS)

If skin irritation occurs: Get medical advice/attention

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Drink plenty of water

Immediately call a POISON CENTER or doctor/physician

**Precautionary Statements - Disposal**

Disposal should be in accordance with applicable regional, national and local laws and regulations

**Hazards not otherwise classified (HNOC)**

**Other Information**

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

**3. COMPOSITION/INFORMATION ON INGREDIENTS**

Chemical Name	CAS No.	Weight-%	Trade Secret
2-Hydroxypropanoic acid	79-33-4	10-30	*
Surfactant Blend	Proprietary	1-5	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

**4. FIRST AID MEASURES****First aid measures**

**Skin Contact** Wash off immediately with soap and plenty of water. If skin irritation persists, call a physician.

**Eye contact** Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

**Inhalation** Remove to fresh air.

**Ingestion** Clean mouth with water and drink afterwards plenty of water.

**Most important symptoms and effects, both acute and delayed**

**Symptoms** Any additional important symptoms and effects are described in Section 11: Toxicology Information.

**Indication of any immediate medical attention and special treatment needed**

**Note to physicians** Treat symptomatically.

**5. FIRE-FIGHTING MEASURES****Suitable extinguishing media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

**Specific hazards arising from the chemical**

No Information available.

**Explosion data**

**Sensitivity to Mechanical Impact** None.

**Sensitivity to Static Discharge** None.

**Protective equipment and precautions for firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**6. ACCIDENTAL RELEASE MEASURES****Personal precautions, protective equipment and emergency procedures**

**Personal precautions** Ensure adequate ventilation, especially in confined areas.

**Environmental precautions**

**Environmental precautions** Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other

surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

#### **Methods and material for containment and cleaning up**

**Methods for containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Pick up and transfer to properly labeled containers.

### **7. HANDLING AND STORAGE**

#### **Precautions for safe handling**

**Advice on safe handling** Handle in accordance with good industrial hygiene and safety practice.

#### **Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place.

**Incompatible materials** None known based on information supplied.

### **8. EXPOSURE CONTROLS/PERSONAL PROTECTION**

#### **Control parameters**

#### **Appropriate engineering controls**

**Engineering Controls** Showers, Eyewash stations & Ventilation systems.

#### **Individual protection measures, such as personal protective equipment**

**Eye/face protection** Wear safety glasses with side shields (or goggles).

**Skin and body protection** Rubber gloves if prolonged contact and/or handling large volumes.

**Respiratory protection** Ensure adequate ventilation, especially in confined areas. If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators or air purifying respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

**General Hygiene** Handle in accordance with good industrial hygiene and safety practice.

### **9. PHYSICAL AND CHEMICAL PROPERTIES**

#### **Information on basic physical and chemical properties**

<b>Physical state</b>	Liquid
<b>Appearance</b>	Clear
<b>Color</b>	Colorless
<b>Odor</b>	Fresh & Clean
<b>Odor threshold</b>	No Information available

<b><u>Property</u></b>	<b><u>Values</u></b>	<b><u>Remarks • Method</u></b>
pH	2.0 - 2.5	
Specific Gravity	1.03	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	Above 200°F	
Boiling point / boiling range	> 212 °F	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		

<b>Upper flammability limit:</b>	No Information available
<b>Lower flammability limit:</b>	No Information available
<b>Vapor pressure</b>	No Information available
<b>Vapor density</b>	No Information available
<b>Water solubility</b>	Complete
<b>Partition coefficient</b>	No Information available
<b>Autoignition temperature</b>	No Information available
<b>Decomposition temperature</b>	No Information available

**Other Information**

<b>Density Lbs/Gal</b>	8.56
<b>VOC Content (%)</b>	Not Applicable

**10. STABILITY AND REACTIVITY****Reactivity**

No data available

**Chemical stability**

Stable under recommended storage conditions.

**Possibility of Hazardous Reactions**

None under normal processing.

**Conditions to avoid**

Extremes of temperature and direct sunlight.

**Incompatible materials**

None known based on information supplied.

**Hazardous Decomposition Products**

None known based on information supplied.

**11. TOXICOLOGICAL INFORMATION****Information on likely routes of exposure****Product Information**

<b>Inhalation</b>	Inhalation of vapors in high concentration may cause irritation of respiratory system. Breathing of vapors may cause dizziness and shortness of breath.
<b>Eye contact</b>	Avoid contact with eyes. Contact with eyes may cause irritation.
<b>Skin Contact</b>	Avoid contact with skin. Causes mild skin irritation.
<b>Ingestion</b>	Do not taste or swallow. May cause stomach distress, nausea, or vomiting.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
2-Hydroxypropanoic acid 79-33-4	= 3730 mg/kg ( Rat ) = 3543 mg/kg ( Rat )	> 2000 mg/kg ( Rabbit ) > 2 g/kg ( Rabbit )	> 7.94 mg/L ( Rat ) 4 h
Surfactant Blend	2546 mg/kg ( Rat )	1844 mg/kg ( Rat )	-

**Information on toxicological effects**

**Symptoms** No Information available.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

<b>Irritation</b>	MAY CAUSE SKIN IRRITATION.
<b>Sensitization</b>	No Information available.
<b>Germ cell mutagenicity</b>	No Information available.

<b>Carcinogenicity</b>	No Information available.
<b>Reproductive toxicity</b>	No Information available.
<b>STOT - single exposure</b>	No Information available.
<b>STOT - repeated exposure</b>	No Information available.
<b>Aspiration hazard</b>	No Information available.

**Numerical measures of toxicity - Product Information**

**Unknown Acute Toxicity** 0% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

<b>ATEmix (dermal)</b>	13,024.00
<b>ATEmix (inhalation-dust/mist)</b>	60.21

**12. ECOLOGICAL INFORMATION****Ecotoxicity**

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-Hydroxypropanoic acid 79-33-4	3.5: 70 h Pseudokirchneriella subcapitata mg/L EC50	320: 96 h Brachydanio rerio mg/L LC50 semi-static 100 - 180: 96 h Lepomis macrochirus mg/L LC50 static 100 - 180: 96 h Oncorhynchus mykiss mg/L LC50 static	180 - 320: 48 h Daphnia magna mg/L EC50 Static 240: 48 h Daphnia magna mg/L EC50
Surfactant Blend	-	32.15: 96 h Rainbow Trout mg/L LC50	-
Trisodium Citrate Dihydrate 6132-04-3	18000 - 32000: 96 h Chlorella vulgaris mg/L EC50	18000 - 32000: 96 h Poecilia reticulata mg/L LC50	5600 - 10000: 48 h Daphnia magna mg/L EC50

**Persistence and degradability**

No Information available.

**Bioaccumulation**

Bioaccumulative potential.

Chemical Name	Partition coefficient
2-Hydroxypropanoic acid 79-33-4	-0.62

**Other adverse effects** No Information available

**13. DISPOSAL CONSIDERATIONS****Waste treatment methods**

**Disposal of wastes** Disposal should be in accordance with applicable regional, national and local laws and regulations.

**Contaminated packaging** Do not reuse container.

**14. TRANSPORT INFORMATION**

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

**DOT** Not regulated

**TDG** Not regulated

## 15. REGULATORY INFORMATION

### International Inventories

TSCA Complies  
DSL/NDSL Complies

### Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory  
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

### US Federal Regulations

#### SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

#### SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

#### CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

#### CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

### US State Regulations

#### California Proposition 65

This product has been evaluated and does not require warning labeling under California Proposition 65.

### U.S. State Right-to-Know Regulations

### U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

## 16. OTHER INFORMATION

<u>NFPA</u>	Health hazards 0	Flammability 0	Instability 0	Physical and Chemical Properties -
<u>HMIS</u>	Health hazards 0	Flammability 0	Physical hazards 0	Personal protection B

Issue Date 09-Nov-2018

Revision Date 12-Jan-2018

#### Revision Note

No Information available

#### Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information

relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**