

Issue Date 08-Jan-2015

Revision Date 08-Jan-2015

Version 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name Foam Hand Soap

Other means of identification

Product Code 640411

Synonyms None

Details of the supplier of the safety data sheet

Company Name Global Industrial
2505 Mill Center Parkway, Buford, GA 30518
(888) 978-7759

Emergency telephone number

Emergency Telephone Chemtrec (US & Canada) 800-424-9300
Chemtrec (outside US & Canada) 703-527-3887

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified

Label elements

Emergency Overview

Hazard statements

Harmful to aquatic life with long lasting effects

Appearance Clear Reddish-Orange

Physical state Liquid

Odor Fresh & Clean

Precautionary Statements - Prevention

Avoid release to the environment

Precautionary Statements - Response

Specific Treatment (See Section 4 on the SDS)

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Other Information

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
4-Chloro-3,5-dimethylphenol	88-04-0	.1-1	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

Skin Contact	Wash skin with soap and water.
Eye contact	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
Inhalation	Remove to fresh air.
Ingestion	Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed

Symptoms	Any additional important symptoms and effects are described in Section 11: Toxicology Information.
-----------------	--

Indication of any immediate medical attention and special treatment needed

Note to physicians	Treat symptomatically.
---------------------------	------------------------

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No Information available.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Ensure adequate ventilation, especially in confined areas.
-----------------------------	--

Environmental precautions

Environmental precautions	See Section 12 for additional ecological information.
----------------------------------	---

Methods and material for containment and cleaning up

Methods for containment	Prevent further leakage or spillage if safe to do so.
Methods for cleaning up	Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters**Exposure Guidelines**

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Formaldehyde 50-00-0	Ceiling: 0.3 ppm	TWA: 0.75 ppm (vacated) TWA: 3 ppm unless specified in 1910.1048 (vacated) STEL: 10 ppm 30 min unless specified in 1910.1048 (vacated) Ceiling: 5 ppm unless specified in 1910.1048 STEL: 2 ppm see 29 CFR 1910.1048	IDLH: 20 ppm Ceiling: 0.1 ppm 15 min TWA: 0.016 ppm

NIOSH IDLH Immediately Dangerous to Life or Health

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses if handling large volume.

Skin and body protection No special technical protective measures are necessary.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Liquid
Appearance Clear Reddish-Orange
Color Reddish-Orange
Odor Fresh & Clean
Odor threshold No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	7.0 - 9.0	
Specific Gravity	1.00	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	None	

Boiling point / boiling range	212 °F
Evaporation rate	No Information available
Flammability (solid, gas)	
Flammability Limits in Air	
Upper flammability limit:	Not Applicable
Lower flammability limit:	Not Applicable
Vapor pressure	No Information available
Vapor density	No Information available
Water solubility	Complete
Partition coefficient	No Information available
Autoignition temperature	No Information available
Decomposition temperature	No Information available

Other Information

Density Lbs/Gal	8.33
VOC Content (%)	0.003

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Extremes of temperature and direct sunlight.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information	Maybe harmful by inhalation, ingestion and in contact with eyes.
Inhalation	Inhalation of vapors in high concentration may cause irritation of respiratory system.
Eye contact	Contact with eyes may cause irritation or burns.
Skin Contact	Repeated or prolonged skin contact may cause allergic reactions with susceptible persons.
Ingestion	May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Formaldehyde 50-00-0	= 600 mg/kg (Rat)	= 270 mg/kg (Rabbit)	= 0.578 mg/L (Rat) 4 h

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No Information available.
Germ cell mutagenicity No Information available.
Carcinogenicity No Information available.

Reproductive toxicity No Information available.
STOT - single exposure No Information available.
STOT - repeated exposure No Information available.
Aspiration hazard No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity
 The following values are calculated based on chapter 3.1 of the GHS document .

12. ECOLOGICAL INFORMATION

Ecotoxicity

4.765% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
4-Chloro-3,5-dimethylphenol 88-04-0	Yes	0.13 - 1.0: 96 h Oncorhynchus mykiss mg/L LC50 static 1.3 - 2.1: 96 h Lepomis macrochirus mg/L LC50 static	6.7 - 9: 48 h Daphnia magna mg/L EC50 Static
Formaldehyde 50-00-0	Yes	22.6 - 25.7: 96 h Pimephales promelas mg/L LC50 flow-through 23.2 - 29.7: 96 h Pimephales promelas mg/L LC50 static 1510: 96 h Lepomis macrochirus µg/L LC50 static 41: 96 h Brachydanio rerio mg/L LC50 static 0.032 - 0.226: 96 h Oncorhynchus mykiss mL/L LC50 flow-through 100 - 136: 96 h Oncorhynchus mykiss mg/L LC50 static	2: 48 h Daphnia magna mg/L LC50 11.3 - 18: 48 h Daphnia magna mg/L EC50 Static

Persistence and degradability

No Information available.

Bioaccumulation

No Information available.

Other adverse effects

No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not reuse container.

Chemical Name	RCRA	RCRA - Basis for Listing	RCRA - D Series Wastes	RCRA - U Series Wastes
Formaldehyde 50-00-0	U122	Included in waste streams: K009, K010, K038, K040, K156, K157	Yes	U122

This product contains one or more substances that are listed with the State of California as a hazardous waste.

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT

Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
 DSL/NDSL Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product contains the following Proposition 65 chemicals

Chemical Name	California Proposition 65
Formaldehyde - 50-00-0	Carcinogen

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Formaldehyde 50-00-0	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

<u>NFPA</u>	Health hazards 0	Flammability 0	Instability 0	Physical and Chemical Properties Yes
<u>HMIS</u>	Health hazards 0	Flammability 0	Physical hazards 0	Personal protection A

Issue Date 08-Jan-2015

Revision Date 08-Jan-2015

Revision Note

No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet