

# HOSPECO

## Safety Data Sheet Ultra-Air 2.0 Screens, All Fragrances

---

### SECTION 1: Identification

#### 1.1 Product identifier:

Product name Ultra-Air 2.0 Screens, All Fragrances  
Recommended Use: Passive Deodorizer

#### 1.4 Supplier's details

Name Hospeco  
Address 10966 Industrial Parkway  
Bolivar, OH 44612  
USA

Telephone 330-874-1017

#### 1.5 Emergency phone number(s)

US, Canada: 800-255-3924. International: +01-813-248-0585

---

### SECTION 2: Hazard identification

#### 2.1 Classification of the substance or mixture

Acute Toxicity Oral 4  
Skin Sensitization 1

#### 2.2 GHS label elements, including precautionary statements

##### Pictogram



**Signal Word:** Warning

##### Hazard statement(s)

H317  
H302

May cause an allergic skin reaction  
Harmful if swallowed

##### Precautionary statement(s)

P264  
P261  
P272  
P270  
P280  
P301  
P330  
P321  
P363  
P302  
P501

Wash hands thoroughly after handling.  
Avoid breathing dust/fume/gas/mist/vapors/spray.  
Contaminated work clothing must not be allowed out of the workplace.  
Do not eat, drink, or smoke when using this product.  
Wear protective gloves.  
IF SWALLOWED: Call a poison center/doctor if you feel unwell.  
Rinse mouth.  
Specific Treatment: Reference section 4 of SDS  
Wash contaminated clothing before reuse.  
IF ON SKIN: Wash with plenty of water.  
Dispose of contents/container in accordance with local/regional/national/international regulations.  
If skin irritation occurs: Get medical advice/attention.

P332+P313

# Safety Data Sheet

## Ultra-Air 2.0 Screen, All Fragrances

---

### SECTION 3: Composition/information on ingredients

#### 3.1 Substances

Other names / synonyms                      Solid plastic slow-release deodorizing preparation in the form of a flat air freshener. It is made from pigmented thermoplastic impregnated with a fragrance composition and color to represent the fragrance. For institutional use only.

#### Hazardous components

##### 1. Ethylenevinylacetate copolymer

Concentration                                      60 - 80 % (weight)

CAS no.    24937-78-8

---

### SECTION 4: First-aid measures

#### 4.1 Description of necessary first-aid measures

General advice	No specific acute effects or symptoms are known.
If inhaled	No acute effects expected. If person is feeling unwell, remove to fresh air.
In case of skin contact	Wash off with soap and water.
In case of eye contact	Possibility of eye contact limited. In the event, wash thoroughly with water or approved eyewash.
If swallowed	Possibility of ingestion limited due to product form and difficulty to chew and ingest. In the event of ingestion, rinse mouth thoroughly with water.

---

### SECTION 5: Fire-fighting measures

#### 5.1 Suitable extinguishing media

Use extinguishing media appropriate for the surrounding fire. Water spray, fog or mist. Dry chemicals, sand etc.

#### 5.2 Specific hazards arising from the chemical

Thermal decomposition or burning may release a variety of products ranging from simple hydrocarbons to toxic/irritating gases including carbon monoxide and carbon dioxide. Full protective clothing should be worn before a confined fire space is entered. Self-contained breathing apparatus should be worn.

---

### SECTION 6: Accidental release measures

#### 6.1 Personal precautions, protective equipment and emergency procedures

No special requirements for accidental release required. Apply good housekeeping practices.

---

### SECTION 7: Handling and storage

#### 7.1 Precautions for safe handling

Follow normal good-housekeeping practices. Keep away from direct flames.

#### 7.2 Conditions for safe storage, including any incompatibilities

# Safety Data Sheet

## Ultra-Air 2.0 Screen, All Fragrances

Keep in cool, dry conditions in original containers at no more than 30° C

---

### SECTION 8: Exposure controls/personal protection

#### 8.2 Appropriate engineering controls

None established.

#### 8.3 Individual protection measures, such as personal protective equipment (PPE)

##### Body protection

Although unexpected, avoid prolonged skin contact. Use chemically resistant gloves as needed.

##### Respiratory protection

None required under normal usage

---

### SECTION 9: Physical and chemical properties

#### Information on basic physical and chemical properties

Appearance/form (physical state, color, etc.)	Polymer solid, color dependent on variant
Odor	Dependent on variant
Odor threshold	Not determined.
pH	Not determined
Melting point/freezing point	Estimated 60° C
Initial boiling point and boiling range	Not determined
Flash point	Not applicable
Evaporation rate	Not determined
Flammability (solid, gas)	Not determined
Upper/lower flammability limits	Not determined
Vapor pressure	Not determined
Vapor density	Not determined
Relative density	Not determined
Solubility(ies)	Not determined
Partition coefficient: n-octanol/water	Not determined
Auto-ignition temperature	Not determined
Decomposition temperature	Not determined
Viscosity	Not determined
Explosive properties	Not determined
Oxidizing properties	Not determined

---

### SECTION 10: Stability and reactivity

#### 10.2 Chemical stability

Normally stable.

#### 10.4 Conditions to avoid

Avoid extreme heat, strong oxidizing agents.

---

### SECTION 11: Toxicological information

#### Information on toxicological effects

##### Acute toxicity

Ingredients include a small quantity of volatile fragrance chemicals which may contain small amounts of substances that are harmful if swallowed and/or irritating to the eyes and skin.

# Safety Data Sheet

## Ultra-Air 2.0 Screen, All Fragrances

### Skin corrosion/irritation

No practical risk of adverse health effects.

### Serious eye damage/irritation

No practical risk of adverse health effects.

### Respiratory or skin sensitization

Prolonged exposure to volatile ingredients is unlikely to cause irritation or other adverse health effects.

---

## SECTION 12: Ecological information

### Toxicity

No specific information has been established regarding the product. However according to the conventional method of Directive 99/45/EC the product is classified as harmful to aquatic organisms, or causing long-term effects in the aquatic environment.

---

## SECTION 13: Disposal considerations

### Disposal of the product

Dispose of in accordance with Local Authority requirements e.g., for used product, as household waste

---

## SECTION 14: Transport information

### DOT (US)

Not dangerous goods

### IMDG

Not dangerous goods

### IATA

Not dangerous goods


---

## SECTION 15: Regulatory information

### HMIS Rating

Ultra-Air 2 Screen	
HEALTH	1
FLAMMABILITY	0
PHYSICAL HAZARD	0
PERSONAL PROTECTION	

### NFPA Rating



**Safety Data Sheet**  
**Ultra-Air 2.0 Screen, All Fragrances**

---

**SECTION 16: Other information**

This Safety Data Sheet is offered solely for your information, consideration and investigation. There are no warranties, either expressed or implied and no responsibility is assumed for the accuracy or completeness of the data contained herein. Version: 1.0, Date of issue: 2018-07-02