SAFETY DATA SHEET

Issue Date 21-Jul-2022 **Revision Date** 03-Mar-2022 **Version** 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier
Product Name Calcium & Lime Remover

Other means of identification
Product Code 641626
Synonyms None

Details of the supplier of the safety data sheet
Company Name Global Industrial
2505 Mill Center Parkway
Buford GA 30518
(888) 978-7759

Emergency telephone number
Emergency Telephone Chemtrec (US &Canada) 800-424-9300
Chemtrec (outside US & Canada) 703-527-3887

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status
This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin corrosion/irritation	Category 1 Sub-category C
Serious eye damage/eye irritation	Category 1

Label elements

Emergency Overview

Danger

Hazard statements
Causes severe skin burns and eye damage



Appearance Clear **Physical state** Liquid **Odor** Fresh & Clean

Precautionary Statements - Prevention
Do not breathe dust/fume/gas/mist/vapors/spray
Wash face, hands and any exposed skin thoroughly after handling
Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response
Specific Treatment (See Section 4 on the SDS)

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
Immediately call a POISON CENTER or doctor/physician
IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower
Wash contaminated clothing before reuse
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
Immediately call a POISON CENTER or doctor/physician
IF SWALLOWED: Rinse mouth. DO NOT induce vomiting
Drink plenty of water
Immediately call a POISON CENTER or doctor/physician

Precautionary Statements - Storage
Store locked up

Precautionary Statements - Disposal
Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)
Other Information
• Harmful to aquatic life with long lasting effects

Unknown Acute Toxicity 0 % of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
2-Hydroxypropanoic acid	79-33-4	10-30	*
Surfactant Blend	Proprietary	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

Skin Contact Wash off immediately with soap and plenty of water. If skin irritation persists, call a physician.

Eye contact Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes.

Inhalation Remove to fresh air.

Ingestion Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed

Symptoms Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media
Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical
No Information available.

Explosion data
Sensitivity to Mechanical Impact None.
Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters
As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation, especially in confined areas.

Environmental precautions

Environmental precautions Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Wear chemical resistant gloves.

Respiratory protection Ensure adequate ventilation, especially in confined areas. If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators or air purifying respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Clear
Color	Colorless
Odor	Fresh & Clean
Odor threshold	No Information available

Property	Values	Remarks • Method
pH	2.0 - 2.5	
Specific Gravity	1.03	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	Above 200°F	
Boiling point / boiling range	> 212 ° F	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

Other Information

Density Lbs/Gal	8.56
VOC Content (%)	Not Applicable

10. STABILITY AND REACTIVITY

Reactivity
No data available

Chemical stability
Stable under recommended storage conditions.

Possibility of Hazardous Reactions
None under normal processing.

Conditions to avoid
Extremes of temperature and direct sunlight.

Incompatible materials
None known based on information supplied.

Hazardous Decomposition Products
None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	Inhalation of vapors in high concentration may cause severe irritation or burns to the respiratory tract.
Eye contact	Avoid contact with eyes. Corrosive. Causes severe eye damage.

Skin Contact Avoid contact with skin. Corrosive. Contact with skin may cause severe irritation and burns.

Ingestion Ingestion causes burns of the upper digestive and respiratory tracts. Can burn mouth, throat, and stomach.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
2-Hydroxypropanoic acid 79-33-4	= 3730 mg/kg (Rat) = 3543 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	> 7.94 mg/L (Rat) 4 h
Surfactant Blend	2546 mg/kg (Rat)	1844 mg/kg (Rat)	-

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation MAY CAUSE SKIN IRRITATION.
Sensitization No Information available.
Germ cell mutagenicity No Information available.
Carcinogenicity No Information available.
Reproductive toxicity No Information available.
STOT - single exposure No Information available.
STOT - repeated exposure No Information available.
Aspiration hazard No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 0 % of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .
ATEmix (oral) 22,167.00
ATEmix (dermal) 13,024.20
ATEmix (inhalation-dust/mist) 60.2114

12. ECOLOGICAL INFORMATION

Ecotoxicity

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-Hydroxypropanoic acid 79-33-4	-	100 - 180: 96 h Lepomis macrochirus mg/L LC50 static 100 - 180: 96 h Oncorhynchus mykiss mg/L LC50 static 320: 96 h Brachydanio rerio mg/L LC50 semi-static	180 - 320: 48 h Daphnia magna mg/L EC50 Static 240: 48 h Daphnia magna mg/L EC50
Surfactant Blend	-	32.15: 96 h Rainbow Trout mg/L LC50	-
Trisodium Citrate Dihydrate 6132-04-3	-	18000 - 32000: 96 h Poecilia reticulata mg/L LC50	5600 - 10000: 48 h Daphnia magna mg/L EC50

Persistence and degradability
No Information available.

Bioaccumulation
Bioaccumulative potential.

Chemical Name	Partition coefficient
2-Hydroxypropanoic acid 79-33-4	-0.62

Other adverse effects No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Do not reuse container.

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT Not regulated

TDG Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL/NDSL	Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product has been evaluated and does not require warning labeling under California Proposition 65.

U.S. State Right-to-Know Regulations

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	**Health hazards** 2	**Flammability** 0	**Instability** 0	**Physical and Chemical Properties** -
HMIS	**Health hazards** 2	**Flammability** 0	**Physical hazards** 0	**Personal protection** B

Issue Date 21-Jul-2022
Revision Date 03-Mar-2022
Revision Note
No Information available
Disclaimer
The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet