

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name Scouring Crème Cleanser

Other means of identification

Product Code 670280
Synonyms None

Details of the supplier of the safety data sheet

Company Name Global Industrial
2505 Mill Center Parkway
Buford GA 30518
(888) 978-7759

Emergency telephone number

Emergency Telephone Chemtrec (US & Canada) 800-424-9300
Chemtrec (outside US & Canada) 703-527-3887

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Skin corrosion/irritation	Category 1
Serious eye damage/eye irritation	Category 1
Carcinogenicity	Category 1A
Specific target organ toxicity (single exposure)	Category 2
Specific target organ toxicity (repeated exposure)	Category 2

Label elements

Emergency Overview

Danger

Hazard statements

Causes severe skin burns and eye damage
May cause cancer
May cause damage to organs
May cause damage to organs through prolonged or repeated exposure



Appearance White Creamy**Physical state** Liquid**Odor** Floral**Precautionary Statements - Prevention**

Obtain special instructions before use
 Do not handle until all safety precautions have been read and understood
 Use personal protective equipment as required
 Do not breathe dust/fume/gas/mist/vapors/spray
 Wash face, hands and any exposed skin thoroughly after handling
 Do not eat, drink or smoke when using this product

Precautionary Statements - Response

Specific Treatment (See Section 4 on the SDS)
 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 Immediately call a POISON CENTER or doctor/physician
 IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower
 Wash contaminated clothing before reuse
 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
 Immediately call a POISON CENTER or doctor/physician
 IF SWALLOWED: Rinse mouth. DO NOT induce vomiting
 Drink plenty of water
 Immediately call a POISON CENTER or doctor/physician

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)**Other Information**

- Toxic to aquatic life with long lasting effects
- Toxic to aquatic life

Unknown Acute Toxicity

26.55% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Free Silica (Quartz)	14808-60-7	1-5	*
Nonylphenol Ethoxylate	9016-45-9	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES**First aid measures****General advice**

Immediate medical attention is required.

Skin Contact

Immediate medical attention is required. Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.

Eye contact

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Do not rub affected area.

Inhalation

Remove to fresh air. Call a physician or poison control center immediately. If not breathing, give artificial respiration. If breathing is difficult, give oxygen.

Ingestion

Immediate medical attention is required. Do NOT induce vomiting. Drink plenty of water. Never give anything by mouth to an unconscious person. Remove from exposure, lie down. Clean mouth with water and drink afterwards plenty of water. Call a physician or poison

control center immediately.

Self-protection of the first aider Use personal protective equipment as required. Avoid contact with skin, eyes or clothing.

Most important symptoms and effects, both acute and delayed

Symptoms Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated. Do not give chemical antidotes. Asphyxia from glottal edema may occur. Marked decrease in blood pressure may occur with moist rales, frothy sputum, and high pulse pressure. Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

The product causes burns of eyes, skin and mucous membranes. Thermal decomposition can lead to release of irritating and toxic gases and vapors. In the event of fire and/or explosion do not breathe fumes.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Evacuate personnel to safe areas. Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Keep people away from and upwind of spill/leak.

Environmental precautions

Environmental precautions Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Dike far ahead of liquid spill for later disposal. Soak up with inert absorbent material. Take up mechanically, placing in appropriate containers for disposal. Clean contaminated surface thoroughly. Prevent product from entering drains. Dam up. After cleaning, flush away traces with water.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Ensure adequate ventilation, especially in confined areas. In case of insufficient ventilation,

wear suitable respiratory equipment. Use only with adequate ventilation and in closed systems.

Conditions for safe storage, including any incompatibilities

Storage Conditions

Keep container tightly closed in a dry and well-ventilated place. Keep out of the reach of children. Keep containers tightly closed in a dry, cool and well-ventilated place. Keep in properly labeled containers.

Incompatible materials

Incompatible with strong acids and bases. Incompatible with oxidizing agents.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Free Silica (Quartz) 14808-60-7	TWA: 0.025 mg/m ³ respirable particulate matter	TWA: 50 µg/m ³ TWA: 50 µg/m ³ excludes construction work, agricultural operations, and exposures that result from the processing of sorptive clays (vacated) TWA: 0.1 mg/m ³ respirable dust : (250)/(%SiO ₂ + 5) mppcf TWA respirable fraction : (10)/(%SiO ₂ + 2) mg/m ³ TWA respirable fraction	IDLH: 50 mg/m ³ respirable dust TWA: 0.05 mg/m ³ respirable dust
2-(2-methoxypropoxy)propano 34590-94-8	STEL: 150 ppm TWA: 100 ppm S*	TWA: 100 ppm TWA: 600 mg/m ³ (vacated) TWA: 100 ppm (vacated) TWA: 600 mg/m ³ (vacated) STEL: 150 ppm (vacated) STEL: 900 mg/m ³ (vacated) S* S*	IDLH: 600 ppm TWA: 100 ppm TWA: 600 mg/m ³ STEL: 150 ppm STEL: 900 mg/m ³
Mica 12001-26-2	TWA: 3 mg/m ³ respirable particulate matter	(vacated) TWA: 3 mg/m ³ respirable dust <1% Crystalline silica TWA: 20 mppcf <1% Crystalline silica	IDLH: 1500 mg/m ³ TWA: 3 mg/m ³ containing <1% Quartz respirable dust
Ethanol 64-17-5	STEL: 1000 ppm	TWA: 1000 ppm TWA: 1900 mg/m ³ (vacated) TWA: 1000 ppm (vacated) TWA: 1900 mg/m ³	IDLH: 3300 ppm TWA: 1000 ppm TWA: 1900 mg/m ³

NIOSH IDLH *Immediately Dangerous to Life or Health*

Other Information

Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls

Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection

Tight sealing safety goggles. Wear a face shield if splashing hazard exists.

Skin and body protection

Wear impervious protective clothing, including boots, gloves, lab coat, apron or coveralls, as appropriate, to prevent skin contact.

Respiratory protection

If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene

When using do not eat, drink or smoke. Keep away from food, drink and animal feeding stuffs. Contaminated work clothing should not be allowed out of the workplace. Regular

cleaning of equipment, work area and clothing is recommended. Avoid contact with skin, eyes or clothing. Take off all contaminated clothing and wash it before reuse. Wear suitable gloves and eye/face protection.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid
Appearance	White Creamy
Color	White
Odor	Floral
Odor threshold	No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	11.5 - 12.5	
Specific Gravity	1.3	
Viscosity	17,000 - 18,000 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	None	
Boiling point / boiling range		
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

Other Information

Density Lbs/Gal	10.83
VOC Content (%)	1.05

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Exposure to air or moisture over prolonged periods.

Incompatible materials

Incompatible with strong acids and bases. Incompatible with oxidizing agents.

Hazardous Decomposition Products

Thermal decomposition can lead to release of irritating and toxic gases and vapors.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	Avoid breathing vapors or mists. Inhalation of vapors in high concentration may cause severe irritation or burns to the respiratory tract. Causes damage to organs through prolonged or repeated exposure if inhaled.
Eye contact	Avoid contact with eyes. Corrosive. Causes severe eye damage.
Skin Contact	Avoid contact with skin. Corrosive. Contact with skin may cause severe irritation and burns.
Ingestion	Do not taste or swallow. Ingestion causes acute irritation and burns to the mucous membranes of the mouth, trachea, esophagus and stomach.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Nonylphenol Ethoxylate 9016-45-9	= 2590 mg/kg (Rat) = 1310 mg/kg (Rat)	= 1780 µL/kg (Rabbit) = 2 mL/kg (Rabbit)	-

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Corrosivity Causes burns. Extremely corrosive and destructive to tissue. Risk of serious damage to eyes.

Sensitization No Information available.

Germ cell mutagenicity No Information available.

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen. Ethanol has been shown to be carcinogenic in long-term studies only when consumed as alcoholic beverage.

Chemical Name	ACGIH	IARC	NTP	OSHA
Free Silica (Quartz) 14808-60-7	A2	Group 1	Known	X

ACGIH (American Conference of Governmental Industrial Hygienists)

A2 - Suspected Human Carcinogen

IARC (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans

Group 3 -Not classifiable as a human carcinogen

NTP (National Toxicology Program)

Known - Known Carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity No Information available.

STOT - single exposure No Information available.

STOT - repeated exposure No Information available.

Chronic toxicity Chronic exposure to corrosive fumes/gases may cause erosion of the teeth followed by jaw necrosis. Bronchial irritation with chronic cough and frequent attacks of pneumonia are common. Gastrointestinal disturbances may also be seen. Ethanol has been shown to be a reproductive toxin only when consumed as an alcoholic beverage. Ethanol has been shown to be carcinogenic in long-term studies only when consumed as alcoholic beverage. Avoid repeated exposure. Possible risk of irreversible effects.

Target organ effects Central nervous system, EYES, Lungs, Respiratory system.

Aspiration hazard No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 26.55% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (dermal) 12,968.00

ATEmix (inhalation-dust/mist) 26.47

12. ECOLOGICAL INFORMATION**Ecotoxicity**

29.95% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-(2-methoxypropoxy)propano 34590-94-8	-	10000: 96 h Pimephales promelas mg/L LC50 static	1919: 48 h Daphnia magna mg/L LC50
Nonylphenol Ethoxylate 9016-45-9	-	5: 96 h Fish mg/L LC50	-
Alkyl (C12-16) dimethyl benzyl ammonium chloride 68424-85-1	-	0.223 - 0.46: 96 h Lepomis macrochirus mg/L LC50 static 1.3: 96 h Poecilia reticulata mg/L LC50 semi-static 2.4: 96 h Oryzias latipes mg/L LC50 semi-static 0.823 - 1.61: 96 h Oncorhynchus mykiss mg/L LC50 static	-
Ethanol 64-17-5	-	12.0 - 16.0: 96 h Oncorhynchus mykiss mL/L LC50 static 100: 96 h Pimephales promelas mg/L LC50 static 13400 - 15100: 96 h Pimephales promelas mg/L LC50 flow-through	9268 - 14221: 48 h Daphnia magna mg/L LC50 10800: 24 h Daphnia magna mg/L EC50 2: 48 h Daphnia magna mg/L EC50 Static

Persistence and degradability

No Information available.

Bioaccumulation

No Information available.

Other adverse effects

No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods**Disposal of wastes**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT

Not regulated

TDG

Not regulated

15. REGULATORY INFORMATION

International Inventories**TSCA**

Complies

DSL/NDSL

Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
Feldspar - 68476-25-5	1.0
2-(2-methoxypropoxy)propano - 34590-94-8	1.0

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	Yes
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

US State Regulations**California Proposition 65**

WARNING: This product contains a chemical known to the state of California to cause cancer.

Chemical Name	California Proposition 65
Free Silica (Quartz) - 14808-60-7	Carcinogen

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Feldspar 68476-25-5	X	-	X
Flux Calcined Diatomaceous Earth 68855-54-9	-	-	X
Free Silica (Quartz) 14808-60-7	X	X	X
Trisodium Phosphate 10101-89-0	X	X	X
2-(2-methoxypropoxy)propano 34590-94-8	X	X	X
Mica 12001-26-2	X	X	X
Ethanol 64-17-5	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 3	Flammability 0	Instability 0	Physical and Chemical Properties - Personal protection B
HMIS	Health hazards 3	Flammability 0	Physical hazards 0	

Issue Date 05-Nov-2018
Revision Date 26-Mar-2018
Revision Note
No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet