

OPH-T PRECISION BALANCES



ROUND PAN
0.01 G READABILITY



SQUARE PAN
0.1 G READABILITY

FEATURES

- Large, high contrast LCD screen
- Comes with an AC adapter; rechargeable battery (optional)
- Splash-proof keyboard and display
- Anti-static stainless steel weighing pan
- Automated zero tracking and full range tare
- Calibration with reference weights
- Parts counting, percent weighing and dynamic weighing
- Multiple weighing units: g, ct, lb, oz, ozt, N, dwt, GN (grain), tLT

SPECIFICATIONS

- READABILITY:** 0.01g, 0.1g
REPEATABILITY: ±0.02g, ±0.2g
LINEARITY: ±0.02g, 0.2g
STABILIZATION TIME:
 5 seconds (typically)
SENSITIVITY: 2ppm / (10 --30)
POWER (AC ADAPTER):
 Input 100V-240VAC, 50HZ/60HZ
 Output 6vDC-9vDC/600mA
BAUD OPTIONS:
 300/600/2400/4800/9600
AMBIENT TEMPERATURE:
 40°F - 110°F
KEYPAD: 5 keys, splash-proof
WARRANTY:
 1 year limited warranty

PART#	CAPACITY	DIMENSIONS	PAN SIZE	SHIP WT.
ROUND PAN				
OPH-T202	200 g x 0.01 g	10" L x 7" W x 3" H	Φ5"	4 lbs
OPH-T302	300 g x 0.01 g	10" L x 7" W x 3" H	Φ5"	4 lbs
OPH-T502	500 g x 0.01 g	10" L x 7" W x 3" H	Φ5"	4 lbs
OPH-T602	600 g x 0.01 g	10" L x 7" W x 3" H	Φ5"	4 lbs
SQUARE PAN				
OPH-T2001	2,000 g x 0.1 g	10" L x 7" W x 3" H	6.3" x 5.7"	4 lbs
OPH-T3001	3,000 g x 0.1 g	10" L x 7" W x 3" H	6.3" x 5.7"	4 lbs
OPH-T5001	5,000 g x 0.1 g	10" L x 7" W x 3" H	6.3" x 5.7"	4 lbs
OPH-T6001	6,000 g x 0.1 g	10" L x 7" W x 3" H	6.3" x 5.7"	4 lbs

