

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name Carpet Spotter & Pretreater

Other means of identification

Product Code 670290
Synonyms None

Details of the supplier of the safety data sheet

Company Name Global Industrial
2505 Mill Center Parkway
Buford GA 30518
(888) 978-7759

Emergency telephone number

Emergency Telephone Chemtrec (US & Canada) 800-424-9300
Chemtrec (outside US & Canada) 703-527-3887

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Serious eye damage/eye irritation	Category 2

Label elements

Emergency Overview

Warning

Hazard statements

Causes serious eye irritation



Appearance Clear Colorless

Physical state Liquid

Odor Solvent

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling
Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response

Specific Treatment (See Section 4 on the SDS)

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

If eye irritation persists: Get medical advice/attention

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Drink plenty of water

Immediately call a POISON CENTER or doctor/physician

Precautionary Statements - Disposal

Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)

Other Information

Unknown Acute Toxicity

0% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
2-(2-butoxyethoxy)ethanol	112-34-5	3-7	*
2-Propanol	67-63-0	1-5	*
Surfactant Blend	Proprietary	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

Skin Contact

Wash off immediately with plenty of water. If skin irritation persists, call a physician.

Eye contact

Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

Inhalation

Remove to fresh air.

Ingestion

Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed

Symptoms

Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians

Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No Information available.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation, especially in confined areas.

Environmental precautions

Environmental precautions Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters**Exposure Guidelines**

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
2-(2-butoxyethoxy)ethanol 112-34-5	TWA: 10 ppm inhalable fraction and vapor	-	-
2-Propanol 67-63-0	STEL: 400 ppm TWA: 200 ppm	TWA: 400 ppm TWA: 980 mg/m ³ (vacated) TWA: 400 ppm (vacated) TWA: 980 mg/m ³ (vacated) STEL: 500 ppm (vacated) STEL: 1225 mg/m ³	IDLH: 2000 ppm TWA: 400 ppm TWA: 980 mg/m ³ STEL: 500 ppm STEL: 1225 mg/m ³

NIOSH IDLH Immediately Dangerous to Life or Health

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Wear protective gloves and protective clothing.

Respiratory protection Ensure adequate ventilation, especially in confined areas. In case of insufficient ventilation, wear suitable respiratory equipment. If irritation is experienced, move to a well ventilated

area.

General Hygiene Handle in accordance with good industrial hygiene and safety practice. Wear suitable gloves and eye/face protection.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Clear Colorless
Color	Colorless
Odor	Solvent
Odor threshold	No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	9.5 - 10.5	
Specific Gravity	0.998	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	Above 200°F	
Boiling point / boiling range	100 °C / 212 ° F Degrees	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

Other Information

Density Lbs/Gal	8.32
VOC Content (%)	10.25

10. STABILITY AND REACTIVITY

Reactivity
No data available

Chemical stability
Stable under recommended storage conditions.

Possibility of Hazardous Reactions
None under normal processing.

Conditions to avoid
Extremes of temperature and direct sunlight.

Incompatible materials
None known based on information supplied.

Hazardous Decomposition Products
None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	Avoid breathing vapors or mists. Inhalation of vapors in high concentration may cause irritation of respiratory system.
Eye contact	Avoid contact with eyes. Direct contact may cause serious eye irritation.
Skin Contact	Avoid contact with skin. May be absorbed through the skin in harmful amounts. Prolonged or repeated contact may dry skin and cause irritation.
Ingestion	Do not taste or swallow. May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
2-(2-butoxyethoxy)ethanol 112-34-5	= 5660 mg/kg (Rat)	= 2700 mg/kg (Rabbit)	-
2-Propanol 67-63-0	= 1870 mg/kg (Rat)	= 4059 mg/kg (Rabbit)	= 72600 mg/m ³ (Rat) 4 h
Surfactant Blend	> 2000 mg/kg (Rat)	> 2000 mg/kg (Rat)	-

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No Information available.
Germ cell mutagenicity No Information available.
Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
2-Propanol 67-63-0	-	Group 3	-	X

IARC (International Agency for Research on Cancer)

Group 3 -Not classifiable as a human carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity No Information available.
STOT - single exposure No Information available.
STOT - repeated exposure No Information available.
Target organ effects EYES, Respiratory system, Skin.
Aspiration hazard No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral)	25,042.00
ATEmix (dermal)	24,690.00
ATEmix (inhalation-dust/mist)	1,815.00

12. ECOLOGICAL INFORMATION**Ecotoxicity**

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-(2-butoxyethoxy)ethanol 112-34-5	100: 96 h Desmodesmus subspicatus mg/L EC50	1300: 96 h Lepomis macrochirus mg/L LC50 static	2850: 24 h Daphnia magna mg/L EC50 100: 48 h Daphnia magna mg/L EC50
2-Propanol 67-63-0	1000: 96 h Desmodesmus subspicatus mg/L EC50 1000: 72 h Desmodesmus subspicatus mg/L EC50	9640: 96 h Pimephales promelas mg/L LC50 flow-through 1400000: 96 h Lepomis macrochirus µg/L LC50 11130: 96 h Pimephales promelas mg/L LC50 static	13299: 48 h Daphnia magna mg/L EC50

Surfactant Blend	-	1.2: 96 h Oncorhynchus mykiss mg/L LC50	5.3: 48 h Daphnia mg/L LC50
Sodium Lauryl Sulfate 151-21-3	53: 72 h Desmodemus subspicatus mg/L EC50 30 - 100: 96 h Desmodemus subspicatus mg/L EC50 117: 96 h Pseudokirchneriella subcapitata mg/L EC50 3.59 - 15.6: 96 h Pseudokirchneriella subcapitata mg/L EC50 static 42: 96 h Desmodemus subspicatus mg/L EC50	8 - 12.5: 96 h Pimephales promelas mg/L LC50 static 15 - 18.9: 96 h Pimephales promelas mg/L LC50 static 22.1 - 22.8: 96 h Pimephales promelas mg/L LC50 static 4.3 - 8.5: 96 h Oncorhynchus mykiss mg/L LC50 static 4.62: 96 h Oncorhynchus mykiss mg/L LC50 flow-through 4.2: 96 h Oncorhynchus mykiss mg/L LC50 10.2 - 22.5: 96 h Pimephales promelas mg/L LC50 semi-static 6.2 - 9.6: 96 h Pimephales promelas mg/L LC50 13.5 - 18.3: 96 h Poecilia reticulata mg/L LC50 semi-static 10.8 - 16.6: 96 h Poecilia reticulata mg/L LC50 static 1.31: 96 h Cyprinus carpio mg/L LC50 semi-static 7.97: 96 h Brachydanio rerio mg/L LC50 flow-through 9.9 - 20.1: 96 h Brachydanio rerio mg/L LC50 semi-static 4.06 - 5.75: 96 h Lepomis macrochirus mg/L LC50 static 4.2 - 4.8: 96 h Lepomis macrochirus mg/L LC50 flow-through 4.5: 96 h Lepomis macrochirus mg/L LC50 5.8 - 7.5: 96 h Pimephales promelas mg/L LC50 static 4.1: 48 h Leuciscus idus mg/L LC50 static	1.8: 48 h Daphnia magna mg/L EC50 21.2: 24 h Daphnia magna mg/L EC50

Persistence and degradability

No Information available.

Bioaccumulation

Bioaccumulative potential.

Chemical Name	Partition coefficient
2-Propanol 67-63-0	0.05

Other adverse effects

No Information available

13. DISPOSAL CONSIDERATIONS**Waste treatment methods****Disposal of wastes**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste Status
2-Propanol 67-63-0	Toxic Ignitable

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT Not regulated

TDG Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies

DSL/NDSL Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
2-(2-butoxyethoxy)ethanol - 112-34-5	1.0
2-Propanol - 67-63-0	1.0

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product has been evaluated and does not require warning labeling under California Proposition 65.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
2-(2-butoxyethoxy)ethanol 112-34-5	X	-	X
2-Propanol 67-63-0	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

<u>NFPA</u>	Health hazards 1	Flammability 0	Instability 0	Physical and Chemical Properties -
<u>HMIS</u>	Health hazards 1	Flammability 0	Physical hazards 0	Personal protection B

Issue Date 06-Nov-2018

Revision Date 06-Feb-2018

Revision Note

No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet