



## OPH-Z HIGH CAPACITY PRECISION BALANCE



### SPECIFICATIONS

**READABILITY:** 0.1g  
**REPEATABILITY:**  $\pm 0.2g$   
**LINEARITY:**  $\pm 0.2g$   
**STABILIZATION TIME:**  
5 seconds (typically)  
**SENSITIVITY:** 2ppm / (10 --30)  
**POWER (AC ADAPTER):**  
Input 100V-240VAC  
Output 6vDC-9vDC/600mA  
**BAUD OPTIONS:**  
300/600/2400/4800/9600  
**AMBIENT TEMPERATURE:**  
40°F - 110°F  
**KEYPAD:** 11 keys, splash-proof  
**WARRANTY:**  
1 year limited warranty

### FEATURES

- Large removable, stainless steel weighing platform
- Splash-proof keyboard and display
- Anti-static stainless steel weighing pan
- Automated zero tracking and full range tare
- Calibration with reference weights
- RS-232 for bi-directional communication with a PC or printer
- Parts counting, percent weighing and dynamic weighing
- Multiple weighing units: g, kg, ct, lb, oz, ozt, dwt, pcs, tls, tIT, tIH, GN(grain), dr, ms, bat, mom T/A/R

PART#	CAPACITY	DIMENSIONS	PAN SIZE	SHIP WT.
OPH-Z10	10 kg x 0.1 g	13" L x 13" W x 5" H	12" x 9"	9 lbs
OPH-Z20	20 kg x 0.1 g			
OPH-Z30	30 kg x 0.1 g			

