

## 4,000 PSI - 4.0 GPM GAS PRESSURE WASHER WITH HONDA GX390 ENGINE AND GENERAL TRIPLEX PUMP

COMMERCIAL SERIES

MODEL: PE-4013HWPSGEN

### FEATURES

- **Commercial Honda engine** with excellent weight to power ratio. Designed to be used all day, everyday.
- **Direct drive** system connects the engine to the pump for a compact and efficient power transfer.
- **Commercial grade General triplex pump** featuring die-cast body, forged brass manifold, one-piece plungers, thermal release valve and improved heat dissipation.
- **External unloader** provides enhanced cooling and be set to dump-to-ground bypass water to maximize cooling system.
- **Commercial grade accessories** included are a 50 foot high-pressure hose, spray gun wand assembly, and four spray nozzles.
- **Heavy-duty stainless steel frame** with storage for accessories and 12" flat free tires easily handles going over rough terrain.



Scan the QR code with your mobile device and discover more about this BE Pressure washer.



### ENGINE

MODEL: **HONDA GX390**  
 TYPE: **AIR COOLED, 4-STROKE OHV**  
 DISPLACEMENT: **389CC**  
 FUEL TYPE: **86 OCTANE, UP TO 10% ETHANOL**  
 OIL TYPE: **SAE 10W30**

### PUMP SPECS

MODEL: **GENERAL EZ4040G**  
 TYPE: **TRIPLEX**  
 PART NUMBER: **85.139.021B**  
 OIL TYPE: **30W NON-DETERGENT**  
 SOAP SYSTEM: **ADJUSTABLE INJECTOR**

### UNLOADER

TYPE: **EXTERNAL W/36" HOSE**  
 PART NUMBER: **85.300.037**

### FRAME

MATERIAL: **STAINLESS STEEL**  
 WHEELS: **12" FLAT FREE**


### ACCESSORIES

HOSE TYPE: **50' X 3/8" STEEL BRAIDED**  
 PART NUMBER: **85.238.153**  
 NOZZLES: **0°, 15°, 40° AND SOAPER**  
 PART NUMBER: **85.210.035BEP**  
 GUN WAND: **36" INSULATED**  
 PART NUMBER: **85.205.026**  
 FITTINGS: **QUICK CONNECT**

### BOXED SIZE

LxWxH: **32" x 25" x 27"**  
 WEIGHT: **158 LBS**

### UNIT SIZE



UNIT WEIGHT: **151 LBS**

### WARRANTY

ENGINE: **3 YEARS**  
 PUMP: **5 YEARS**  
 UPC: **777897105698**

03-2021