


## OP-916-NN HEAVY DUTY FLOOR SCALES



OP-902 Indicator



### FEATURES

- Painted rugged diamond deck tread plate construction
- Anti-corrosion, baked on powder paint
- Channel construction for superior strength
- Painted mild steel junction box
- Side access to junction box to minimize water access
- Four alloy steel load cells
- Load cell capacity is 2X the scale capacity for a 200% overload protection
- Four adjustable alloy steel ball capture support feet
- 20' heavy duty stainless steel shielded cable
- Factory pre-calibrated for quick setup

### OPTIONS/ACCESSORIES:

- Access ramps
- Pit frames
- Impact Protection
- Portability frames
- Thermal printer
- Stand for indicator
- Large Display
- Data logging software
- Remote junction box
- Wireless option
- Explosion proof option

PRODUCT NO.	PLATFORM SIZE	CAPACITY	NTEP	SHIP WT.
OP-916-4x4-5K-NN	48" x 48" x 4.2" (H)	5,000 lb x 1 lb / 2,500 kg	No	270 lbs
OP-916-4x4-10K-NN	48" x 48" x 4.2" (H)	10,000 lb x 2 lb / 5,000 kg	No	280 lbs
OP-916-5x5-5K-NN	60" x 60" x 4.2" (H)	5,000 lb x 1 lb / 2,500 kg	No	400 lbs
OP-916-5x5-10K-NN	60" x 60" x 4.2" (H)	10,000 lb x 2 lb / 5,000 kg	No	420 lbs

