HOSPECO

Safety Data Sheet Ultra-Air Deodorizing Clip, All Fragrances

SECTION 1: Identification

1.1 Product identifier

Product name Ultra-Air Deodorizing Clip, All Fragrances

1.4 Supplier's details

Name Hospeco

Address 10966 Industrial Parkway

Bolivar, OH 44612

USA

Telephone 330-874-1017

5 Emergency phone number(s)

USA: (813) 248-0573

SECTION 2: Hazard identification

2.1 Classification of the substance or mixture

Acute Toxicity Oral 4 Skin Sensitization 1

2.2 GHS label elements, including precautionary statements

Pictogram



Signal Word: Warning Hazard statement(s)

H317 May cause an allergic skin reaction

H302 Harmful if swallowed

Precautionary statement(s)

P264 Wash hands thoroughly after handling.
P301 IF SWALLOWED: Call physician
P302 IF ON SKIN: Wash with plenty of water.

P332+P313 If skin irritation occurs: Get medical advice/attention.

SECTION 3: Composition/information on ingredients

3.1 Substances

Other names / synonyms Solid plastic slow-release deodorizing preparation in the form of a

flat air freshener. It is made from pigmented thermoplastic impregnated with a fragrance composition and color to represent the fragrance. For

institutional use only.

Safety Data Sheet Ultra-Air Deodorizing Clip, All Fragrances

Hazardous components

1. Ethylenevinylacetate copolymer

Concentration 60 - 80 % (weight) CAS no. 24937-78-8

SECTION 4: First-aid measures

4.1 Description of necessary first-aid measures

General advice No specific acute effects or symptoms are known.

If inhaled No acute effects expected. If person is feeling unwell, remove to fresh air.

In case of skin contact Wash off with soap and water.

In case of eye contact Possibility of eye contact limited. In the event, wash thoroughly with water or

approved eyewash.

If swallowed Possibility of ingestion limited due to product form and difficulty to chew and

ingest. In the event of

ingestion, rinse mouth thoroughly with water.

SECTION 5: Fire-fighting measures

5.1 Suitable extinguishing media

Use extinguishing media appropriate for the surrounding fire. Water spray, fog or mist. Dry chemicals, sand etc.

5.2 Specific hazards arising from the chemical

Thermal decomposition or burning may release a variety of products ranging from simple hydrocarbons to toxic/irritating gases including carbon monoxide and carbon dioxide. Full protective clothing should be worn before a confined fire space is entered. Self-contained breathing apparatus should be worn.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

No special requirements for accidental release required. Apply good housekeeping practices.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Follow normal good-housekeeping practices. Keep away from direct flames.

7.2 Conditions for safe storage, including any incompatibilities

Keep in cool, dry conditions in original containers at no more than 30° C

SECTION 8: Exposure controls/personal protection

8.2 Appropriate engineering controls

None established.

8.3 Individual protection measures, such as personal protective equipment (PPE)

Safety Data Sheet Ultra-Air Deodorizing Clip, All Fragrances

Body protection

Although unexpected, avoid prolonged skin contact. Use chemically resistant gloves as needed.

Respiratory protection

None required under normal usage

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties

Appearance/form (physical state, color, etc.)

Air freshe

Odor

Odor threshold

Hq

Melting point/freezing point

Initial boiling point and boiling range

Flash point Evaporation rate

Flammability (solid, gas)

Upper/lower flammability limits

Vapor pressure

Vapor density

Relative density Solubility(ies)

Partition coefficient: n-octanol/water

Auto-ignition temperature

Decomposition temperature

Viscosity

Explosive properties

Oxidizing properties

Air freshener infused with fragrance oil.

Dependent on variant

Not determined.

Not determined

Estimated 60° C

Not determined Not applicable

Not determined

Not determined

SECTION 10: Stability and reactivity

10.2 Chemical stability

Normally stable.

10.4 Conditions to avoid

Avoid extreme heat, strong oxidizing agents.

SECTION 11: Toxicological information

Information on toxicological effects

Acute toxicity

Ingredients include a small quantity of volatile fragrance chemicals which may contain small amounts of substances that are harmful if swallowed and/or irritating to the eyes and skin.

Skin corrosion/irritation

No practical risk of adverse health effects.

Serious eye damage/irritation

No practical risk of adverse health effects.

Respiratory or skin sensitization

Prolonged exposure to volatile ingredients is unlikely to cause irritation or other adverse health effects.

SECTION 12: Ecological information

Toxicity

No specific information has been established regarding the product. However according to the conventional method of Directive 99/45/EC the product is classified as harmful to aquatic organisms, or causing long-term effects in the aquatic environment.

SECTION 13: Disposal considerations

Disposal of the product

Dispose of in accordance with Local Authority requirements e.g., for used product, as household waste

SECTION 14: Transport information

DOT (US)

Not dangerous goods

IMDG

Not dangerous goods

IATA

Not dangerous goods

SECTION 15: Regulatory information

HMIS Rating



NFPA Rating



SECTION 16: Other information