

T909 INDICATOR






FEATURES

- Multiple weighing units: lb/kg or lb/kg/g/oz/lb-oz (on upgraded model)
- Gross/Tare/Pre-Set Tare/Zero
- Multiple Hold functions
- Overload / Underload alarm
- Power saving mode
- Automatic date and time update
- Ability to modify gravity based on different geographical locations
- 100% manual zero range setting
- Automatic error warning alarm
- Splash proof keyboard and display
- Bright LED display easy to read both indoor and outdoor
- Displays up to 50,000 graduations
- Mounting bracket and Hardware (included)
- Operates on 110V AC adapter and rechargeable battery (included)
- Full Duplex RS-232 Serial Port
- Drives up to 8 350Ω load cells
- 1 Year Warranty

ACCESSORIES

- Thermal Ticket Printer
- Label Printer
- Zebra Label Printer
- Remote Display
- Stainless Steel Stand
- I/O Card to control external system



SPECIFICATIONS

Display:	LED; 1-inch x 6-digit numeric
Units:	lb, kg (primary); oz, lb:oz, g (secondary)
Accuracy Class:	10,000 e
Resolution:	120,000 dd industrial; 10,000 dd HB44
Excitation Voltage:	5V DC
Largest output current:	120 mA
Excitation Circuit:	5 VDC, 4 wire connections
Load Cell:	8 load cells of 350 Ω maximum
Load Cell Excitation:	5 ± 0.5VDC
Display Resolution:	30,000 ; ADC: 2,000,000
Zero stability error:	TK0 0.1μV//K
Sensitivity (internal):	0.3μV/d
Input voltage:	-30 to +30mV DC
Power:	100~240VAC @50~60hz
Battery:	6V 1.3Ah
Operating Temp.	14°F to 104 °F(-10°C to 40°C) ≤90%RH
Weight:	4.3 lbs (1.95 kg)
Internal Resolution:	120,000 dd industrial; 10,000 dd HB44
Display Increment:	Selectable 1, 2, 5, 10, 20, 50
Conversion Rate:	12 samples/second typical
Analog Signal Input Range:	1mV/V to 3mV/V
Analog Signal Sensitivity:	0.1 uV/graduation (min)
Measurement Rate:	0~15mV
Auto Zero Tracking:	0 - 5 dd increments
Auto Zero Delay:	0 - 3 second increments
Motion Detect:	1 - 10 dd
Motion Delay:	1 - 55 dd