Original Deodorizing Super Sock

SAFETY DATA SHEET

SECTION 1: Identification

1.1 Product identifier

Product name Original Deodorizing Super Sock

1.4 Supplier's details

Name HOSPECO

Address 10966 INDUSTRIAL PARKWAY NW

BOLIVAR OH 44612

USA

Telephone 800-443-4321

1.5 Emergency phone number(s)

US, Canada: 800-255-3924. International: +01-813-248-0585

SECTION 2: Hazard identification

2.1 Classification of the substance or mixture

GHS classification in accordance with: (US) OSHA (29 CFR 1910.1200)

- Eye damage/irritation, Cat. 2A
- Skin corrosion/irritation, Cat. 2
- Sensitization, skin, Cat. 1

2.2 GHS label elements, including precautionary statements

Pictogram



Signal word Warning

Hazard statement(s)

H315 Causes skin irritation

H317 May cause an allergic skin reaction
H319 Causes serious eye irritation

Precautionary statement(s)

P261 Avoid breathing dust/fume/gas/mist/vapors/spray.

P264 Wash ... thoroughly after handling.

P272 Contaminated work clothing must not be allowed out of the workplace.

P280 Wear eye protection/face protection/protective gloves.

P302+P352 IF ON SKIN: Wash with plenty of water/...

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses if present and easy to do. Continue rinsing.

P321 Specific treatment (see ... on this label).

P332+P313 If skin irritation occurs: Get medical advice/attention.
P333+P313 If skin irritation or rash occurs: Get medical advice/attention.
P337+P313 If eye irritation persists: Get medical advice/attention.
P362+P364 Take off contaminated clothing and wash it before reuse.

P363 Wash contaminated clothing before reuse.

P501 Dispose of contents/container to ...

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Hazardous components

1. Odor Counteractant

Concentration > 50 % (weight)

Eye damage/irritation, Cat. 2ASkin corrosion/irritation, Cat. 2Sensitization, skin, Cat. 1

H315 Causes skin irritation

H317 May cause an allergic skin reaction
H319 Causes serious eye irritation

SECTION 4: First-aid measures

4.1 Description of necessary first-aid measures

If inhaled Move person to fresh air; if effects occur, consult a physician.

In case of skin contact Wash off with plenty of water.

In case of eye contact Flush eyes thoroughly with water for several minutes. Remove contact

lenses after the

initial 1-2 minutes and continue flushing for several additional minutes. If

effects occur, consult a

physician, preferably an ophthalmologist.

If swallowed, do not induce vomiting. Administer 2 glasses of water

immediately. Obtain medical care and hospital treatment if symptoms arise.

SECTION 5: Fire-fighting measures

5.1 Suitable extinguishing media

Water fog or fine spray. Dry chemical fire extinguishers. Carbon

Version: 1.0, Date of issue: 2018-11-26, p. 2 of 5

dioxide fire extinguishers. Foam. Alcohol resistant foams (ATC type) are preferred. General purpose synthetic foams (including AFFF) or protein foams may function, but will be less effective.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Use appropriate safety

equipment. For additional information, refer to Section 8, Exposure Controls and Personal Protection.

6.2 Environmental precautions

Prevent from entering into soil, ditches, sewers, waterways and/or groundwater. See Section 12, Ecological Information.

6.3 Methods and materials for containment and cleaning up

The product as supplied is in a contained state.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Store in a cool, dry place.

7.2 Conditions for safe storage, including any incompatibilities

Kepp product tightly closed when not in use.

SECTION 8: Exposure controls/personal protection

8.3 Individual protection measures, such as personal protective equipment (PPE)

Eye/face protection

Avoid contact with eyes.

Skin protection

Use gloves if handling large quantities.

Respiratory protection

Not typically necessary.

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties

Appearance/form (physical state, color, etc.)

Tan to brown

Odor Dependant on fragrance variant.

Odor threshold Not available PH Not applicable Melting point/freezing point Not available

Initial boiling point and boiling range

Flash point

Not available

Not applicable

>204F

Evaporation rate Not available Flammability (solid, gas) Not flammable Upper/lower flammability limits Not available

Version: 1.0, Date of issue: 2018-11-26, p. 3 of 5

Vapor pressure Not available Vapor density Not available Relative density Not available Solubility(ies) Not applicable Partition coefficient: n-octanol/water Not available Auto-ignition temperature Not applicable Decomposition temperature Not available Viscosity Not applicable Explosive properties Not available Oxidizing properties

SECTION 10: Stability and reactivity

10.2 Chemical stability

Stable at room temperature and in recommended storage conditions.

10.4 Conditions to avoid

Excessive heat/cold.

SECTION 11: Toxicological information

Information on toxicological effects

Skin corrosion/irritation

May cause skin irritation or an allergic skin reaction.

Serious eye damage/irritation

May cause eye irritation.

Respiratory or skin sensitization

Does not cause respiratory sensitization under recommended use.

SECTION 12: Ecological information

Persistence and degradability

Readily biodegradable.

SECTION 13: Disposal considerations

Disposal of the product

Dispose in accordance with local, state, national, and federal regulations.

Disposal of contaminated packaging

Dispose in accordance with local, state, national, and federal regulations.

SECTION 14: Transport information

DOT (US)

Not dangerous goods

IMDG

Not dangerous goods

IATA

Not dangerous goods

SECTION 15: Regulatory information

HMIS Rating

Original Deodorizing Super Sock	
HEALTH	1
FLAMMABILITY	0
PHYSICAL HAZARD	0
PERSONAL PROTECTION	

NFPA Rating



SECTION 16: Other information