SAFETY DATA SHEET

#### **SECTION 1: Identification**

1.1 Product identifier

Product name Highly Concentrated Extraction Cleaner 2001

1.4 Supplier's details

Name HOSPECO

Address 10966 Industrial Parkway

Bolivar OH 44612

Telephone 330-874-1017

1.5 Emergency phone number(s)

US, Canada: 800-255-3924. International: +01-813-248-0585

#### **SECTION 2: Hazard identification**

#### 2.1 Classification of the substance or mixture

GHS classification in accordance with: OSHA (29 CFR 1910.1200)

- Eye damage/irritation, Cat. 1
- Sensitization, skin, Cat. 1
- Skin corrosion/irritation, Cat. 2

#### 2.2 GHS label elements, including precautionary statements

**Pictogram** 



Signal word Danger

Hazard statement(s)

H315 Causes skin irritation

H317 May cause an allergic skin reaction
H318 Causes serious eye damage

Precautionary statement(s)

P261 Avoid breathing dust/fume/gas/mist/vapors/spray.

SAFETY DATA SHEET

P264 Wash exposed areas thoroughly after handling.

P272 Contaminated work clothing must not be allowed out of the workplace.

P280 Wear eye protection/face protection/protective gloves.

P302+P352 IF ON SKIN: Wash with plenty of water.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses if present and easy to do. Continue rinsing.

P332+P313 If skin irritation occurs: Get medical advice/attention.

P333+P313 If skin irritation or rash occurs: Get medical advice/attention. P362+P364 Take off contaminated clothing and wash it before reuse.

P363 Wash contaminated clothing before reuse.

#### **SECTION 3: Composition/information on ingredients**

#### 3.2 Mixtures

#### **Hazardous components**

#### 1. Sodium metasilicate pentahydrate

Concentration > 0 - < 5 % (weight)

Skin corrosion/irritation, Cat. 1BEye damage/irritation, Cat. 1

H314 Causes severe skin burns and eye damage

H318 Causes serious eye damage

#### 2. Nonionic Surfactant

Concentration > 0 - < 5 % (weight)

- Eye damage/irritation, Cat. 1

- Hazardous to the aquatic environment - acute hazard, Cat. 2

- Hazardous to the aquatic environment - long-term hazard, Cat. 3

- Skin corrosion/irritation, Cat. 2

H315 Causes skin irritation

H318 Causes serious eye damage

H401 Toxic to aquatic life

H412 Harmful to aquatic life with long lasting effects

#### 3. D-Limonene

Concentration > 0 - < 5 % (weight)

EC no. 227-813-5 CAS no. 5989-27-5

Aspiration hazard, Cat. 1Flammable liquids, Cat. 3

- Hazardous to the aquatic environment - acute hazard, Cat. 1

Version: 1.0, Date of issue: 2019-09-18, p. 2 of 7

SAFETY DATA SHEET

- Hazardous to the aquatic environment - long-term hazard, Cat. 1

- Sensitization, skin, Cat. 1

- Skin corrosion/irritation, Cat. 2

H226 Flammable liquid and vapor

H304 May be fatal if swallowed and enters airways

H315 Causes skin irritation

H317 May cause an allergic skin reaction

H400 Very toxic to aquatic life

H410 Very toxic to aquatic life with long lasting effects

#### 4. Aklyl Ether Phosphate

Concentration > 0 - < 5 % (weight)

- Skin corrosion/irritation, Cat. 1B

- Eye damage/irritation, Cat. 1

- Hazardous to the aquatic environment, short-term (acute), Cat. 3

H314 Causes severe skin burns and eye damage

H318 Causes serious eye damage

H402 Harmful to aquatic life

#### 5. Fragrance

Concentration > 0 - < 5 % (weight)

- Flammable liquids, Cat. 3

- Acute toxicity, dermal, Cat. 5

- Acute toxicity, inhalation, Cat. 5

- Acute toxicity, oral, Cat. 5

- Aspiration hazard, Cat. 1

- Skin corrosion/irritation, Cat. 2

- Sensitization, skin, Cat. 1B

- Eye damage/irritation, Cat. 2A

H226 Flammable liquid and vapor H303 May be harmful if swallowed

H304 May be fatal if swallowed and enters airways

H313 May be harmful in contact with skin

H315 Causes skin irritation

H317 May cause an allergic skin reaction
H319 Causes serious eye irritation
H333 May be harmful if inhaled

#### **SECTION 4: First-aid measures**

#### 4.1 Description of necessary first-aid measures

Version: 1.0, Date of issue: 2019-09-18, p. 3 of 7

SAFETY DATA SHEET

If inhaled Move to fresh air.

In case of skin contact Wash with water and soap as a precaution.

In case of eye contact Rinse immediately with plenty of water for at least 15 minutes.

If swallowed Prevent aspiration of vomit. Turn victim's head to the side.

#### **SECTION 5: Fire-fighting measures**

#### 5.1 Suitable extinguishing media

Carbon dioxide (CO2).

Dry chemical.

Dry sand.

Limestone powder.

#### 5.3 Special protective actions for fire-fighters

Use personal protective equipme

#### **SECTION 6: Accidental release measures**

#### 6.1 Personal precautions, protective equipment and emergency procedures

Evacuate personnel to safe areas.

#### 6.2 Environmental precautions

Construct a dike to prevent spreading.

#### 6.3 Methods and materials for containment and cleaning up

Place in appropriate chemical waste container.

#### **SECTION 7: Handling and storage**

#### 7.1 Precautions for safe handling

Use personal protective equipment. When using, do not eat, drink or smoke.

#### 7.2 Conditions for safe storage, including any incompatibilities

Keep away from direct sunlight and store in inert environment.

#### **SECTION 8: Exposure controls/personal protection**

#### 8.1 Control parameters

1. D-Limonene (CAS: 5989-27-5 EC: 227-813-5)

TLV® (Inhalation): 20 ppm (ACGIH)

#### 8.3 Individual protection measures, such as personal protective equipment (PPE)

#### Eye/face protection

Chemical safety glasses.

Version: 1.0, Date of issue: 2019-09-18, p. 4 of 7

SAFETY DATA SHEET

#### Skin protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

#### Respiratory protection

Not required for properly ventilated areas.

#### **SECTION 9: Physical and chemical properties**

#### Information on basic physical and chemical properties

Appearance/form (physical state, color, etc.) Yellow liquid

Odor Citrus

Odor threshold No data available

10.0-12.0 Hq

Melting point/freezing point No data available Initial boiling point and boiling range No data available

Flash point >200F

Evaporation rate No data available Flammability (solid, gas) Not flammable Upper/lower flammability limits No data available Vapor pressure No data available

Vapor density No data available Relative density 1.01-1.03 Solubility(ies)

Partition coefficient: n-octanol/water No data available Auto-ignition temperature No data available Decomposition temperature No data available

Water

Viscosity As water

Explosive properties No data available Oxidizing properties No data available

#### **SECTION 10: Stability and reactivity**

#### 10.2 Chemical stability

Stable under normal conditions.

#### 10.4 Conditions to avoid

Stong acids and oxidizing agents

#### **SECTION 11: Toxicological information**

#### Information on toxicological effects

#### Skin corrosion/irritation

Moderate skin irritation.

SAFETY DATA SHEET

#### Serious eye damage/irritation

Severe eye irritation.

#### Respiratory or skin sensitization

May cause a sensitization reaction.

#### Carcinogenicity

This product contains no listed carcinogens according to IARC, ACGIH, NTP and/or OSHA in concentrations of 0.1 percent or greater.

#### **SECTION 12: Ecological information**

#### Persistence and degradability

Biodegradable

#### **SECTION 13: Disposal considerations**

#### Disposal of the product

Dispose of container and unused contents in accordance with federal, state, and local requirements.

#### Disposal of contaminated packaging

Dispose of container and unused contents in accordance with federal, state, and local requirements.

#### **SECTION 14: Transport information**

#### DOT (US)

Not dangerous goods

#### **IMDG**

Not dangerous goods

#### IATA

Not dangerous goods

#### **SECTION 15: Regulatory information**

#### 15.1 Safety, health and environmental regulations specific for the product in question

#### **SARA 302 Components**

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

#### **SARA 313 Components**

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

#### SARA 311/312 Hazards

Fire Hazard, Acute Health Hazard, Chronic Health Hazard

# Highly Concentrated Extraction Cleaner 2001 SAFETY DATA SHEET

#### **Massachusetts Right To Know Components**

D-Limonene

#### Pennsylvania Right To Know Components

D-Limonene

#### **New Jersey Right To Know Components**

D-Limonene

#### California Prop. 65 Components

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

#### **HMIS Rating**

Highly Concentrated Extraction Cleaner	
2001	
HEALTH	2
FLAMMABILITY	0
PHYSICAL HAZARD	0
PERSONAL PROTECTION	

#### **NFPA Rating**



#### **SECTION 16: Other information**

This Safety Data Sheet is offered solely for your information, consideration and investigation. There are no warranties, either expressed or implied and no responsibility is assumed for the accuracy or completeness of the data contained herein.