

The World's TOUGHEST Fire Hose

COLORS:



JAFx4

- Revolutionary co-extrusion technology creates a “Four Layer Hose In One Operation” without the use of glues or adhesives thereby forming a homogeneous hose which cannot delaminate.
- Resists burn-through
- Super resistant to abrasion
- UL19 & Can/ULC-S511-14 Certified – 1 1/2", 1 3/4", 2", 2 1/2"
- Excellent resistance to heat, ozone, weather, most chemicals (acids, bases, salts, oils, solvents, etc.), flame, wear, tear and puncture.
- Highly flexible and smooth inner lining provides excellent dilation characteristics with low friction loss and high kinking resistance.
- Meets or exceeds NFPA Standard on Fire Hose (current edition)
- 10 year warranty

Applications –

- Active Municipal Departments
- Heavy Industrial Municipalities
- Refining, Chemical, Utility Industries
- Coarse, Abrasive Landscapes
- Marine Environments
- Daily Use Applications such as washdown and sewage treatment plants

Lengths – Available in 50' and 100' lengths.



Size (in)	Bowl Size (in)	Service Test PSI	Proof Test PSI	Burst Test PSI	Weight (lbs/ft) Uncoupled
1	1 3/16	580	1160	1740	0.160
1 1/2	1 3/4	300	600	900	0.296
1 3/4	2 1/16	300	600	900	0.343
2	2 9/32	300	600	900	0.390
2 1/2	2 13/16	300	600	900	0.517
4	4 17/32	250	500	750	0.874
5	5 3/8	250	500	750	1.109

ATIIX4FL0319

ATI reserves the right to modify any specification without prior notice to meet or exceed changing standards. Special diameters or construction characteristics can be produced upon special request. Contact your local dealer or ATI at: sales@atifireproducts.com