### FR FEL SERIES CONTAINERS






## Toter®

#### **NEW TOTER FR SERIES**

- Steel rod reinforcement and ribbed bottom wear chimes for enhanced durability
- Double-walled lift pockets to distribute weight for maximum pocket strength
- Integrated bumpers to protect the container for long life
- Graphic space available for custom signage







Replaceable, double-walled lift pockets for easy maintenance



Optional comfort & grip handles for easy maneuverability



Replaceable double-walled bumpers for long-lasting durability







#### STACKABLE DESIGN **SAVES ON SPACE**



- Stackable when fully assembled
- Shipped unassembled for better truckload efficiency

					Unassembled		Assembled	
Part	Description	Size (L x D x H)	Load Rating	Weight	Containers Per Stack	53' t/l Quantity	Containers Per Stack	53' t/l Quantity
FR010	1-cubic-yard FEL*	82.3" x 38.0" x 38.8"	750 lbs/ 340.91 kg	192 lbs.	6	96	4	60
FR020	2-cubic-yard FEL*	82.3" x 43.1" x 52.8"	1,000 lbs/ 454.55 kg	231 lbs.	5	80	3	45
FR030	3-cubic-yard FEL*	82.3" x 51.1" x 61.9"	1,500 lbs/ 681.8 kg	280 lbs.	4	64	2	24
FR040	4-cubic-yard FEL	82.3" x 60.5" x 67.4"	2,000 lbs/ 909.1 kg	315 lbs.	3	30	2	20

<sup>\*</sup>Dimensions include casters.

Part	Post-Mold Graphic	Drain Plug	Lock Bar (Manual or Automatic)	No Casters	6" Standard Casters (2 Swivel, 2 Rigid)	6" Standard Casters (All Swivel)	6" HD Casters (2 Swivel, 2 Rigid or All Swivel)	8" Standard Casters (All Swivel)	Caster Mounting Pads Only	Bumpers
FR010	•	•	•	•	S	•	•	•	•	S
FR020	•	•	•	•	S	•	•	•	•	S
FR030	•	•	•	•	S	•	•	•	•	S
FR040	•	•	•	S	•	•	•	•	•	S

S = standard • = optional

#### STANDARD COLORS

















Colors shown are as accurate as printing allows. Actual product colors are subject to variation from printed sample.



# Toter<sup>®</sup>

**Built for Extremes®** 

PO Box 5338 841 Meacham Road Statesville, NC 28677 844-556-6677 sales@wastequip.com www.toter.com