



50-3 Air Hydraulic Jack

50/25/10 Ton Air Hydraulic Jack

- 3-stage air hydraulic jack for low buses and other low clearance vehicles
- Minimum height of only 150 mm combined with a high lifting capacity
- Telescopic cylinders ensure an excellent maximum lift together with a low closed height
- Designed for heavy-duty, intensive commercial use
- Built-in safety overload valve



Specifications	
Capacity	50 / 25 / 10 Tons
Min. Height	5.9" (150mm)
Max Height	8.2" / 10.4" / 13.1" (210 / 265 / 335 mm)
Frame Length	31.9" (810)
Handle Legth	45.7" (1160mm)
Width (with wheels)	12.2" (310mm)
Air supply	9-10 bar
Air Consumption	350 l/min
Weight	147.7 lbs (67kg)

