


OPH-P HIGH PRECISION BALANCE



FEATURES

- Designed for every day laboratory routines
- Built in glass draftshield for maximum stability
- Splashproof keyboard and display
- High contrast LCD screen
- Stainless steel weighing pan and draft ring are removable for easy clean up
- Automatic zero tracking and full range tare
- Calibration with reference weights
- Parts counting, percent weighing and dynamic weighing
- Cast aluminum construction, static resistant ABS, static resistant doors, stainless steel pan and leveling feet
- Configurable RS232 interface
- Multiple weighing units: g, kg, ct, lb, oz, ozt, dwt, pcs, tls, tIT, tIH, GN(grain), dr, ms, bat, mom T/A/R

SPECIFICATIONS

- READABILITY:**
0.0001g, 0.001g
- REPEATABILITY:**
±0.0001g, ±0.001g
- LINEARITY:**
±0.0002g, ±0.002g
- STABILIZATION TIME:**
2 seconds (typically)
- SENSITIVITY:**
2ppm / (10 --30)
- POWER (AC ADAPTER):**
Input 110V-240VAC, 50HZ/60HZ
- BAUD OPTIONS:**
300/600/2400/4800/9600
- AMBIENT TEMPERATURE:**
40°F - 110°F
- KEYPAD:**
8 keys, splash-proof
- WARRANTY:**
1 year limited warranty

PART #	CAPACITY	DIMENSIONS	PAN SIZE	SHIP WT.
OPH-P104	100 g x 0.0001 g	13.5" L x 8.75" W x 13" H	Φ3.5"	9 lbs
OPH-P204	200 g x 0.0001 g	13.5" L x 8.75" W x 13" H	Φ3.5"	9 lbs
OPH-P103	100 g x 0.001 g	13.5" L x 8.75" W x 13" H	Φ3.5"	9 lbs
OPH-P203	200 g x 0.001 g	13.5" L x 8.75" W x 13" H	Φ3.5"	9 lbs
OPH-P303	300 g x 0.001 g	13.5" L x 8.75" W x 13" H	Φ3.5"	9 lbs
OPH-P1003	1,000 g x 0.001 g	13.5" L x 8.75" W x 13" H	Φ4.25"	9 lbs
OPH-P2003	2,000 g x 0.001 g	13.5" L x 8.75" W x 13" H	Φ4.25"	9 lbs

