



High Grade Fire-Retardant ABS Hand Dryer

Model: HD0903

Model #	Color	
HD0903-17	White	<input type="checkbox"/>
Width: 10.50"	Height: 8.75"	Depth: 6.75"
Weight: 8.4 lbs	Material: ABS Plastic	
Motor Type: 1/8 HP, Brushless, 100W		
Thermal Protection: Heater Shuts Off at 286°F (141°C)		Operating Airflow: 3,242 LFM
Air Output Temperature: 136°F (58°C); Ambient Temperature 68°F (20°C)		
Sound Level: 55±3dB	Isolation: Class 1	
Drip Proof: IPX1	Watts: 1800W	RPM: 2,850
Voltage & Amps: 110/120V / 13.8-15 Amps		



Painted Cast Aluminum Hand Dryer

Model: HD0907

Model #	Color	
HD0907-17	White	<input type="checkbox"/>
Width: 9.75"	Height: 8.75"	Depth: 6.75"
Weight: 11.2 lbs	Material: Aluminum	
Motor Type: Brushless, 100W		
Thermal Protection: Heater Shuts Off at 136°F (58°C)		Operating Airflow: 3,242 LFM
Air Output Temperature: 136°F (58°C); Ambient Temperature 68°F (20°C)		
Sound Level: 55±3dB	Isolation: Class 1	
Drip Proof: IPX1	Watts: 1800W	RPM: 2,850
Voltage & Amps: 110/120V / 13.8-15 Amps		



Conventional Series Hand Dryer

Model: HD0901

Model #	Color	
HD0903-11	Brushed Chrome	<input type="checkbox"/>
HD0901-17	White	<input type="checkbox"/>
Width: 11.1875"	Height: 9.75"	Depth: 8"
Weight: 15.4 lbs	Material: Steel	
Motor Type: 1/4 HP, Brushless, 200W		
Thermal Protection: Motor Shuts Off at 221°F (105°C) Heater Shuts Off at 149°F (65°C)		Operating Airflow: 5,514 LFM
Air Output Temperature: 137°F (58°C); Ambient Temperature 68°F (20°C)		
Sound Level: 70±3dB	Isolation: Class 1	
Drip Proof: IPX1	Watts: 1800-2200W	RPM: 5,500
Voltage & Amps: 110/120V / 18.3-20 Amps		