

OPF-N PRECISION BALANCE



SPECIFICATIONS

READABILITY: 0.1g, 0.2g, 0.5g, 1g
REPEATABILITY: $\pm 0.1g$, 0.2g, 0.5g, 1g
LINEARITY: $\pm 0.2g$, 0.4g, 1g, 2g
RESPONSE TIME: 3 seconds
POWER (AC ADAPTER):
 Input 100V-240V AC
 Output 6vDC-9vDC/600mA
BAUD OPTIONS:
 300/600/2400/4800/9600
AMBIENT TEMPERATURE:
 40°F - 110°F
KEYPAD: 4 keys, splash-proof
WARRANTY:
 1 year limited warranty

FEATURES

- Large removable, anti-static stainless steel weighing platform
- Comes with a 9V rechargeable battery
- Large high contrast backlit LCD screen
- Splash-proof keyboard and display
- Automatic zero tracking and full range tare
- Calibration with reference weights
- Percent weighing and dynamic weighing
- Multiple weighing units: g, kg, lb, oz

PART#	CAPACITY	DIMENSIONS	PAN SIZE	SHIP WT.
OPF-N3	3 kg x 0.1 g	12.5" L x 10.5" W x 5.5" H	11" x 8.5"	10 lbs
OPF-N7.5	7.5 kg x 0.2 g	12.5" L x 10.5" W x 5.5" H	11" x 8.5"	10 lbs
OPF-N15	15 kg x 0.5 g	12.5" L x 10.5" W x 5.5" H	11" x 8.5"	10 lbs
OPF-N30	30 kg x 1 g	12.5" L x 10.5" W x 5.5" H	11" x 8.5"	10 lbs

