

PRODUCT DATA SHEET

Part Number	332
EAN	
Manufacturer	Walther-Werke
WEEE-Reg-Nr:	DE 22131895

30A IEC 60309 Coupler, 3-PH, 5 Wire

- High impact thermoplastic housing featuring high resistance
 And toughness creating an abrasion-resistant material
- Cable gland with "onion ring" neoprene bushing
- Retaining device
- Internal strain relief with "swing-away" feature
- Locking ring and gasket
- Zinc electroplated steel screws
- Shrouded pins
- Color coded by voltage
- Double terminal screws on all amperage devices
- Ground first to mate last to break for added safety
- Walther can produce and supply the mating cable assemblies.



Ordering/Logistics Information

Order Unit	Piece
Customs Number	
Net Weight	0.62 lbs or 0.28 kg
Packing Quantity (VPE)	10
Packaging Length	12.21 in or 0.31 m
Packaging Width	7.68 in or 0.195 m
Packaging Depth	5.51 in or 0.14 m
Gross Weight (VPE)	6.61 lbs or 2.996 kg

Certification


UL certification E329476


And multiple international certification



Technical Product Data

IEC-amperage	32 A			
Amperage according to UL/CSA (for UL-version)	30 A			
Number of poles and wires	3P+N+G			
Voltage according to EN 60309-2	400 V (50+60Hz) red			
Clock hour position	6 h			
Identification color	Red			
Maximum Cable diameter	1.10 in or 27.95 mm			
Cable strip length	1 .77 in +/- 0.1 in or 45 mm +/- 2.5 mm			
Maximum torque terminal screw	0.8 Nm			
Degree of protection (IP)	IP44			
Connection system	Screwed terminal			
Contact material	Nickel-plated brass			
Cable entry	Swivel			
Angle of plug	Straight			
Material	Plastic			
Inflammability class of insulation material according to with UL94	V2			





Amp. Pole	16			32			63		
	3	4	5	3	4	5	3	4	5
d	135	151	151	171	171	171	255	255	255
Øe	51	65	65	72	72	72	96	96	96
1	68	85	85	91	91	98	114	114	114
m	110	113	113	136	136	136	194	194	194

All specifications are subject to change without notice. Consult a Walther Electric Engineer for the latest specifications or speak with a member of our Customer Care Team +1 (800) 925-8437.