

## OP-915BW PORTABLE BENCH SCALES



ALL STAINLESS  
STEEL



STANDARD  
DIAMOND PLATE



STANDARD  
WITH SS COVER

### FEATURES

- Convenient portable weighing platform with wheels
- Easily moves in any work area
- 27.5" backrail for pushing or pulling
- Swivel wheel casters come with brakes in the back
- High accuracy stainless steel load cells
- Rechargeable batter (up to 100 hrs)
- Hinged indicator bracket
- IP Rating: Standard- IP65, Stainless Steel- IP67
- Legal for Trade: NTEP approved CC# 11-016
- Measurement Canada CC# AM-5817

PART #	DESCRIPTION	CAPACITY	PLATFORM SIZE	SHIP WT.
<b>STANDARD (INC. INDICATOR AND COLUMN)</b>				
OP-915BW-1824-500	Mild Steel Platform / Stainless Steel Cover	500 lb x 0.1 lb	18" x 24" x 10" H	92 lbs
OP-915BWDP-1824-500	Mild Steel Platform / Diamond Plate Cover	500 lb x 0.1 lb	18" x 24" x 10" H	94 lbs
OP-915BW-2424-1000	Mild Steel Platform / Stainless Steel Cover	500 lb x 0.1 lb	24" x 24" x 10" H	106 lbs
OP-915BWDP-2432-1000	Mild Steel Platform / Diamond Plate Cover	1,000 lb x 0.2 lb	24" x 32" x 10" H	149 lbs
<b>STAINLESS STEEL WASHDOWN (INC. INDICATOR AND COLUMN)</b>				
OP-915SSBW-1824-500	All Stainless Steel	500 lb x 0.1 lb	18" x 24" x 10" H	78 lbs
OP-915SSBW-2424-500	All Stainless Steel	500 lb x 0.1 lb	24" x 24" x 10" H	95 lbs

