

OP-916-SS STAINLESS STEEL HEAVY DUTY FLOOR SCALES



Diamond Plate Top



Smooth Top

FEATURES

- 304 stainless steel construction
- Channel construction for superior strength
- NEMA 4X watertight stainless steel junction box
- Side access to junction box to minimize water access
- Four NTEP certified laser welded and sealed IP68 stainless steel load cells
- Load cell capacity is 2X the scale capacity for a 200% overload protection
- Four adjustable stainless steel ball capture support feet
- 20' heavy duty stainless steel shielded cable
- Factory pre-calibrated for quick setup

OPTIONS/ACCESSORIES:

- Access ramps
- Pit frames
- Impact Protection
- Portability frames
- Thermal printer
- Stand for indicator
- Large Display
- Data logging software
- Remote junction box
- Wireless option
- Explosion proof option



OP-900B-SL Stainless Steel
NEMA-4X Washdown Indicator

PART#	PLATFORM SIZE	CAPACITY	NTEP	SHIP WT.
SMOOTH TOP				
OP-916SS-2x2-5K	2' x 2' x 4.2" H	5,000 lb x 1 lb / 2,500 kg	Yes	165 lbs
OP-916SS-3x3-5K	3' x 3' x 4.2" H	5,000 lb x 1 lb / 2,500 kg	Yes	275 lbs
OP-916SS-4x4-5K	4' x 4' x 4.2" H	5,000 lb x 1 lb / 2,500 kg	Yes	350 lbs
OP-916SS-4x4-10K	4' x 4' x 4.2" H	10,000 lb x 2 lb / 5,000 kg	Yes	395 lbs
OP-916SS-5x5-5K	5' x 5' x 4.2" H	5,000 lb x 1 lb / 2,500 kg	Yes	540 lbs
OP-916SS-5x5-10K	5' x 5' x 4.2" H	10,000 lb x 2 lb / 5,000 kg	Yes	625 lbs
DIAMOND PLATED TOP				
OP-916SSDP-3x3-5K	3' x 3' x 4.2" H	5,000 lb x 1 lb / 2,500 kg	Yes	270 lbs
OP-916SSDP-4x4-5K	4' x 4' x 4.2" H	5,000 lb x 1 lb / 2,500 kg	Yes	350 lbs
OP-916SSDP-4x4-10K	4' x 4' x 4.2" H	10,000 lb x 2 lb / 5,000 kg	Yes	395 lbs
OP-916SSDP-5x5-5K	5' x 5' x 4.2" H	5,000 lb x 1 lb / 2,500 kg	Yes	540 lbs
OP-916SSDP-5x5-10K	5' x 5' x 4.2" H	10,000 lb x 2 lb / 5,000 kg	Yes	625 lbs

