

Safety Data Sheet

Issue Date: 03-Feb-1992

Revision Date: 29-Jan-2015

Version 1

1. IDENTIFICATION

Product Identifier

Product Name AF-6800 Conduct Coat Anti-Static Floor Finish

Other means of identification

SDS # DYNI-001

Recommended use of the chemical and restrictions on use

Recommended Use Floor finish/floor coating.

Details of the supplier of the safety data sheet

Supplier Address

Static Solutions
43 Broad Street
Hudson, MA 01749

Emergency Telephone Number

Company Phone Number

Phone: 978-310-7251

Fax: 978-310-7146

Emergency Telephone (24 hr)

INFOTRAC 1-352-323-3500 (International)

1-800-535-5053 (North America)

2. HAZARDS IDENTIFICATION

Appearance White liquid

Physical State Liquid

Odor Mild

Classification

Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 2
Reproductive toxicity	Category 2

Signal Word

Warning

Hazard Statements

Causes skin irritation

Causes serious eye irritation

Suspected of damaging fertility or the unborn child



Hazard Statement:

H315 - Causes skin irritation

H319 - Causes serious eye irritation

Precautionary Statements - Prevention

Obtain special instructions before use
Do not handle until all safety precautions have been read and understood

P281 - Use personal protective equipment as required
P264 -Wash face, hands and any exposed skin thoroughly after handling
Wear eye/face protection

Precautionary Statements - Response

If exposed or concerned: Get medical advice/attention
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P337 + P313 If eye irritation persists: Get medical advice/attention

P302 + P352 IF ON SKIN: Wash with plenty of soap and water
P362 Take off contaminated clothing and wash it before reuse
P332 + P313 If skin irritation occurs: Get medical advice/attention

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Other Hazards

Toxic to aquatic life with long lasting effects

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%
Diethylene glycol monomethyl ether	111-77-3	<5
tributoxyethyl phosphate	78-51-3	<3
Zinc Oxide	1314-13-2	<1
Ammonium hydroxide	1336-21-6	<1

If Chemical Name/CAS No is "proprietary" and/or Weight-% is listed as a range, the specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. FIRST-AID MEASURES

First Aid Measures

- General Advice** If exposed or concerned: Get medical advice/attention.
- Eye Contact** Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
- Skin Contact** Wash with plenty of soap and water. Take off contaminated clothing and wash it before reuse. If skin irritation occurs: Get medical advice/ attention.
- Inhalation** Remove to fresh air.
- Ingestion** Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects

Symptoms Causes skin irritation. Causes serious eye irritation. Suspected of damaging fertility or the unborn child.

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Carbon dioxide (CO2). Dry chemical.

Unsuitable Extinguishing Media Not determined.

Specific Hazards Arising from the Chemical

Not determined.

Hazardous Combustion Products Toxic gases may be released.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions Use personal protective equipment as required.

Methods and material for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for Clean-Up Halt spill at source and contain or dike spill with inert absorbent material. Transfer liquid to containers for recovery or disposal. Shovel absorbent into drums for disposal in accordance with local, state and federal regulations.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on Safe Handling Handle in accordance with good industrial hygiene and safety practice. Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Use personal protective equipment as required. Wash face, hands, and any exposed skin thoroughly after handling. Wear eye/face protection.

Conditions for safe storage, including any incompatibilities

Storage Conditions Store locked up.

Incompatible Materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
---------------	-----------	----------	------------

Zinc Oxide 1314-13-2	STEL: 10 mg/m ³ respirable fraction TWA: 2 mg/m ³ respirable fraction	TWA: 5 mg/m ³ fume TWA: 15 mg/m ³ total dust TWA: 5 mg/m ³ respirable fraction (vacated) TWA: 5 mg/m ³ fume (vacated) TWA: 10 mg/m ³ total dust (vacated) TWA: 5 mg/m ³ respirable fraction (vacated) STEL: 10 mg/m ³ fume (vacated)	IDLH: 500 mg/m ³ Ceiling: 15 mg/m ³ dust TWA: 5 mg/m ³ dust and fume STEL: 10 mg/m ³ fume
-------------------------	--	---	--

Appropriate engineering controls

Engineering Controls Showers. Eyewash stations. Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/Face Protection Wear approved safety goggles with side shields.

Skin and Body Protection Wear rubber gloves. Wear protective work clothing.

Respiratory Protection None required in well ventilated areas. An approved organic vapor full face respirator is advised for poorly ventilated areas.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical State	Liquid	Odor	Mild
Appearance	White liquid	Odor Threshold	Not determined
Color	White		

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	8.0-9.0	
Melting Point/Freezing Point	0 °C / 32 °F	
Boiling Point/Boiling Range	100 °C / 212 °F	
Flash Point	Non flammable	
Evaporation Rate	<1 to water	(butyl acetate = 1)
Flammability (Solid, Gas)	Liquid-Not applicable	
Upper Flammability Limits	Not available	
Lower Flammability Limit	Not available	
Vapor Pressure	Not determined	
Vapor Density	<1 to water	(Air=1)
Specific Gravity	Not determined	
Water Solubility	Infinitely miscible	
Solubility in other solvents	Not determined	
Partition Coefficient	Not available	
Auto-ignition Temperature	Greater than 121.1 °C / 250 °F	
Decomposition Temperature	Not determined	
Kinematic Viscosity	20	
Dynamic Viscosity	Not determined	
Explosive Properties	Not determined	
Oxidizing Properties	Not determined	
VOC Content (%)	Less than 5%	

10. STABILITY AND REACTIVITY

Reactivity

Not reactive under normal conditions.

Chemical Stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Under normal conditions of storage and use, hazardous polymerization will not occur.

Conditions to Avoid

Heat, flames and sparks.

Incompatible Materials

None known based on information supplied.

Hazardous Decomposition Products

Toxic gases may be released.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Eye Contact Causes serious eye irritation.

Skin Contact Causes skin irritation.

Inhalation Do not inhale.

Ingestion Do not ingest.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Diethylene glycol monomethyl ether 111-77-3	= 4 mL/kg (Rat)	= 2500 µL/kg (Rabbit)	-
tributoxyethyl phosphate 78-51-3	= 3000 mg/kg (Rat)	> 5000 mg/kg (Rabbit)	> 6.4 mg/L (Rat) 4 h
Zinc Oxide 1314-13-2	> 5000 mg/kg (Rat)	-	-
Ammonium hydroxide 1336-21-6	= 350 mg/kg (Rat)	-	-

Information on physical, chemical and toxicological effects

Symptoms Please see section 4 of this SDS for symptoms.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Carcinogenicity Based on the information provided, this product does not contain any carcinogens or potential carcinogens as listed by OSHA, IARC or NTP.

Reproductive toxicity Suspected of damaging fertility or the unborn child.

Numerical measures of toxicity

Not determined

12. ECOLOGICAL INFORMATION

Ecotoxicity

Toxic to aquatic life with long lasting effects.

Component Information

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Diethylene glycol monomethyl ether 111-77-3	500: 72 h Desmodismus subspicatus mg/L EC50	7500: 96 h Lepomis macrochirus mg/L LC50 static 7500: 96 h Lepomis macrochirus mg/L LC50 5741: 96 h Pimephales promelas mg/L LC50	EC50 > 10000 mg/L 17 h	500: 48 h Daphnia magna mg/L EC50
tributoxyethyl phosphate 78-51-3		10.4 - 12.0: 96 h Pimephales promelas mg/L LC50 flow-through		
Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Ammonium hydroxide 1336-21-6		8.2: 96 h Pimephales promelas mg/L LC50		0.66: 48 h water flea mg/L EC50 0.66: 48 h Daphnia pulex mg/L EC50

Persistence/Degradability

Not determined.

Bioaccumulation

Not determined.

Mobility

Chemical Name	Partition Coefficient
Diethylene glycol monomethyl ether 111-77-3	-0.682
tributoxyethyl phosphate 78-51-3	4.78

Other Adverse Effects

Not determined

13. DISPOSAL CONSIDERATIONS

Waste Treatment Methods

Disposal of Wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated Packaging Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Status

Chemical Name	California Hazardous Waste Status
Zinc Oxide 1314-13-2	Toxic
Ammonium hydroxide 1336-21-6	Toxic Corrosive

14. TRANSPORT INFORMATION

Note

Please see current shipping paper for most up to date shipping information, including exemptions and special circumstances.

DOT Not regulated

IATA Not regulated

IMDG
Marine Pollutant This material may meet the definition of a marine pollutant

15. REGULATORY INFORMATION

International Inventories

Chemical Name	TSCA	DSL	NDSL	EINECS	ELINCS	ENCS	IECSC	KECL	PICCS	AICS
Diethylene glycol monomethyl ether	Present	X		Present		Present	X	Present	X	X
Chemical Name	TSCA	DSL	NDSL	EINECS	ELINCS	ENCS	IECSC	KECL	PICCS	AICS
tributoxyethyl phosphate	Present	X		Present		Present	X	Present	X	X
Zinc Oxide	Present	X		Present		Present	X	Present	X	X
Ammonium hydroxide	Present	X		Present		Present	X	Present	X	X

Legend:

- TSCA - United States Toxic Substances Control Act Section 8(b) Inventory*
- DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List*
- EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances*
- ENCS - Japan Existing and New Chemical Substances*
- IECSC - China Inventory of Existing Chemical Substances*
- KECL - Korean Existing and Evaluated Chemical Substances*
- PICCS - Philippines Inventory of Chemicals and Chemical Substances*
- AICS - Australian Inventory of Chemical Substances*

US Federal Regulations

CERCLA

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Ammonium hydroxide 1336-21-6	1000 lb		RQ 1000 lb final RQ RQ 454 kg final RQ

SARA 313

Chemical Name	CAS No	Weight-%	SARA 313 - Threshold Values %
Diethylene glycol monomethyl ether - 111-77-3	111-77-3	<5	1.0
Zinc Oxide - 1314-13-2	1314-13-2	<1	1.0
Ammonium hydroxide - 1336-21-6	1336-21-6	<1	1.0

CWA (Clean Water Act)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Zinc Oxide		X		
Ammonium hydroxide	1000 lb			X

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Diethylene glycol monomethyl ether 111-77-3	X	X	X
Zinc Oxide 1314-13-2	X	X	X
Ammonium hydroxide 1336-21-6	X	X	X

16. OTHER INFORMATION

<u>NFPA</u>	Health Hazards	Flammability	Instability	Special Hazards
	1	0	0	Not determined
<u>HMIS</u>	Health Hazards	Flammability	Physical Hazards	Personal Protection
	1	0	0	Not determined

Issue Date: 03-Feb-1992
Revision Date: 29-Jan-2015
Revision Note: New format

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet