WEB pyramexsafety.com
PHONE 800.736.8673
FAX 901.861.4967
FACEBOOK facebook.com/pyramexsafety

PYRAMEX

The Peak of Safety and Style

Ballistic Eyewear

• ANSI Z87.1 High Impact; • CE EN166; • Cert. Mod. - CAN/CSA Z94.3-07; • AS/NZS 1337; • MIL-PRF 32432; • H2X Anti-Fog



Ballistic Test
Tested with **0.15 caliber jagged steel** piece projected toward the spectacle at **650 feet per second**.

High Velocity Impact Test
Tested with **round steel ball** projected at **150 feet per second**.



Independent laboratory test results conclude that the following Pyramex eyewear complies with MIL-PRF 32432 Ballistic Fragmentation.

The following high velocity impact tests were performed:
Test A: 0.15 caliber, 5.8 grain projectile at 650 feet per second
Test B: 0.22 caliber, 17 grain at 550 feet per second

Class 1 = Spectacle (Test A)
Class 2 = Goggle (Test B)
Class 3 = Hybrid Goggle (Test B)



I-Force® & I-Force Slim Class 3

- Quick Release interchangeable temples and strap.
- Vented foam carriage.
- Dual pane lens provides the ultimate anti-fog performance.
- Outer polycarbonate lens protects against the environment, while inner acetate lens is designed to prevent fogging.
- Outside lens is coated with Anti-fog Technology.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Frame with Temples and Strap

I-Force	I-Force Slim	Lens	
Part	**Part**		
SB7010SDT	SB7010SDNT		Clear H2X Anti-Fog Dual Pane
SB7020SDT	SB7020SDNT		Gray H2X Anti-Fog Dual Pane
SB7025SDT	—		Light Gray H2X Anti-Fog Dual Pane
SB7030SDT	SB7030SDNT		Amber H2X Anti-Fog Dual Pane
SB7070SDT	—		Silver Mirror Anti-Fog Dual Pane
SB7080SDT	SB7080SDNT		Indoor/Outdoor Mirror Anti-Fog Dual Pane



V2G® Class 3

- Lens and frame vented to increase air flow.
- Headband and temples feature ratchet adjustment for perfect fit, features quick fit retainer.
- Interchangeable temples and headband included.
- Flame resistant foam padding.
- 9.75 base curved lens provides full side protection.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Frame with Temples and Strap

Part	Lens
GB1810ST	Clear H2X Anti-Fog
GB1820ST	Gray H2X Anti-Fog
GB1830ST	Amber H2X Anti-Fog
GB1850SFT	5.0 IR Filter H2X Anti-Fog
GB1860SFT	3.0 IR Filter H2X Anti-Fog



V2G-Plus™ Class 2

- Includes a wide adjustable elastic strap with quick release system for secure fit.
- TPU frame features excellent resistance to cold and heat.
- Thermo Lens System provides excellent resistance to fogging caused by temperature difference between indoor and outdoor or between on-site and ambient environment.
- Special indirect ventilation system located at the top and bottom of frame allow air flow and heat release.
- Multi-functional goggle with 180° vision, protects against chemical splash, sun glare, dust, flying particles, wind.
- Outer polycarbonate lens protects against the environment, while an inner lens prevents fogging.
- Inner lens is made from acetate, separated by a thin spacer of air, sealed together with foam.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Goggle with Strap

Part	Lens
GB6410SDT	Clear H2X Anti-Fog Dual Lens
GB6420SDT	Gray H2X Anti-Fog Dual Lens

• ANSI Z87.1 High Impact; • CE EN166; • Cert. Mod. - CAN/CSA Z94.3-07; • AS/NZS 1337; • MIL-PRF 32432; • H2X Anti-Fog

Ballistic Eyewear

WEB pyramexsafety.com
PHONE 800.736.8673
FAX 901.861.4967
FACEBOOK facebook.com/pyramexsafety

PYRAMEX

The Peak of Safety and Style





V3G® Class 3

- Lens and frame vented to increase air flow.
- Interchangeable temples and headband included.
- Headband and temples feature ratchet adjustment and quick fit retainer.
- Flame resistant foam padding
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Frame with Temples and Strap

Part	Lens
GB8210ST•	Clear H2X Anti-Fog
GB8210STK•	Clear H2X Ultra Anti-Fog
GB8220ST•	Gray H2X Anti-Fog
GB8230ST•	Amber H2X Anti-Fog
GB8280ST•	Indoor/Outdoor Mirror Anti-Fog

The prescription model of the V3G has a larger lens to accomodate the RX8200 lens insert (sold separately).

Black Frame with Temples and Strap

Part	Lens
GB8210STRX•	Clear H2X Anti-Fog



XSG® Kit Class 3

Black Frame with Temples and Strap

GB4010KIT•

Clear Ballistic, Gray Ballistic and Amber Ballistic Interchangeable Lenses. All lenses are anti-fog. Black Ballistic Nylon Case for storage. Interchangeable temples included. Passes MIL-PRF 32432 High Velocity Impact Standards.



Class 2

Capstone® 500 Series

- Dual purpose goggle adaptable to many different applications.
- Removable vent caps allow the user to remove when more ventilation is required.
- Lens is coated to prevent fogging.
- Soft PVC body conforms to facial contours.
- Fits over prescription glasses.
- Scratch resistant polycarbonate lens provides 99% UVA/B/C protection.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Gray Goggle with Quick Release Strap

Part	Lens
GG504T•	Clear H2X Anti-Fog



Class 2

Capstone® 600 Series

- Modern co-material goggle provides superior protection against dust entry and chemical splash.
- Thermoplastic (TPE) body with universal nose bridge is flexible and contours to the user's face.
- Indirect ventilation system prevents fogging.
- Includes interchangeable cloth and neoprene straps.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Gray Goggle with Adjustable Strap

Part	Lens
G604T2•	Clear H2X Anti-Fog



Class 2

Capstone® Dual Lens

- Indirect-vent frame provides protection against chemical splash and dust.
- Soft vinyl goggle body.
- Double lens consists of polycarbonate lens on the outer side with acetate anti-fog lens on inner side.
- Dual pane lens ensures ultimate anti-fog performance.
- Fits over prescription glasses.
- Removable vent caps.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Gray Goggle with Adjustable Elastic Strap

Part	Lens
G504DT•	Clear Dual Pane H2X Anti-Fog Lens



Highlander™ Plus Class 1

- Indirect vented foam carriage.
- Resilient and durable frame features an extended side shield design.
- Detachable strap for temple option.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black and Gray Frame with Strap

Part	Lens
SBG5010DT•••••	Clear H2X Anti-Fog
SBG5020DT•••••	Gray H2X Anti-Fog
SBG5030DT•••••	Amber H2X Anti-Fog
SBG5055DT•••	Sky Red Mirror Anti-Fog
SBG5080DT•••	Indoor/Outdoor Mirror Anti-Fog



Venture 3® Class 1

- Ventilated nose piece is soft and adjustable.
- Top of frame is ventilated allowing air to circulate.
- Soft dual-injected rubber temple tips combined with fully adjustable straight back temples.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Frame

Part	Lens
SB5710D••••	Clear
SB5710DT•••••••	Clear H2X Anti-Fog
SB5720D••••	Gray
SB5720DT•••••••	Gray H2X Anti-Fog
SB5730D•••••	Amber
SB5760D••••	Infinity Blue
SB5770D•••••	Silver Mirror
SB5770DT•••••	Silver Mirror Anti-Fog
SB5780D••••	Indoor/Outdoor Mirror
SB5750SFT••••	5.0 IR Filter H2X Anti-Fog
SB5760SFT••••	3.0 IR Filter H2X Anti-Fog



Venture II® Class 1

- Temples adjust to four different lengths.
- Nose buds secure the glass and prevent slipping.
- 9.75 base curved lens provides full side protection without distracting seams or traditional type side shields.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Frame

Part	Lens
SB1810S•••••	Clear
SB1810ST•••••••	Clear H2X Anti-Fog
SB1820S•••••	Gray
SB1820ST•••••••	Gray H2X Anti-Fog
SB1830S•••	Amber
SB1835S•••••	Sun Block Bronze
SB1840S•••••	Orange
SB1860S•••••	Infinity Blue
SB1870S•••••	Silver Mirror
SB1875S•••	Blue Mirror
SB1880S•••••	Indoor/Outdoor Mirror
SB1880ST•••	Indoor/Outdoor Mirror Anti-Fog
SB1890S•••	Gold Mirror
SB1850SF•••••	5.0 IR Filter
SB1860SF•••••	3.0 IR Filter

Realtree Hardwoods® HD Frame

SH1810S••	Clear
SH1820S••	Gray
SH1830S••	Amber

Metallic Blue Frame

SMB1810S•••	Clear
SMB1820S••	Gray
SMB1880S••	Indoor/Outdoor Mirror

Maroon Frame

SMM1810S•••	Clear

Slate Gray Frame

SSG1810S•••	Clear

• ANSI Z87.1 High Impact; • CE EN166; • Cert. Mod. - CAN/CSA Z94.3-07; • AS/NZS 1337; • MIL-PRF 32432; • H2X Anti-Fog

Ballistic Eyewear

WEB pyramexsafety.com
PHONE 800.736.8673
FAX 901.861.4967
FACEBOOK facebook.com/pyramexsafety

PYRAMEX

The Peak of Safety and Style



Rendezvous® Class 1

- Adjustable nose pad.
- Lens/frame design allows air to flow freely.
- Temples adjust to four different lengths.
- Align lens angle to proper position for work application with ratcheting lens pitch adjustment.
- 9.5 base curve lens.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Frame

Part	Lens
SB2810S	Clear
SB2810ST	Clear H2X Anti-Fog
SB2815S	Coffee
SB2820S	Gray
SB2820ST	Gray H2X Anti-Fog
SB2830S	Amber
SB2840S	Orange
SB2860S	Infinity Blue
SB2860ST	Infinity Blue H2X Anti-Fog
SB2870S	Silver Mirror
SB2875S	Blue Mirror
SB2880S	Indoor/Outdoor Mirror

Crystal Blue Frame

SCB2810S	Clear

Crystal Clear Frame

SCC2810S	Clear
SCC2810ST	Clear H2X Anti-Fog
SCC2870S	Silver Mirror

Crystal Gray Frame

SCG2810ST	Clear H2X Anti-Fog



Onix™ Class 1

- Cushioned temple tips provide non-slip comfort.
- Lightweight frame and suspended lens design provide perfect fit for a variety of users.
- Suspended lens provides stylish look, comfort fit, panoramic view and maximum protection.
- Adjustable nose piece provides 3 different angles, allowing the user to find the most comfortable fit.
- Ratcheting temples provide different angles for perfect view and fit.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Frame

Part	Lens
SB4910S	Clear
SB4910ST	Clear H2X Anti-Fog
SB4920S	Gray
SB4970S	Silver Mirror
SB4980S	Indoor/Outdoor Mirror

Hi-Vis Green Frame

SGR4910ST	Clear H2X Anti-Fog
SGR4920S	Gray
SGR4920ST	Gray H2X Anti-Fog

Black and Blue Frame

SN4920S	Gray

Pink Frame

SP4910S	Clear

Black and Red Frame

SR4980S	Indoor/Outdoor Mirror



Ionix™ Class 1

- Extreme style in safety eyewear.
- Built-in rubber nose piece.
- Ventilated, straight-back flexible temples.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Frame

Part	Lens
SB8110D	Clear
SB8110DT	Clear Anti-Fog
SB8116D	Sandstone Bronze
SB8120D	Gray
SB8120DT	Gray Anti-Fog
SB8165D	Ice Blue Mirror
SB8170D	Silver Mirror
SB8180D	Indoor/Outdoor Mirror



Forum® Class 1

- Soft PVC nose piece.
- Fashionable stream line design incorporates the elements of safety in trend setting eyewear.
- Metal emblem on temple presents this premium eyewear at the top of its class.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Frame

Part	Lens
SB6610D	Clear
SB6610DT	Clear H2X Anti-Fog
SB6620D	Gray
SB6670D	Silver Mirror
SB6680D	Indoor/Outdoor Mirror



Itek® Class 1

- Soft integrated nose piece.
- Lightweight, frameless protection is ideal for all-day wear.
- Soft dual injected rubber temple tips provide non-slip comfort.
- 9.75 base curve lens provides excellent side protection.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Part	Lens and Temples
S5810S	Clear
S5810ST	Clear Anti-Fog
S5820S	Gray
S5820ST	Gray Anti-Fog
S5830S	Amber
S5860S	Infinity Blue
S5870S	Silver Mirror
S5875S	Blue Mirror
S5880S	Indoor/Outdoor Mirror



Intrepid II® Class 1

- Soft, non-slip rubber nose piece.
- Sporty co-injected straight back nylon temples.
- Passes MIL-PRF 32432 High Velocity Impact Standards.

Black Temples

Part	Lens
SB8810S	Clear
SB8820S	Gray
SB8830S	Amber
SB8835S	Sun Block Bronze
SB8880S	Indoor/Outdoor Mirror