

HSM® 1049 SA PET Crusher

Much more than the average bottle crusher!



- Compacts PET bottles and cans down to 1/3 or 1/4 of the original volume
- Effortlessly perforates and crushes in one working cycle
- Crusher rollers are made of specially hardened and ground steel - completely impervious and sturdy - for longer life
- Scraper system removes the compressed plastic bottles and cans reliably from the crusher rollers
- Dosing shaft with several blades ensures the PET bottles and cans are fed reliably from the rollers
- Control is via an easy to use keyboard with forward / stop / reverse functions
- Illuminated display with current operating status: ready, overload, door open and container full
- Energy saving - automatically shuts down after 2 minutes of non use
- 2000 1 liter bottle capacity
- 76.6 gallon material collection trolley

HSM part#	HSM1692	HSM1697
Motor in Horsepower	2 hp	4 hp
Voltage / Frequency	120V / 60 Hz	3 x 208V / 60 Hz
Volume reduction at a ratio of	1:3 up to 1:4	1:3 up to 1:4
Working width	19.29"	19.29"
Bottle diameter	2" - 4.75"	2" - 4.75"
Throughput of PET bottles/cans per cycle	50 - 70	50 - 70
Hourly throughput of PET bottles/cans	up to 2400 / hr	up to 2400 / hr
Machine Dimensions (H x W x D)	35.4" x 31.18" x 62.4"	35.4" x 31.18" x 62.4"
Machine Weight	496 lbs	496 lbs
Options	Part #	
Plastic Bags	1452995000	

All technical specifications are approximate values. Technical and design modifications reserved.