

BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Version 2.3

Revision Date 12/05/2017

Print Date 05/13/2019

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Material number : 00000000001046473

Manufacturer or supplier's details

Company : Zep Inc.

Address : 350 Joe Frank Harris Parkway, SE
Emerson, GA 30137

Telephone : 404-352-1680

Emergency telephone numbers
For SDS Information : Compliance Services 1-877-428-9937

For a Medical Emergency : 877-541-2016 Toll Free - All Calls Recorded

For a Transportation : CHEMTREC: 800-424-9300 - All Calls Recorded.

Emergency : In the District of Columbia 202-483-7616

Recommended use of the chemical and restrictions on use

Recommended use : Hand Care

SECTION 2. HAZARDS IDENTIFICATION
Emergency Overview

| | |
|------------|----------------|
| Appearance | liquid |
| Colour | red |
| Odour | characteristic |

GHS Classification

Not a hazardous substance or mixture.

GHS label elements

Not a hazardous substance or mixture.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

| Chemical name | CAS-No. | Concentration [%] |
|--|------------|-------------------|
| Distillates (petroleum), hydrotreated light | 64742-47-8 | >= 20 - < 30 |
| Alcohols, C9-11, ethoxylated | 68439-46-3 | >= 5 - < 10 |
| Fatty acids, tall-oil, reaction products with isopropanolamine | 68440-26-6 | >= 1 - < 5 |
| Solvent naphtha (petroleum), heavy aliph. | 64742-96-7 | >= 1 - < 5 |
| White mineral oil (petroleum) | 8042-47-5 | >= 1 - < 5 |

BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Version 2.3

Revision Date 12/05/2017

Print Date 05/13/2019

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

- General advice : Move out of dangerous area.
Show this safety data sheet to the doctor in attendance.
Do not leave the victim unattended.
- If inhaled : If unconscious, place in recovery position and seek medical advice.
If symptoms persist, call a physician.
- In case of skin contact : This product is formulated for use on skin but should always be immediately washed off with plenty of water. Discontinue use if irritation and redness develop. If conditions persist for more than 72 hours, consult a physician.
- In case of eye contact : If eye irritation persists, consult a specialist.
Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If in eyes, rinse with water for 15 minutes.
- If swallowed : Keep respiratory tract clear.
DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.
- Most important symptoms and effects, both acute and delayed : Effects may be delayed, symptoms may include minor eye or skin irritation.
Overexposure may cause mild eye or skin irritation.
- Notes to physician : Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
Water spray jet
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during firefighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : Carbon dioxide (CO₂)
Carbon monoxide
Smoke
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Version 2.3

Revision Date 12/05/2017

Print Date 05/13/2019

- Further information : For safety reasons in case of fire, cans should be stored separately in closed containments.
Use a water spray to cool fully closed containers.
- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Material can create slippery conditions.
Use non-slip safety shoes in areas where spills or leaks can occur.
Refer to protective measures listed in sections 7 and 8.
- Environmental precautions : Prevent further leakage or spillage if safe to do so.
Prevent product from entering drains.
If the product contaminates rivers and lakes or drains inform respective authorities.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

- Advice on safe handling : Avoid contact with eyes.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Dispose of rinse water in accordance with local and national regulations.
- Conditions for safe storage : Keep container tightly closed in a dry and well-ventilated place.
Containers which are opened must be carefully resealed and kept upright to prevent leakage.
- Materials to avoid : No materials to be especially mentioned.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION
Components with workplace control parameters

| Components | CAS-No. | Value type (Form of exposure) | Control parameters / Permissible concentration | Basis |
|---|------------|----------------------------------|---|----------|
| Distillates (petroleum), hydrotreated light | 64742-47-8 | TWA | 500 ppm 2,000 mg/m ³ | OSHA Z-1 |
| | | TWA | 400 ppm 1,600 mg/m ³ | OSHA P0 |

BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Version 2.3

Revision Date 12/05/2017

Print Date 05/13/2019

| | | | | |
|-------------------------------|-----------|--------------------------------|----------|-----------|
| | | TWA (Mist) | 5 mg/m3 | OSHA Z-1 |
| | | TWA (Mist) | 5 mg/m3 | OSHA P0 |
| | | TWA (Mist) | 5 mg/m3 | NIOSH REL |
| | | ST (Mist) | 10 mg/m3 | NIOSH REL |
| | | PEL (particulate) | 5 mg/m3 | CAL PEL |
| White mineral oil (petroleum) | 8042-47-5 | TWA (Mist) | 5 mg/m3 | |
| | | STEL (Mist) | 10 mg/m3 | |
| | | TWA (Mist) | 5 mg/m3 | OSHA Z-1 |
| | | TWA (Inhalable fraction) | 5 mg/m3 | ACGIH |
| | | TWA (Mist) | 5 mg/m3 | OSHA P0 |
| | | TWA (Mist) | 5 mg/m3 | NIOSH REL |
| | | ST (Mist) | 10 mg/m3 | NIOSH REL |
| | | PEL (particulate) | 5 mg/m3 | CAL PEL |

Engineering measures : Not applicable

Personal protective equipment

Respiratory protection : In case of insufficient ventilation, wear suitable respiratory equipment.

Hand protection
Remarks : No special protection is required.

Eye protection : Eye protection is not required while washing with this product. In the workplace, the use of safety glasses is recommended to avoid eye exposure during the handling of containers or during spill clean-up.

Skin and body protection : No special protection is required.

Hygiene measures : Wash hands before breaks and at the end of workday.
When using do not eat or drink.
When using do not smoke.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : liquid

Colour : red

Odour : characteristic

Odour Threshold : No data available

pH : 7 - 8

Melting point/freezing point : No data available

Boiling point : not determined

BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Version 2.3

Revision Date 12/05/2017

Print Date 05/13/2019

| | |
|--|---------------------------------|
| Flash point | : > 93.3 °C Method: TCC |
| Evaporation rate | : 1 |
| Upper explosion limit | : No data available |
| Lower explosion limit | : No data available |
| Vapour pressure | : No data available |
| Relative vapour density | : No data available |
| Density | : 0.96 g/cm3 |
| Solubility(ies) | |
| Water solubility | : emulsifiable |
| Solubility in other solvents | : not determined |
| Partition coefficient: n-octanol/water | : No data available |
| Auto-ignition temperature | : not determined |
| Thermal decomposition | : No data available |
| Viscosity | |
| Viscosity, kinematic | : 40 mm ² /s (40 °C) |

SECTION 10. STABILITY AND REACTIVITY

| | |
|------------------------------------|---|
| Reactivity | : Stable |
| Chemical stability | : Stable under normal conditions. |
| Possibility of hazardous reactions | : No decomposition if stored and applied as directed. |
| Conditions to avoid | : No data available |
| Incompatible materials | : None. |
| Hazardous decomposition products | : No hazardous decomposition products are known. |

SECTION 11. TOXICOLOGICAL INFORMATION**Potential Health Effects**

| | |
|------------------------------|--|
| Aggravated Medical Condition | : None known. |
| Symptoms of Overexposure | : Effects may be delayed, symptoms may include minor eye or skin irritation. |

BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Version 2.3

Revision Date 12/05/2017

Print Date 05/13/2019

Carcinogenicity:**IARC**

No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

ACGIH

No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

OSHA

No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.

NTP

No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Acute toxicity**Product:**

Acute oral toxicity : Acute toxicity estimate : > 5,000 mg/kg
Method: Calculation method

Acute dermal toxicity : Acute toxicity estimate : > 5,000 mg/kg
Method: Calculation method

Components:**Distillates (petroleum), hydrotreated light:**

Acute oral toxicity : LD50 Rat: > 5,000 mg/kg

Acute inhalation toxicity : LC50 Rat: > 4.6 mg/l
Exposure time: 6 h

Acute dermal toxicity : LD50 Rat: > 2,000 mg/kg

Alcohols, C9-11, ethoxylated:

Acute oral toxicity : LD50 Oral Rat: 1,400 mg/kg

Skin corrosion/irritation**Product:**

Result: No skin irritation

Serious eye damage/eye irritation**Product:**

Result: No eye irritation

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Version 2.3

Revision Date 12/05/2017

Print Date 05/13/2019

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

Product:

Remarks: No data available

Components:

Distillates (petroleum), hydrotreated light:

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available

Bioaccumulative potential

Product:

Partition coefficient: n-octanol/water : Remarks: No data available

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Version 2.3

Revision Date 12/05/2017

Print Date 05/13/2019

Remarks : This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : No data available

Components:

Distillates (petroleum), hydrotreated light :

Additional ecological information : No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : The product should not be allowed to enter drains, water courses or the soil. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of in accordance with local regulations.

Contaminated packaging : Empty remaining contents. Dispose of as unused product. Do not re-use empty containers.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IMDG (Vessel):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Cargo Air):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Passenger Air):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: TDG (Canada):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications

BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Version 2.3

Revision Date 12/05/2017

Print Date 05/13/2019

noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.
No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act**CERCLA Reportable Quantity**

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : No SARA Hazards

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop. 65

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

DSL All components of this product are on the Canadian DSL
TSCA On TSCA Inventory

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

Inventory Acronym and Validity Area Legend:


TSCA (USA), DSL (Canada), NDSL (Canada)

BZ7946 CHERRY IHC PUMC N/PMP R04860 4/1G

Version 2.3

Revision Date 12/05/2017

Print Date 05/13/2019

SECTION 16. OTHER INFORMATION**Further information****NFPA:****HMIS III:**

| | |
|------------------------|----------|
| HEALTH | 0 |
| FLAMMABILITY | 1 |
| PHYSICAL HAZARD | 0 |

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Not a hazardous substance or mixture.

| | |
|----------------|------------|
| Version: | 2.3 |
| Revision Date: | 12/05/2017 |
| Print Date: | 05/13/2019 |

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.