1. IDENTIFICATION AND GENERAL INFORMATION

P/N#: 3001, 3001-05, 3001-10, 3001-20PP, 3001-20PPD, 3001-200PU

Nomenclature: Alcohol Free Towelettes Recommended Use of the Chemical & Restrictions on Use:

Uses: Personal protective equipment cleaner

Company Name: Allegro Industries
Address: 1360 Shiloh Church Rd
Piedmont, SC 29673

864-846-8740 Chemtrac: 800-424-9300

2. HAZARDS IDENTIFICATION

Appearance: Liquid absorbed onto a towelette

Physical State: Solid containing liquid

Classification:

This chemical does not meet the hazardous criteria set forth by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200). However, this Safety Data Sheet (SDS) contains valuable information critical to the safe handling and proper use of this product.

This SDS should be retained and available for employees and other users of this product.

Unknown Acute Toxicity: 1.82% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION

This product is not hazardous according to OSHA 29 CFR 1910.1200. Components not listed are not hazardous or are below reportable limits.

4. FIRST AID MEASURES

Inhalation: Remove to fresh air. If breathing is difficult, give oxygen. If breathing has stopped, give artificial respiration.

Skin Contact: Wash skin off with water. Remove contaminated clothing and clean before reusing.

Eye Contact: Flush eyes immediately with plenty of water. **Ingestion:** If swallowed, consult a physician immediately.

Most important symptoms and effects:

Symptoms: Mists may irritate nasal passages. Prolonged inhalation of vapors causes nausea, loss of motor skills,

and disorientation. Contact with eyes is painful and will cause chemical burns. Prolonged contact

with skin causes irritation.

Indication of any immediate medical attention and special treatment needed:

Notes to Physician: Treat symptomatically.

5. FIRE FIGHTING MEASURES

Suitable Extinguishing Media:

Dry chemical. Carbon dioxide (CO2). Foam. Water spray (fog). Any "ABC" class.

Unsuitable Extinguishing

Not determined

Media:

Specific Hazards Arising

Not determined

from the Chemical:

Protective equipment and precautions for firefighters:

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and fullprotective gear. Clothing should be worn in fighting fires involving chemicals.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures:

MS010

REV:I

Personal Precautions: Use personal protective equipment as required. Prevent electrical sparking. Ventilate area of leak or spill. Spilled

material is slippery. Wash thoroughly after handling.

Environmental Precautions: Contain all spills and leaks to prevent discharge into the environment. See Section 12 for additional

Ecological Information.

Methods and material for containment and cleaning up:

Methods for Containment: Prevent further leakage or spillage if safe to do so.

Methods for Clean-Up: Small spills: Soak up with absorbent, shovel into waste container, and flush with water.

Large spills: Recover liquid for reprocessing or disposal.

7. HANDLING AND STORAGE

Precautions for safe handling:

Advice on Safe Handling: Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities:

Storage Conditions: Empty container may retain vapor or residue. Keep container tightly closed and store in a

cool, dry and well-ventilated place.

Incompatible Materials: None known based on information supplied.

8. EXPOSURE CONTROLS

Exposure Guidelines: This product, as supplied, does not contain any hazardous materials with occupational

exposure limits established by the region specific regulatory bodies

Appropriate engineering controls:

Engineering Controls: Apply technical measures to comply with the occupational exposure limits.

Individual protection measures, such as personal protective equipment:

Eye/Face Protection: Avoid contact with eyes.

Skin and Body Protection: Wear suitable protective clothing.

Respiratory Protection: Ensure adequate ventilation, especially in confined areas.

General Hygiene

Partition Coefficient:

Considerations: Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State: Solid containing liquid

Appearance: Liquid absorbed onto a towelette

Color:Not determinedOdor:Not determinedOdor Threshold:Not determinedAuto-Ignition Temperature:Not determinedFlash Point:105 °C / 221 °F

Flammable Limits in Air- Lower: 3% Flammable Limits in Air-Upper: 19%

pH: Not determined
Melting Point: Not determined
Freezing Point: Not determined
Boiling Point/ Boiling Range: 93 °C / 200 °F
Flammability: Not determined
Solubility: Not determined
Decomposition Temperature: Not determined

MS010

Not determined

Viscosity: Not determined

Evaporation Rate: Estimated slower than ethyl ether **Vapor Density:** Estimated heavier than air

Vapor Pressure: Not determined

10. STABILITY AND REACTIVITY

Reactivity: Not reactive under normal conditions.

Chemical Stability: Stable under recommended storage conditions.

Possibility of Hazardous

Reactions: None under normal processing. Conditions to Avoid: Avoid open fire or flame.

Incompatible Materials: None known based on information supplied.

Hazardous Decomposition

Products: None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure:

Product Information:

Eve Contact: Avoid contact with eyes. **Skin Contact:** Avoid contact with skin.

Inhalation: Do not inhale. **Ingestion:** Do not ingest.

Component Information:

Information on physical, chemical and toxicological effects:

Symptoms: Mists may irritate nasal passages. Prolonged inhalation of vapors causes nausea, loss of motor skills,

and disorientation. Contact with eyes is painful and will cause chemical burns. Prolonged contact

with skin causes irritation.

Delayed and immediate effects as well as chronic effects from short and long-term exposure:

Carcinogenicity: This product does not contain any carcinogens or potential carcinogens as listed by OSHA, IARC or NTP.

Numerical measures of toxicity: Not determined

Unknown Acute Toxicity: 1.82% of the mixture consists of ingredient(s) of unknown toxicity.

12. ECOLOGICAL INFORMATION

Ecotoxicity: The product is not classified as environmentally hazardous. However, this does not exclude the possibility

that large or frequent spills can have a harmful or damaging effect on the environment.

Persistence/Degradability: Not determined.

Bioaccumulation: Not determined.

Mobility: Not determined.

Other Adverse Effects: Not determined.

13. DISPOSAL CONSIDERATIONS

Waste Treatment Methods:

Recover material or dispose in accordance with all applicable federal, state and local **Disposal of Wastes:**

regulations. Material collected with absorbent may be disposed in a permitted landfill in

accordance with federal, state and local regulations.

Contaminated Packaging: Disposal should be in accordance with applicable regional, national and local laws and **MS010**

regulations.

14. TRANSPORT INFORMATION

Note: Please see current shipping paper for most up to date shipping information, including

exemptions and special circumstances.

DOT: Not regulated

IATA: Not regulated

IMDG: Not regulated

15. REGULATORY INFORMATION

US Federal Regulations:

CERCLA: This material, as supplied, does not contain any substances regulated as hazardous substances under the

Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the

Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355).

SARA 313: Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA).

This product does not contain anychemicals which are subject to the reporting requirements of the Act and

Title 40 of the Code of Federal Regulations, Part 372

CWA (Clean Water Act): This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act

(40 CFR 122.21 and 40CFR 122.42)

US State Regulations:

California Proposition 65: This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know

Regulations: This product does not contain any substances regulated under applicable state right-to-know regulations

16. OTHER INFORMATION

NFPA HMIS

Health Hazards: Not determined **Health Hazards:** Not determined Flammability: Not determined Flammability: Not determined **Instability:** Not determined **Physical Hazards:** Not determined **Special Hazards:** Not determined **Personal Protection:** Not determined

Revised October 21, 2019 Rev. I

DISCLAIMER: THE INFORMATION FURNISHED HEREIN IS BELIEVED TO BE ACCURATE AND REPRESENTS
THE BEST DATA CURRENTLY AVAILABLE TO US. NO WARRANTY, EXPRESSED OR IMPLIED IS MADE
AND ALLEGRO INDUSTRIES ASSUMES NO LEGAL RESPONSIBILITY OR LIABILITY RESULTING FROM ITS USE.