



# **SPECIFICATIONS**

Description: FILTRATION SYSTEM
Part Number: 9872-40, 9872-40W/O
Style: FIXED TO 2 OUTPUTS

## **GENERAL DESCRIPTION:**

System for compressed air filtration that meets NIOSH regulations for breathing systems. Three stages of filtration: to dust, water, oil and hydrocarbons from compressed air. *Optional* Carbon Monoxide monitor is provided to monitor gas concentrations. Provides filtered air for Grade D breathing.

### FILTER SYSTEM:

1st stage: Filter 5 micron particles and automatic drain

2nd Stage: Coalescing filter cloth and drain 0010

microns manual

3rd Stage: Activated carbon filter of 0.003 microns and manual drain

Regulator: High pressure adjustable knob range 0-160 PSI gauge and external valve

pressure relief

Manometer: Acrylic translucent, Teflon float, with adjustable valve.

Graduations: 0.0 - 1.0 LPM

## **CARBON MONOXIDE MONITOR:**

Power Source: 115V AC adapter 9V DC

9V DC Alkaline battery (optional)

Alarm: 10 ppm (Canada: 5ppm) with external connection for strobe light alarm.

(PN 9871-01 – optional)

Audible Alarm: 90 dB (*Piezo*)

Visual: External LED Light

Censor: Electrochemical, replaceable

Buttons: "Mode" and "Set" Display: Liquid Crystal

Operations: Average, maximum battery charge and calibration

Calibration: Auto Tune to 20 ppm of carbon monoxide

#### **DIMENSIONS:**

Length In. (cm)	Width In. (cm)	Height In. (cm)	Weight Lbs. (Kg)
13" (32.5)	6" (15)	12" (30)	18 (8.1)

1360 Shiloh Church Road Piedmont, SC 29673 864-846-8740 800-622-3530 FAX: 800-362-7231 www.allegrosafety.com