



# LED PANEL LAMP



## PRODUCT FEATURES

- White, Ultra Thin & Seamless Aluminum Frame
- Durable Aluminum Backing for Rigidity
- UL Certified with Isolated External Power Supply
- DLC 4.4 Standard
- Edge-lit LED Technology (2 Sides)
- IP20 Rating
- 100-277 Voltage Rating, 0-10V Dimming
- **Rubber Cushion Inserts** (6) to Prevent Misalignment of LEDs
- Constructed Using Double Sided, Robot Welding Technology
- 50,000 Hour Lifetime Rating
- Flicker-free
- PMMA LGP Anti-Yellow Lens
- 5-Year Limited Warranty
- Can be Surface Mounted, Recessed or Suspended

## PRODUCT SPECIFICATIONS

MODEL	POWER (W)	LUMENS (LM)	CCT (K)	DIMENSIONS (FT)	EFFICIENCY (lm/W)	BEAM ANGLE
CLP7-2X2-40WN-S40KA	40	4000	4000	2 X 2	100	120°
CLP7-2X2-40WN-S50KA	40	4000	5000	2 X 2	100	120°
CLP7-2X4-50WN-S40KA	50	5000	4000	2 x 4	100	120°
CLP7-2X4-50WN-S50KA	50	5000	5000	2 x 4	100	120°

