

Specifications



**Model 761219
Wall Mounted
Bottle Refilling
Station**

*Rated for indoor
use only*

Replacement Filters:
Model 761215 or 761215 PF

*For more information visit:
globalindustrial.com
or call 1-800-645-1232*

FEATURES:

- Touchless, sensor activation with auto 20-second Touchless
- Keyed door for easy filter access
- Quick-fill rate of 1.0 GPM
- Laminar water flow ensures minimal splash
- Splash proof drain cover
- Drainage system eliminates standing water
- LED filter level indicator display
- LED display counter tracks bottle quantity saved from waste
- Rust-proof and dent resistant lower cover
These claims verified through internal manufacture testing

COOLING SYSTEM:

- Hermetically-sealed, single-phase reciprocating compressor; lifetime lubrication
- Fan cooled condenser with copper tube and aluminum fins; permanently lubricated motor
- Cooling system includes self-cleansing tube tank, continuous copper tubing, stainless steel tank and EPS foam insulation; meets UL requirements for self-extinguishing material
- R134a refrigerant control accurately calibrates capillary tubes
- Easily accessible and adjustable thermostat

Replacement Filter: Model 761215

3600-gallon capacity filtration system with NSF/ANSI 42 & 53 (lead, class 1 particulate, chlorine, taste and odor)

Replacement Filter: Model 761215PF

3600-gallon capacity filtration system with NSF/ANSI 42, 53 & 401 (lead, class 1 particulate, chlorine, taste and odor, PFAS, Cyst, Turbidity and Microplastic)

CONSTRUCTION:

- Stainless steel pan with integral drain
- Galvanized structural steel frame
- Stainless steel bottle filler trim
- Rust-proof and dent resistant lower cover




Meets all ADA Guidelines

System 761219 certified by IAPMO R&T against NSF/ANSI/CAN 372 for lead free compliance Meets Federal and State Low-Lead Law Requirements Certified to UL399 and CAN/CSA 22.2 No. 120

WARRANTY:

5 year limited warranty on refrigeration system. Electrical components and water system are warranted for 12 months from the date of installation, or 18 months from the factory shipment date (whichever date comes first).

Specifications Chart

Specifications Chart							
Model	Voltage/Hertz	*Chilling Cap.	F.L. Amps	Rated Watts	UL399 and CAN/CSA 22.2 No. 120 Certified	ADA Compliant	System 761219 certified by IAPMO R&T against NSF/ANSI/CAN 372 for lead free compliance
761219	115V/60Hz	8 GPH	1.9	185	✓	✓	✓

*At 46° - 54° (F) against ambient air temperature of 77° (F)

PATENTED AND OTHER PATENTS PENDING