

AUTO RIDE-ON FLOOR SWEEPER SCRUBBER

WITH A 44"W CLEANING PATH, BY GLOBAL INDUSTRIAL™



Quickly clean large areas with the Global Industrial™ Auto Ride-On Floor Sweeper Scrubber.

Built for efficiency, this **2-in-1 machine** combines the functionality of a sweeper and the cleaning power of a floor scrubber in a single unit for a deeper, more thorough clean. The **magnetic bar** collects metal debris to prevent damage to the machine, while the **dust suppression system** stops dust from becoming airborne during operation, reducing wear & tear. This unit features an **onboard sprayer**, a **built-in vacuum tool kit** for hard-to-reach places, and a **solution tank with a quick-connect fitting** that cuts off the water hose when it is done filling.

Best for use in warehouses, distribution centers, and other large facilities, this sweeper scrubber is powered by maintenance-free AGM batteries, has a 4-hour runtime, and provides operators with a 44"W cleaning path with a coverage rate of **130,000 sq. ft. per hour**. For operator safety, this machine is equipped with a **blue safety light**, a **strobe light**, a **seat belt**, a **pressure-sensitive seat**, and a **backup camera with a video display** that helps eliminate blind spots.

KEY FEATURES



MAGNETIC BAR

The magnetic pickup bar collects metal debris, such as loose nuts, bolts, nails, and more, while cleaning to prevent damage to the machine



2-IN-1 MACHINE

Engineered to deliver the combined functionality of a sweeper and a floor scrubber, this innovative machine improves workplace efficiency by quickly cleaning large facilities



BUILT-IN TOOL KIT

Designed for precision cleaning, the onboard tool kit includes a sprayer, an extension hose, and dual vacuum wands for spot cleaning and reaching difficult areas

WEIGHT & DIMENSIONS

Height	61"
Length	108"
Weight	2645 lbs.
Squeegee Width	57"
Cleaning Width	44"

PRODUCT DETAILS

Assembly Required	No
Operation	Battery AGM 12*6V/200Ah
Type	Traction Drive
Number Of Speeds	Variable Speed
Cleaning Capacity	130,000 SQ. FT/HR
Drive Speed	0-8 MPH
Voltage	72
Battery Runtime	4 HRS
Pad Pressure	170 lbs.
Brush Motor RPM	175
Solution Tank	87.2 Gal.
Water Lift	65"

MADE TO EXCEED.®

- ✓ Sweep & scrub in a single pass
- ✓ Built for cleaning large industrial facilities
- ✓ Easy to operate with intuitive controls
- ✓ Advanced safety features




57" Wide Cast Aluminum Squeegee Assembly




Blue Safety Light Alerts Personnel Of Approaching Equipment



Intuitive Driver Controls With Backup Camera Display



Magnetic Bar Collects Metal Debris And Hardware



Sprayer, Dual Vacuum Wands, & Extension Hose