


Assembly Instructions

 Customer Service
 US: 1-800-645-2986

Instrucciones de Ensamblaje













 Servicio de atención al Cliente
 US: 1-800-645-2986

Directives d'assemblage

 Service à la clientèle
 Canada: 888-645-2986




Solar Powered LED Sign

Models 708312 708313

CONTENTS					
Ref.	Qty.	Description	Ref.	Qty.	Description
1	1	Flashing Sign	H6	4	12mm Diameter Plain Washer..... 
2	1	Solar Panel Assembly	H7	4	12mm Diameter Lock Washer 
3	2	Pole Mounting Bracket	H8	4	M12 x 1.50 Hex Nut 
H1	1	M10 x 1.5 x 25mm Lg. Torx Pan Head Bolt 	H9	2	8mm Diameter Plain Washer 
H2	1	10mm Diameter Lock Washer 	H10	2	8mm Diameter Lock Washer 
H3	1	10mm Diameter Plain Washer 	H11	2	M8 x 1.25 Hex Nut 
H4	4	M12 x 1.50 x 45mm Lg. T-Bolt 		1	Torx Allen Key 
H5	2	M8 x 1.25 x 45mm Lg. T-Bolt 		1	AC Charger



WARNING

- Before proceeding with any assembly, installation, maintenance, and/or troubleshooting, read all Warnings. Failure to pay attention to them could result in serious injury or death.
- Use OSHA- approved Protective Clothing and Devices, Cut-proof Gloves, and Safety Glasses for all procedures. Failure to do so could result in serious injury or death.
- Solar panels produce an electrical current. To reduce the risk of injury, use shock-proof gloves and never perform any procedure in or near standing water.
- Batteries must be disposed of according to local code. **DO NOT INCINERATE!** Failure to heed this warning could result in serious injury or death.




Solar Powered LED Sign



Assembly Instructions



Detail A



Detail B



SPECIFICATIONS

Model	708312	708313
Type	Solar Powered Stop Sign, MUTCD: R1-1	Solar Powered Pedestrian Crossing Sign, MUTCD: R1-1
Material	Aluminum	Aluminum
Solar Panel	Monocrystalline Silicone 18V, 10W	Monocrystalline Silicone 12V, 5W
Reflective Film	3M Diamond Grade Reflective Film	3M Diamond Grade Reflective Film
LED	Monocrystalline Red LED 1W	Monocrystalline Yellow LED 1W
Flashing Interval	50 times/minute	50 times/minute
Modes	Off, Flashing 12 hours/day, 24 hours/day	Off, Flashing 12 hours/day, 24 hours/day
Battery	Lithium Ion (11.1V/10Ah), 5-7 Days working time after one full charge, 3-5 year lifetime	
Visible Distance	2600 Feet	2600 Feet
MUTCD	MUTCD Section 2A.07 Retro Reflectivity and Illumination	