

COMMERCIAL AIR SCRUBBER & NEGATIVE AIR MACHINE

WITH HEPA FILTRATION, 3300 CFM BY GLOBAL INDUSTRIAL™

This Commercial Air Scrubber & Negative Air Machine is your solution for heavy-duty air purification.

An ideal solution for warehouses, gymnasiums, and other large spaces, this machine is outfitted with 4" casters for easy maneuverability and is designed to fit through standard door openings. Featuring a durable steel body, this unit is built to perform in any environment. When used as a stand-alone unit, this versatile machine acts as an air purifier or it can be used as a negative air machine when ducting is attached to exhaust filtered air outside the affected area. 20" diameter ducting available separately. Limited 1-Year Warranty.

FEATURES INCLUDE:



2-STAGE FILTRATION SYSTEM

Stage 1 - (4) Pleated MERV 9 Pre-Filters collect and trap pollen, hair, and larger dust particles

Stage 2 - (4) HEPA MERV 16 filters catch bacteria, allergens, dust, mold spores, and fungi



OPTIMAL VERSATILITY

Daisy-chain capability allows you to link up to three units using a single power outlet



LIGHT INDICATOR

Indicator light illuminates when the HEPA filter needs to be replaced

WEIGHT & DIMENSIONS

Width x Length x Height	24" x 24" x 43-1/2"
Weight	150 lbs.
Cord Length	25 ft
Coverage Area	10,000 ft ²

PRODUCT DETAILS

Filtration Type	Pre-Filter/HEPA
Type	Commercial Air Scrubber/Negative Air Machine
CFM	3300 CFM
Amperage	5 A
Number of Speeds	Variable
Hertz	60 Hz
Casters	Yes
Purification%	99.97 Against 0.3-Micron Particles
Wattage	600W
Voltage	115 V
Decibels	75



HIGHLIGHTS

- ✓ 2-stage HEPA filtration system for advanced air purification
- ✓ Capable of filtering/scrubbing/cleaning up to 4.7 Million cubic feet per day
- ✓ Uses an efficient mix of airflow and filtration to create cleaner air



20" air outlet for venting outside



25' power cord



4 air intakes (1 on each side) with 2-stage filtration



Locking caster wheels provide mobility